

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1057282

Luminaire Tested: PRLX-CYL2W-DI-X-930-15L-SP-MD-U-S-X-X-BLAK

Issue Date: 8/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1057282
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2504-407-4, G2-2504-407-5)
Test Lab: INNOVATION CENTER
Issue Date: 8/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-CYL2W-DI-X-930-15L-SP-MD-U-S-X-X-BLAK
Description: PrentaLux 2-INCH CYLINDER
DOWNLIGHT 750 LUMENS, SPOT OPTIC (19-DEGREES)
UPLIGHT 750 LUMENS, MEDIUM OPTIC (23-DEGREES)
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1714.1 lumens
Efficiency: N/A
Efficacy: 133.9 lumens/watt
Spacing Criteria (0/90/45): 0.33 / 0.33 / 0.34
Luminous Opening: Circular (Dia: 0.15' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 12.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1057282

CATALOG NUMBER: PRLX-CYL2W-DI-X-930-15L-SP-MD-U-S-X-X-BLAK

Luminous Intensity Polar Plot



TEST NUMBER: P1057282

CATALOG NUMBER: PRLX-CYL2W-DI-X-930-15L-SP-MD-U-S-X-X-BLAK

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	101	97	95	92	93	90	88	86	77	75	74	65	64	63	54	53	53
2	95	89	85	81	88	83	79	76	72	69	67	61	60	58	52	51	50
3	89	82	77	73	83	77	73	69	67	64	62	58	56	54	50	49	48
4	84	76	71	66	78	72	67	63	63	60	57	55	53	51	48	47	45
5	80	71	65	61	74	67	62	58	60	56	53	53	50	48	46	45	43
6	75	67	61	56	71	63	58	54	57	53	50	50	48	46	45	43	42
7	72	63	57	53	67	60	54	51	54	50	47	48	46	44	43	41	40
8	68	59	53	49	64	56	51	48	51	47	45	46	44	42	42	40	39
9	65	56	51	47	62	54	49	45	49	45	43	45	42	40	40	39	37
10	63	53	48	44	59	51	46	43	47	43	41	43	40	38	39	37	36

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2860514	2860514	2860514
5°	2387768	2387768	2387768
10°	1361594	1361594	1361594
15°	651741	651741	651741
20°	364833	364833	364833
25°	255618	255618	255618
30°	177099	177099	177099
35°	92987	92987	92987
40°	34238	34238	34238
45°	10207	10207	10207
50°	4812	4812	4812
55°	3595	3595	3595
60°	3093	3093	3093
65°	2440	2440	2440
70°	1507	1507	1507
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10207 cd/sqm

TEST NUMBER: P1057282

CATALOG NUMBER: PRLX-CYL2W-DI-X-930-15L-SP-MD-U-S-X-X-BLAK

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	297.3	17.3
10°-20°	289.4	16.9
20°-30°	166.6	9.7
30°-40°	76.8	4.5
40°-50°	11.6	0.7
50°-60°	2.8	0.2
60°-70°	1.4	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.6	0.0
110°-120°	1.8	0.1
120°-130°	3.6	0.2
130°-140°	13.9	0.8
140°-150°	82.1	4.8
150°-160°	187.6	10.9
160°-170°	325.0	19.0
170°-180°	253.3	14.8
0°-30°	753.3	43.9
0°-40°	830.1	48.4
0°-60°	844.5	49.3
0°-90°	846.2	49.4
90°-120°	2.3	0.1
90°-150°	102.0	5.9
90°-180°	868.0	50.6
0°-180°	1714.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4439	4439	4439	4439	4439	
5°	3691	3691	3691	3691	3691	297
15°	977	977	977	977	977	289
25°	360	360	360	360	360	167
35°	118	118	118	118	118	77
45°	11	11	11	11	11	12
55°	3	3	3	3	3	3
65°	2	2	2	2	2	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0
95°	0	0	0	0	0	0
105°	1	1	1	1	1	1
115°	2	2	2	2	2	2
125°	4	4	4	4	4	4
135°	14	14	14	14	14	14
145°	125	125	125	125	125	82
155°	399	399	399	399	399	188
165°	1154	1154	1154	1154	1154	325
175°	2995	2995	2995	2995	2995	253
180°	3441	3441	3441	3441	3441	

TEST NUMBER: P1057282

CATALOG NUMBER: PRLX-CYL2W-DI-X-930-15L-SP-MD-U-S-X-X-BLAK

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4438.9	4438.9	4438.9	4438.9	4438.9
1°	4354.8	4354.8	4354.8	4354.8	4354.8
2°	4270.8	4270.8	4270.8	4270.8	4270.8
3°	4121.3	4121.3	4121.3	4121.3	4121.3
4°	3906.2	3906.2	3906.2	3906.2	3906.2
5°	3691.2	3691.2	3691.2	3691.2	3691.2
6°	3377.1	3377.1	3377.1	3377.1	3377.1
7°	3063.0	3063.0	3063.0	3063.0	3063.0
8°	2741.0	2741.0	2741.0	2741.0	2741.0
9°	2410.9	2410.9	2410.9	2410.9	2410.9
10°	2080.8	2080.8	2080.8	2080.8	2080.8
11°	1817.6	1817.6	1817.6	1817.6	1817.6
12°	1554.3	1554.3	1554.3	1554.3	1554.3
13°	1333.5	1333.5	1333.5	1333.5	1333.5
14°	1155.2	1155.2	1155.2	1155.2	1155.2
15°	976.9	976.9	976.9	976.9	976.9
16°	865.1	865.1	865.1	865.1	865.1
17°	753.3	753.3	753.3	753.3	753.3
18°	664.3	664.3	664.3	664.3	664.3
19°	598.1	598.1	598.1	598.1	598.1
20°	532.0	532.0	532.0	532.0	532.0
21°	491.4	491.4	491.4	491.4	491.4
22°	450.8	450.8	450.8	450.8	450.8
23°	416.3	416.3	416.3	416.3	416.3
24°	387.9	387.9	387.9	387.9	387.9
25°	359.5	359.5	359.5	359.5	359.5
26°	335.2	335.2	335.2	335.2	335.2
27°	310.9	310.9	310.9	310.9	310.9
28°	286.6	286.6	286.6	286.6	286.6
29°	262.3	262.3	262.3	262.3	262.3
30°	238.0	238.0	238.0	238.0	238.0
31°	212.8	212.8	212.8	212.8	212.8
32°	187.6	187.6	187.6	187.6	187.6
33°	163.6	163.6	163.6	163.6	163.6
34°	140.9	140.9	140.9	140.9	140.9
35°	118.2	118.2	118.2	118.2	118.2
36°	100.0	100.0	100.0	100.0	100.0
37°	81.8	81.8	81.8	81.8	81.8
38°	66.3	66.3	66.3	66.3	66.3
39°	53.5	53.5	53.5	53.5	53.5
40°	40.7	40.7	40.7	40.7	40.7
41°	33.1	33.1	33.1	33.1	33.1
42°	25.4	25.4	25.4	25.4	25.4
43°	19.5	19.5	19.5	19.5	19.5
44°	15.3	15.3	15.3	15.3	15.3

TEST NUMBER: P1057282

CATALOG NUMBER: PRLX-CYL2W-DI-X-930-15L-SP-MD-U-S-X-X-BLAK

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
45°	11.2	11.2	11.2	11.2	11.2
46°	9.3	9.3	9.3	9.3	9.3
47°	7.3	7.3	7.3	7.3	7.3
48°	6.1	6.1	6.1	6.1	6.1
49°	5.4	5.4	5.4	5.4	5.4
50°	4.8	4.8	4.8	4.8	4.8
51°	4.2	4.2	4.2	4.2	4.2
52°	3.5	3.5	3.5	3.5	3.5
53°	3.2	3.2	3.2	3.2	3.2
54°	3.2	3.2	3.2	3.2	3.2
55°	3.2	3.2	3.2	3.2	3.2
56°	2.9	2.9	2.9	2.9	2.9
57°	2.6	2.6	2.6	2.6	2.6
58°	2.4	2.4	2.4	2.4	2.4
59°	2.4	2.4	2.4	2.4	2.4
60°	2.4	2.4	2.4	2.4	2.4
61°	2.1	2.1	2.1	2.1	2.1
62°	1.8	1.8	1.8	1.8	1.8
63°	1.6	1.6	1.6	1.6	1.6
64°	1.6	1.6	1.6	1.6	1.6
65°	1.6	1.6	1.6	1.6	1.6
66°	1.3	1.3	1.3	1.3	1.3
67°	1.0	1.0	1.0	1.0	1.0
68°	0.8	0.8	0.8	0.8	0.8
69°	0.8	0.8	0.8	0.8	0.8
70°	0.8	0.8	0.8	0.8	0.8
71°	0.8	0.8	0.8	0.8	0.8
72°	0.8	0.8	0.8	0.8	0.8
73°	0.6	0.6	0.6	0.6	0.6
74°	0.3	0.3	0.3	0.3	0.3
75°	0.0	0.0	0.0	0.0	0.0
76°	0.0	0.0	0.0	0.0	0.0
77°	0.0	0.0	0.0	0.0	0.0
78°	0.0	0.0	0.0	0.0	0.0
79°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
81°	0.0	0.0	0.0	0.0	0.0
82°	0.0	0.0	0.0	0.0	0.0
83°	0.0	0.0	0.0	0.0	0.0
84°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
86°	0.0	0.0	0.0	0.0	0.0
87°	0.0	0.0	0.0	0.0	0.0
88°	0.0	0.0	0.0	0.0	0.0
89°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1057282

CATALOG NUMBER: PRLX-CYL2W-DI-X-930-15L-SP-MD-U-S-X-X-BLAK

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0
91°	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0
103°	0.2	0.2	0.2	0.2	0.2
104°	0.5	0.5	0.5	0.5	0.5
105°	0.8	0.8	0.8	0.8	0.8
106°	0.8	0.8	0.8	0.8	0.8
107°	0.8	0.8	0.8	0.8	0.8
108°	0.8	0.8	0.8	0.8	0.8
109°	0.8	0.8	0.8	0.8	0.8
110°	0.8	0.8	0.8	0.8	0.8
111°	1.1	1.1	1.1	1.1	1.1
112°	1.4	1.4	1.4	1.4	1.4
113°	1.6	1.6	1.6	1.6	1.6
114°	1.6	1.6	1.6	1.6	1.6
115°	1.6	1.6	1.6	1.6	1.6
116°	1.9	1.9	1.9	1.9	1.9
117°	2.2	2.2	2.2	2.2	2.2
118°	2.4	2.4	2.4	2.4	2.4
119°	2.4	2.4	2.4	2.4	2.4
120°	2.4	2.4	2.4	2.4	2.4
121°	2.7	2.7	2.7	2.7	2.7
122°	3.0	3.0	3.0	3.0	3.0
123°	3.4	3.4	3.4	3.4	3.4
124°	3.7	3.7	3.7	3.7	3.7
125°	4.0	4.0	4.0	4.0	4.0
126°	4.3	4.3	4.3	4.3	4.3
127°	4.6	4.6	4.6	4.6	4.6
128°	5.1	5.1	5.1	5.1	5.1
129°	5.8	5.8	5.8	5.8	5.8
130°	6.4	6.4	6.4	6.4	6.4
131°	7.3	7.3	7.3	7.3	7.3
132°	8.3	8.3	8.3	8.3	8.3
133°	9.7	9.7	9.7	9.7	9.7
134°	11.7	11.7	11.7	11.7	11.7

TEST NUMBER: P1057282

CATALOG NUMBER: PRLX-CYL2W-DI-X-930-15L-SP-MD-U-S-X-X-BLAK

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
135°	13.6	13.6	13.6	13.6	13.6
136°	18.4	18.4	18.4	18.4	18.4
137°	23.2	23.2	23.2	23.2	23.2
138°	29.6	29.6	29.6	29.6	29.6
139°	37.5	37.5	37.5	37.5	37.5
140°	45.5	45.5	45.5	45.5	45.5
141°	59.0	59.0	59.0	59.0	59.0
142°	72.4	72.4	72.4	72.4	72.4
143°	88.3	88.3	88.3	88.3	88.3
144°	106.9	106.9	106.9	106.9	106.9
145°	125.4	125.4	125.4	125.4	125.4
146°	149.7	149.7	149.7	149.7	149.7
147°	174.0	174.0	174.0	174.0	174.0
148°	199.4	199.4	199.4	199.4	199.4
149°	225.9	225.9	225.9	225.9	225.9
150°	252.4	252.4	252.4	252.4	252.4
151°	280.5	280.5	280.5	280.5	280.5
152°	308.6	308.6	308.6	308.6	308.6
153°	338.0	338.0	338.0	338.0	338.0
154°	368.7	368.7	368.7	368.7	368.7
155°	399.4	399.4	399.4	399.4	399.4
156°	439.0	439.0	439.0	439.0	439.0
157°	478.6	478.6	478.6	478.6	478.6
158°	526.7	526.7	526.7	526.7	526.7
159°	583.3	583.3	583.3	583.3	583.3
160°	639.8	639.8	639.8	639.8	639.8
161°	725.5	725.5	725.5	725.5	725.5
162°	811.1	811.1	811.1	811.1	811.1
163°	914.0	914.0	914.0	914.0	914.0
164°	1034.1	1034.1	1034.1	1034.1	1034.1
165°	1154.2	1154.2	1154.2	1154.2	1154.2
166°	1309.2	1309.2	1309.2	1309.2	1309.2
167°	1464.2	1464.2	1464.2	1464.2	1464.2
168°	1637.2	1637.2	1637.2	1637.2	1637.2
169°	1828.3	1828.3	1828.3	1828.3	1828.3
170°	2019.3	2019.3	2019.3	2019.3	2019.3
171°	2229.6	2229.6	2229.6	2229.6	2229.6
172°	2439.8	2439.8	2439.8	2439.8	2439.8
173°	2634.9	2634.9	2634.9	2634.9	2634.9
174°	2814.7	2814.7	2814.7	2814.7	2814.7
175°	2994.6	2994.6	2994.6	2994.6	2994.6
176°	3121.8	3121.8	3121.8	3121.8	3121.8
177°	3249.0	3249.0	3249.0	3249.0	3249.0
178°	3338.3	3338.3	3338.3	3338.3	3338.3
179°	3389.7	3389.7	3389.7	3389.7	3389.7

TEST NUMBER: P1057282

CATALOG NUMBER: PRLX-CYL2W-DI-X-930-15L-SP-MD-U-S-X-X-BLAK

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
180°	3441.2	3441.2	3441.2	3441.2	3441.2

TEST NUMBER: P1057282

CATALOG NUMBER: PRLX-CYL2W-DI-X-930-15L-SP-MD-U-S-X-X-BLAK

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	1.29	0.00	0.00	0.00	0.00	1.29
	3H	0.00	0.00	0.00	0.36	1.68	0.00	0.00	0.00	0.36	1.68
	4H	0.00	0.00	0.00	0.28	1.61	0.00	0.00	0.00	0.28	1.61
	6H	0.00	0.00	0.00	0.12	1.46	0.00	0.00	0.00	0.12	1.46
	8H	0.00	0.00	0.00	0.05	1.38	0.00	0.00	0.00	0.05	1.38
	12H	0.00	0.00	0.00	0.00	1.31	0.00	0.00	0.00	0.00	1.31
4H	2H	0.00	0.00	0.00	0.21	1.54	0.00	0.00	0.00	0.21	1.54
	3H	0.00	0.00	0.34	0.77	2.11	0.00	0.00	0.34	0.77	2.11
	4H	0.00	0.00	0.27	0.65	2.01	0.00	0.00	0.27	0.65	2.01
	6H	0.00	0.00	0.16	0.50	1.86	0.00	0.00	0.16	0.50	1.86
	8H	0.00	0.00	0.10	0.40	1.77	0.00	0.00	0.10	0.40	1.77
	12H	0.00	0.00	0.04	0.30	1.68	0.00	0.00	0.04	0.30	1.68
8H	4H	0.00	0.00	0.16	0.46	1.83	0.00	0.00	0.16	0.46	1.83
	6H	0.00	0.00	0.06	0.32	1.69	0.00	0.00	0.06	0.32	1.69
	8H	0.00	0.00	0.01	0.21	1.60	0.00	0.00	0.01	0.21	1.60
	12H	0.00	0.00	0.00	0.10	1.54	0.00	0.00	0.00	0.10	1.54
12H	4H	0.00	0.00	0.10	0.37	1.74	0.00	0.00	0.10	0.37	1.74
	6H	0.00	0.00	0.01	0.21	1.60	0.00	0.00	0.01	0.21	1.60
	8H	0.00	0.00	0.00	0.10	1.54	0.00	0.00	0.00	0.10	1.54

END OF REPORT