

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245228

Luminaire Tested: PRLX-NIM-S-930-02L-U-NL

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1245228  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PrentaLux  
Catalog Number: PRLX-NIM-S-930-02L-U-NL  
Description: 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, NATURAL LINES SHADE TEXTURE  
LIGHT LEVEL 1  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 227.9 lumens  
Efficiency: N/A  
Efficacy: 36.2 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.4  
Luminous Opening: Rectangular w/ Sides (W: 0.58' x L: 0.58' x H: 0.87')  
CIE Type: Semi-Direct  
  
Input Watts (W): 6.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

TEST NUMBER: P1245228

CATALOG NUMBER: PRLX-NIM-S-930-02L-U-NL

### Luminous Intensity Polar Plot





TEST NUMBER: P1245228

CATALOG NUMBER: PRLX-NIM-S-930-02L-U-NL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	113	113	113	113	107	107	107	107	96	96	96		87	87	87		78	78	78	74
1	101	96	91	87	96	91	87	83	82	79	76		74	71	69		66	64	62	58
2	92	84	77	71	87	80	73	68	72	67	63		65	61	57		58	55	52	49
3	85	74	66	60	80	71	64	58	64	58	53		58	53	49		52	48	45	42
4	78	67	58	52	74	64	56	50	58	52	47		52	47	43		47	43	40	37
5	72	60	52	46	69	58	50	44	53	46	41		48	43	39		44	39	36	33
6	68	55	47	41	64	53	45	40	48	42	37		44	39	35		41	36	33	30
7	63	51	43	37	60	49	41	36	45	39	34		41	36	32		38	33	30	28
8	59	47	39	34	56	45	38	33	42	36	31		39	33	30		36	31	28	26
9	56	44	36	31	53	42	35	30	39	33	29		36	31	28		34	29	26	24
10	53	41	34	29	51	40	33	28	37	31	27		34	29	26		32	28	24	23

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	6074
5°	5995
10°	5270
15°	1280
20°	1067
25°	889
30°	703
35°	582
40°	497
45°	451
50°	408
55°	377
60°	355
65°	330
70°	314
75°	298
80°	270
85°	255

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 451 cd/sqm

TEST NUMBER: P1245228

CATALOG NUMBER: PRLX-NIM-S-930-02L-U-NL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	19.9	8.7
10°-20°	21.1	9.3
20°-30°	19.7	8.6
30°-40°	19.4	8.5
40°-50°	19.3	8.5
50°-60°	19.2	8.4
60°-70°	18.5	8.1
70°-80°	16.8	7.4
80°-90°	14.0	6.1
90°-100°	13.4	5.9
100°-110°	12.5	5.5
110°-120°	11.0	4.8
120°-130°	9.0	4.0
130°-140°	6.7	2.9
140°-150°	4.3	1.9
150°-160°	2.2	1.0
160°-170°	0.8	0.3
170°-180°	0.1	0.0
<hr/>		
0°-30°	60.7	26.6
0°-40°	80.0	35.1
0°-60°	118.5	52.0
0°-90°	167.9	73.7
90°-120°	36.9	16.2
90°-150°	57.0	25.0
90°-180°	60.0	26.3
0°-180°	227.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	192	
5°	213	20
15°	55	21
25°	43	20
35°	31	19
45°	25	19
55°	21	19
65°	18	18
75°	16	17
85°	13	11
90°	12	7
95°	12	10
105°	12	13
115°	11	11
125°	10	9
135°	9	7
145°	7	4
155°	5	2
165°	2	1
175°	0	0
180°	0	

TEST NUMBER: P1245228

CATALOG NUMBER: PRLX-NIM-S-930-02L-U-NL

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	192.0
2.5°	198.2
5°	213.4
7.5°	210.9
10°	207.2
12.5°	88.8
15°	54.7
17.5°	51.8
20°	48.9
22.5°	46.5
25°	43.2
27.5°	39.5
30°	35.8
32.5°	32.9
35°	30.8
37.5°	28.8
40°	27.1
42.5°	25.9
45°	25.1
47.5°	23.8
50°	23.0
52.5°	22.2
55°	21.4
57.5°	20.6
60°	20.1
62.5°	19.3
65°	18.5
67.5°	18.1
70°	17.3
72.5°	16.9
75°	16.0
77.5°	15.2
80°	14.0
82.5°	13.2
85°	12.7
87.5°	12.3
90°	12.3
92.5°	12.3
95°	12.3
97.5°	12.3
100°	11.9
102.5°	11.9
105°	11.9
107.5°	11.9
110°	11.5

TEST NUMBER: P1245228

CATALOG NUMBER: PRLX-NIM-S-930-02L-U-NL

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	11.5
115°	11.1
117.5°	10.7
120°	10.7
122.5°	10.3
125°	9.9
127.5°	9.9
130°	9.5
132.5°	9.0
135°	8.6
137.5°	8.2
140°	7.8
142.5°	7.4
145°	7.0
147.5°	6.2
150°	5.8
152.5°	5.3
155°	4.9
157.5°	4.1
160°	3.7
162.5°	3.3
165°	2.5
167.5°	2.1
170°	1.6
172.5°	0.8
175°	0.4
177.5°	0.0
180°	0.0



TEST NUMBER: P1245228

CATALOG NUMBER: PRLX-NIM-S-930-02L-U-NL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.2	6.3	5.9	7.1	7.9	5.2	6.3	5.9	7.1	7.9
	3H	7.5	8.5	8.2	9.3	10.2	7.5	8.5	8.2	9.3	10.2
	4H	8.5	9.5	9.3	10.3	11.2	8.5	9.5	9.3	10.3	11.2
	6H	9.5	10.4	10.3	11.2	12.2	9.5	10.4	10.3	11.2	12.2
	8H	9.9	10.8	10.7	11.6	12.6	9.9	10.8	10.7	11.6	12.6
	12H	10.4	11.2	11.1	12.0	13.0	10.4	11.2	11.1	12.0	13.0
4H	2H	5.8	6.7	6.5	7.5	8.4	5.8	6.7	6.5	7.5	8.4
	3H	8.3	9.1	9.1	9.9	10.9	8.3	9.1	9.1	9.9	10.9
	4H	9.5	10.3	10.3	11.1	12.1	9.5	10.3	10.3	11.1	12.1
	6H	10.6	11.3	11.4	12.1	13.1	10.6	11.3	11.4	12.1	13.1
	8H	11.1	11.8	11.9	12.6	13.6	11.1	11.8	11.9	12.6	13.6
	12H	11.7	12.2	12.5	13.1	14.1	11.7	12.2	12.5	13.1	14.1
8H	4H	9.9	10.5	10.7	11.4	12.4	9.9	10.5	10.7	11.4	12.4
	6H	11.2	11.7	12.0	12.6	13.6	11.2	11.7	12.0	12.6	13.6
	8H	11.8	12.3	12.7	13.2	14.2	11.8	12.3	12.7	13.2	14.2
	12H	12.5	12.9	13.3	13.8	14.9	12.5	12.9	13.3	13.8	14.9
12H	4H	10.0	10.5	10.8	11.4	12.4	10.0	10.5	10.8	11.4	12.4
	6H	11.3	11.8	12.2	12.7	13.7	11.3	11.8	12.2	12.7	13.7
	8H	12.0	12.5	12.9	13.3	14.4	12.0	12.5	12.9	13.3	14.4

(END OF REPORT)