

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245093

Luminaire Tested: PRLX-NIM-L-935-27L-U-NR

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245093
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2412-299-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-NIM-L-935-27L-U-NR
Description: 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, NATURAL RIBS SHADE TEXTURE
LIGHT LEVEL 8
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2796.1 lumens
Efficiency: N/A
Efficacy: 40.3 lumens/watt
Spacing Criteria (0/90/45): 0.19 / 0.19 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.58' x L: 0.58' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 69.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1245093

CATALOG NUMBER: PRLX-NIM-L-935-27L-U-NR

Luminous Intensity Polar Plot





TEST NUMBER: P1245093

CATALOG NUMBER: PRLX-NIM-L-935-27L-U-NR

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	56
1	95	89	83	78	87	82	77	73	70	66	62	58	55	53	48	45	43	38
2	85	76	68	61	78	70	63	57	59	54	49	49	45	42	40	37	34	30
3	77	66	57	50	71	61	53	47	52	45	40	43	38	34	35	31	28	24
4	71	58	49	42	65	54	46	40	46	39	34	38	33	29	31	27	24	20
5	65	52	43	36	60	48	40	34	41	35	30	34	29	25	28	24	21	18
6	60	47	38	32	55	44	36	30	37	31	26	31	26	22	26	22	19	16
7	56	43	34	28	51	40	32	27	34	28	23	29	24	20	24	20	17	15
8	52	39	31	25	48	36	29	24	32	25	21	27	22	18	23	19	16	13
9	49	36	28	23	45	34	27	22	29	23	19	25	20	17	21	17	15	12
10	46	33	26	21	43	31	25	20	27	22	18	24	19	16	20	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	122392
5°	55420
10°	13196
15°	5232
20°	3316
25°	2649
30°	2272
35°	2108
40°	2113
45°	2006
50°	2045
55°	2096
60°	2159
65°	2124
70°	2217
75°	2215
80°	2230
85°	2262

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 90°
 Luminance: 2314 cd/sqm



TEST NUMBER: P1245093

CATALOG NUMBER: PRLX-NIM-L-935-27L-U-NR

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.0	5.9
10°-20°	93.2	3.3
20°-30°	90.6	3.2
30°-40°	116.2	4.2
40°-50°	152.5	5.5
50°-60°	191.6	6.9
60°-70°	228.1	8.2
70°-80°	254.2	9.1
80°-90°	262.2	9.4
90°-100°	262.2	9.4
100°-110°	254.2	9.1
110°-120°	226.7	8.1
120°-130°	186.2	6.7
130°-140°	142.1	5.1
140°-150°	95.7	3.4
150°-160°	52.5	1.9
160°-170°	21.1	0.8
170°-180°	2.6	0.1
0°-30°	347.8	12.4
0°-40°	464.1	16.6
0°-60°	808.2	28.9
0°-90°	1552.7	55.5
90°-120°	743.1	26.6
90°-150°	1167.1	41.7
90°-180°	1243.0	44.5
0°-180°	2796.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3869	
5°	2247	164
15°	300	93
25°	192	91
35°	180	116
45°	192	153
55°	216	192
65°	228	228
75°	240	254
85°	240	196
90°	240	132
95°	240	196
105°	240	254
115°	228	227
125°	204	186
135°	180	142
145°	156	96
155°	108	53
165°	72	21
175°	12	3
180°	0	

TEST NUMBER: P1245093

CATALOG NUMBER: PRLX-NIM-L-935-27L-U-NR

CANDELA DISTRIBUTION (FULL):

0°	
0°	3868.7
2.5°	4289.3
5°	2246.8
7.5°	949.2
10°	648.8
12.5°	408.5
15°	300.4
17.5°	252.3
20°	216.3
22.5°	204.3
25°	192.2
27.5°	192.2
30°	180.2
32.5°	180.2
35°	180.2
37.5°	192.2
40°	192.2
42.5°	192.2
45°	192.2
47.5°	204.3
50°	204.3
52.5°	204.3
55°	216.3
57.5°	216.3
60°	228.3
62.5°	228.3
65°	228.3
67.5°	228.3
70°	240.3
72.5°	240.3
75°	240.3
77.5°	240.3
80°	240.3
82.5°	240.3
85°	240.3
87.5°	240.3
90°	240.3
92.5°	240.3
95°	240.3
97.5°	240.3
100°	240.3
102.5°	240.3
105°	240.3
107.5°	240.3
110°	240.3

TEST NUMBER: P1245093

CATALOG NUMBER: PRLX-NIM-L-935-27L-U-NR

CANDELA DISTRIBUTION (continued):

	0°
112.5°	228.3
115°	228.3
117.5°	228.3
120°	216.3
122.5°	216.3
125°	204.3
127.5°	204.3
130°	192.2
132.5°	192.2
135°	180.2
137.5°	180.2
140°	168.2
142.5°	156.2
145°	156.2
147.5°	144.2
150°	132.2
152.5°	120.1
155°	108.1
157.5°	108.1
160°	96.1
162.5°	84.1
165°	72.1
167.5°	60.1
170°	48.1
172.5°	36.0
175°	12.0
177.5°	0.0
180°	0.0



TEST NUMBER: P1245093

CATALOG NUMBER: PRLX-NIM-L-935-27L-U-NR

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.0	11.1	10.9	12.0	13.2	10.0	11.1	10.9	12.0	13.2
	3H	13.1	14.0	14.0	15.0	16.2	13.1	14.0	14.0	15.0	16.2
	4H	14.6	15.5	15.5	16.4	17.6	14.6	15.5	15.5	16.4	17.6
	6H	16.0	16.9	16.9	17.8	19.0	16.0	16.9	16.9	17.8	19.0
	8H	16.7	17.5	17.6	18.5	19.7	16.7	17.5	17.6	18.5	19.7
	12H	17.4	18.1	18.3	19.1	20.3	17.4	18.1	18.3	19.1	20.3
4H	2H	10.8	11.7	11.7	12.7	13.9	10.8	11.7	11.7	12.7	13.9
	3H	14.1	14.9	15.0	15.8	17.1	14.1	14.9	15.0	15.8	17.1
	4H	15.7	16.4	16.6	17.4	18.6	15.7	16.4	16.6	17.4	18.6
	6H	17.3	18.0	18.2	18.9	20.2	17.3	18.0	18.2	18.9	20.2
	8H	18.1	18.7	19.0	19.7	20.9	18.1	18.7	19.0	19.7	20.9
	12H	18.8	19.4	19.8	20.4	21.7	18.8	19.4	19.8	20.4	21.7
8H	4H	16.2	16.8	17.2	17.8	19.1	16.2	16.8	17.2	17.8	19.1
	6H	18.0	18.6	19.0	19.6	20.8	18.0	18.6	19.0	19.6	20.8
	8H	18.9	19.4	19.9	20.4	21.7	18.9	19.4	19.9	20.4	21.7
	12H	19.9	20.3	20.9	21.3	22.6	19.9	20.3	20.9	21.3	22.6
12H	4H	16.3	16.9	17.3	17.9	19.2	16.3	16.9	17.3	17.9	19.2
	6H	18.2	18.7	19.2	19.7	21.0	18.2	18.7	19.2	19.7	21.0
	8H	19.2	19.6	20.2	20.6	21.9	19.2	19.6	20.2	20.6	21.9

(END OF REPORT)