

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P981024

Luminaire Tested: PRLX-CYL3-10-935-10L-WD-U-S-X-X-WHTE

Issue Date: 4/11/2025

Test Information

Test Method: LM-79-2019
Report Number: P981024
TEST IS SCALED FROM (FO44195.PSO)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/11/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-CYL3-10-935-10L-WD-U-S-X-X-WHTE
Description: PrentaLux 3-INCH CYLINDER, WIDE FLOOD OPTIC
1000 LUMENS
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 959.2 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 1.07 / 1.07 / 0.89
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P981024

CATALOG NUMBER: PRLX-CYL3-10-935-10L-WD-U-S-X-X-WHTE

Luminous Intensity Polar Plot



TEST NUMBER: P981024

CATALOG NUMBER: PRLX-CYL3-10-935-10L-WD-U-S-X-X-WHTE

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		94
2	108	104	100	97	106	102	99	96	99	96	94		96	94	92		88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		82
4	98	91	86	82	97	90	85	82	88	84	81		86	83	80		77
5	94	86	80	76	92	85	80	76	83	79	75		82	78	75		73
6	89	81	75	71	88	80	75	71	79	74	70		77	73	70		68
7	85	76	71	67	84	76	70	66	74	70	66		73	69	66		64
8	81	72	67	63	80	72	66	62	71	66	62		70	65	62		60
9	78	68	63	59	77	68	63	59	67	62	59		66	62	58		57
10	74	65	59	56	73	64	59	56	64	59	55		63	58	55		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	212176
5°	222716
10°	235689
15°	243134
20°	236271
25°	208222
30°	139616
35°	59160
40°	19637
45°	5024
50°	3173
55°	2561
60°	1974
65°	1453
70°	1154
75°	1186
80°	1642
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5024 cd/sqm

TEST NUMBER: P981024

CATALOG NUMBER: PRLX-CYL3-10-935-10L-WD-U-S-X-X-WHTE

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.6	10.2
10°-20°	299.1	31.2
20°-30°	380.2	39.6
30°-40°	152.1	15.9
40°-50°	19.0	2.0
50°-60°	6.1	0.6
60°-70°	2.9	0.3
70°-80°	1.5	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	776.9	81.0
0°-40°	929.0	96.8
0°-60°	954.1	99.5
0°-90°	959.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	959.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	968	
5°	1012	98
15°	1071	299
25°	861	380
35°	221	152
45°	16	19
55°	7	6
65°	3	3
75°	1	2
85°	1	1
90°	0	

TEST NUMBER: P981024

CATALOG NUMBER: PRLX-CYL3-10-935-10L-WD-U-S-X-X-WHTE

CANDELA DISTRIBUTION (FULL):

0°	
0°	967.6
1°	974.8
2°	992.1
3°	1004.9
4°	1009.5
5°	1011.8
6°	1013.6
7°	1016.8
8°	1025.7
9°	1041.0
10°	1058.5
11°	1071.0
12°	1073.8
13°	1071.0
14°	1070.4
15°	1071.0
16°	1066.5
17°	1054.2
18°	1037.7
19°	1027.3
20°	1012.5
21°	990.7
22°	963.2
23°	929.7
24°	895.2
25°	860.6
26°	819.5
27°	768.5
28°	708.2
29°	632.6
30°	551.4
31°	471.4
32°	399.7
33°	336.9
34°	278.4
35°	221.0
36°	171.9
37°	135.3
38°	109.1
39°	87.8
40°	68.6
41°	54.0
42°	42.8
43°	32.6
44°	22.9

TEST NUMBER: P981024

CATALOG NUMBER: PRLX-CYL3-10-935-10L-WD-U-S-X-X-WHTE

CANDELA DISTRIBUTION (continued):

	0°
45°	16.2
46°	13.0
47°	11.8
48°	10.8
49°	10.0
50°	9.3
51°	8.6
52°	7.9
53°	7.3
54°	6.8
55°	6.7
56°	6.6
57°	6.4
58°	6.1
59°	5.5
60°	4.5
61°	3.6
62°	3.3
63°	3.3
64°	3.1
65°	2.8
66°	2.7
67°	2.7
68°	2.5
69°	2.2
70°	1.8
71°	1.6
72°	1.6
73°	1.5
74°	1.5
75°	1.4
76°	1.4
77°	1.4
78°	1.4
79°	1.3
80°	1.3
81°	1.2
82°	1.1
83°	1.0
84°	0.9
85°	0.7
86°	0.4
87°	0.1
88°	0.0
89°	0.0

TEST NUMBER: P981024

CATALOG NUMBER: PRLX-CYL3-10-935-10L-WD-U-S-X-X-WHTE

CANDELA DISTRIBUTION (continued):



TEST NUMBER: P981024

CATALOG NUMBER: PRLX-CYL3-10-935-10L-WD-U-S-X-X-WHTE

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.08	6.00	5.44	6.31	6.62	5.08	6.00	5.44	6.31	6.62
	3H	5.70	6.51	6.08	6.84	7.21	5.70	6.51	6.08	6.84	7.21
	4H	5.92	6.67	6.33	7.03	7.42	5.92	6.67	6.33	7.03	7.42
	6H	6.31	6.99	6.73	7.37	7.77	6.31	6.99	6.73	7.37	7.77
	8H	6.52	7.16	6.96	7.55	7.96	6.52	7.16	6.96	7.55	7.96
	12H	6.63	7.24	7.07	7.62	8.06	6.63	7.24	7.07	7.62	8.06
4H	2H	5.09	5.84	5.50	6.19	6.58	5.09	5.84	5.50	6.19	6.58
	3H	5.82	6.43	6.24	6.84	7.25	5.82	6.43	6.24	6.84	7.25
	4H	6.17	6.72	6.61	7.14	7.59	6.17	6.72	6.61	7.14	7.59
	6H	6.79	7.25	7.26	7.71	8.18	6.79	7.25	7.26	7.71	8.18
	8H	7.11	7.54	7.59	7.99	8.47	7.11	7.54	7.59	7.99	8.47
	12H	7.33	7.70	7.83	8.19	8.67	7.33	7.70	7.83	8.19	8.67
8H	4H	6.27	6.70	6.75	7.15	7.63	6.27	6.70	6.75	7.15	7.63
	6H	7.09	7.43	7.61	7.94	8.42	7.09	7.43	7.61	7.94	8.42
	8H	7.55	7.85	8.09	8.37	8.87	7.55	7.85	8.09	8.37	8.87
	12H	7.93	8.19	8.46	8.69	9.27	7.93	8.19	8.46	8.69	9.27
12H	4H	6.28	6.65	6.77	7.14	7.61	6.28	6.65	6.77	7.14	7.61
	6H	7.17	7.46	7.70	7.99	8.49	7.17	7.46	7.70	7.99	8.49
	8H	7.70	7.96	8.23	8.46	9.04	7.70	7.96	8.23	8.46	9.04

END OF REPORT