

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245253

Luminaire Tested: PRLX-NIM-S-935-05L-U-NR

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245253
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-NIM-S-935-05L-U-NR
Description: 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, NATURAL RIBS SHADE TEXTURE
LIGHT LEVEL 2
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 535.0 lumens
Efficiency: N/A
Efficacy: 48.2 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.4
Luminous Opening: Rectangular w/ Sides (W: 0.58' x L: 0.58' x H: 0.87')
CIE Type: Semi-Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1245253
CATALOG NUMBER: PRLX-NIM-S-935-05L-U-NR

Luminous Intensity Polar Plot





TEST NUMBER: P1245253

CATALOG NUMBER: PRLX-NIM-S-935-05L-U-NR

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	113	113	113	113	107	107	107	107	96	96	96		87	87	87		78	78	78	74
1	101	96	91	87	96	91	87	83	82	79	76		74	71	69		66	64	62	58
2	92	84	77	71	87	80	73	68	72	67	63		65	61	57		58	55	52	49
3	85	74	66	60	80	71	64	58	64	58	53		58	53	49		52	48	45	42
4	78	67	58	52	74	64	56	50	58	52	47		52	47	43		47	43	40	37
5	72	60	52	46	69	58	50	44	53	46	41		48	43	39		44	39	36	33
6	68	55	47	41	64	53	45	40	48	42	37		44	39	35		41	36	33	30
7	63	51	43	37	60	49	41	36	45	39	34		41	36	32		38	33	30	28
8	59	47	39	34	56	45	38	33	42	36	31		39	33	30		36	31	28	26
9	56	44	36	31	53	42	35	30	39	33	29		36	31	27		34	29	26	24
10	53	41	34	29	51	40	33	28	37	31	27		34	29	26		32	28	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	14252
5°	14066
10°	12367
15°	3002
20°	2505
25°	2086
30°	1647
35°	1368
40°	1169
45°	1056
50°	957
55°	885
60°	835
65°	774
70°	735
75°	700
80°	632
85°	601

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1056 cd/sqm

TEST NUMBER: P1245253

CATALOG NUMBER: PRLX-NIM-S-935-05L-U-NR

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.7	8.7
10°-20°	49.5	9.3
20°-30°	46.1	8.6
30°-40°	45.4	8.5
40°-50°	45.3	8.5
50°-60°	45.1	8.4
60°-70°	43.4	8.1
70°-80°	39.5	7.4
80°-90°	32.9	6.1
90°-100°	31.4	5.9
100°-110°	29.5	5.5
110°-120°	25.9	4.8
120°-130°	21.1	4.0
130°-140°	15.7	2.9
140°-150°	10.1	1.9
150°-160°	5.3	1.0
160°-170°	1.8	0.3
170°-180°	0.2	0.0
0°-30°	142.4	26.6
0°-40°	187.8	35.1
0°-60°	278.2	52.0
0°-90°	393.9	73.6
90°-120°	86.8	16.2
90°-150°	133.8	25.0
90°-180°	141.0	26.4
0°-180°	535.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	450	
5°	501	47
15°	128	50
25°	101	46
35°	72	45
45°	59	45
55°	50	45
65°	43	43
75°	38	40
85°	30	25
90°	29	16
95°	29	23
105°	28	29
115°	26	26
125°	23	21
135°	20	16
145°	16	10
155°	12	5
165°	6	2
175°	1	0
180°	0	

TEST NUMBER: P1245253

CATALOG NUMBER: PRLX-NIM-S-935-05L-U-NR

CANDELA DISTRIBUTION (FULL):

0°	
0°	450.5
2.5°	465.0
5°	500.7
7.5°	494.9
10°	486.2
12.5°	208.4
15°	128.3
17.5°	121.6
20°	114.8
22.5°	109.0
25°	101.3
27.5°	92.6
30°	83.9
32.5°	77.2
35°	72.4
37.5°	67.5
40°	63.7
42.5°	60.8
45°	58.8
47.5°	56.0
50°	54.0
52.5°	52.1
55°	50.2
57.5°	48.2
60°	47.3
62.5°	45.3
65°	43.4
67.5°	42.4
70°	40.5
72.5°	39.6
75°	37.6
77.5°	35.7
80°	32.8
82.5°	30.9
85°	29.9
87.5°	28.9
90°	28.9
92.5°	28.9
95°	28.9
97.5°	28.9
100°	28.0
102.5°	28.0
105°	28.0
107.5°	28.0
110°	27.0



TEST NUMBER: P1245253

CATALOG NUMBER: PRLX-NIM-S-935-05L-U-NR

CANDELA DISTRIBUTION (continued):

	0°
112.5°	27.0
115°	26.0
117.5°	25.1
120°	25.1
122.5°	24.1
125°	23.2
127.5°	23.2
130°	22.2
132.5°	21.2
135°	20.3
137.5°	19.3
140°	18.3
142.5°	17.4
145°	16.4
147.5°	14.5
150°	13.5
152.5°	12.5
155°	11.6
157.5°	9.6
160°	8.7
162.5°	7.7
165°	5.8
167.5°	4.8
170°	3.9
172.5°	1.9
175°	1.0
177.5°	0.0
180°	0.0



TEST NUMBER: P1245253

CATALOG NUMBER: PRLX-NIM-S-935-05L-U-NR

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.1	9.3	8.8	10.0	10.9	8.1	9.3	8.8	10.0	10.9
	3H	10.4	11.5	11.2	12.2	13.1	10.4	11.5	11.2	12.2	13.1
	4H	11.5	12.5	12.2	13.2	14.2	11.5	12.5	12.2	13.2	14.2
	6H	12.5	13.4	13.2	14.2	15.1	12.5	13.4	13.2	14.2	15.1
	8H	12.9	13.8	13.7	14.6	15.5	12.9	13.8	13.7	14.6	15.5
	12H	13.3	14.2	14.1	14.9	15.9	13.3	14.2	14.1	14.9	15.9
4H	2H	8.7	9.7	9.5	10.5	11.4	8.7	9.7	9.5	10.5	11.4
	3H	11.2	12.1	12.0	12.9	13.8	11.2	12.1	12.0	12.9	13.8
	4H	12.5	13.2	13.2	14.0	15.0	12.5	13.2	13.2	14.0	15.0
	6H	13.6	14.3	14.4	15.1	16.1	13.6	14.3	14.4	15.1	16.1
	8H	14.1	14.8	14.9	15.6	16.6	14.1	14.8	14.9	15.6	16.6
	12H	14.6	15.2	15.4	16.0	17.0	14.6	15.2	15.4	16.0	17.0
8H	4H	12.8	13.5	13.6	14.3	15.3	12.8	13.5	13.6	14.3	15.3
	6H	14.2	14.7	15.0	15.6	16.6	14.2	14.7	15.0	15.6	16.6
	8H	14.8	15.3	15.6	16.1	17.1	14.8	15.3	15.6	16.1	17.1
	12H	15.5	15.9	16.3	16.8	17.8	15.5	15.9	16.3	16.8	17.8
12H	4H	12.9	13.5	13.7	14.3	15.3	12.9	13.5	13.7	14.3	15.3
	6H	14.3	14.8	15.1	15.6	16.7	14.3	14.8	15.1	15.6	16.7
	8H	15.0	15.4	15.8	16.3	17.3	15.0	15.4	15.8	16.3	17.3

(END OF REPORT)