

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P981044

Luminaire Tested: PRLX-CYL3-10-940-23L-WD-U-S-X-X-WHTE

Issue Date: 4/11/2025

Test Information

Test Method: LM-79-2019
Report Number: P981044
TEST IS SCALED FROM (FO44195.PSO)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/11/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-CYL3-10-940-23L-WD-U-S-X-X-WHTE
Description: PrentaLux 3-INCH CYLINDER, WIDE FLOOD OPTIC
2300 LUMENS
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2383.8 lumens
Efficiency: N/A
Efficacy: 105.9 lumens/watt
Spacing Criteria (0/90/45): 1.07 / 1.07 / 0.89
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 22.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P981044

CATALOG NUMBER: PRLX-CYL3-10-940-23L-WD-U-S-X-X-WHTE

Luminous Intensity Polar Plot





TEST NUMBER: P981044

CATALOG NUMBER: PRLX-CYL3-10-940-23L-WD-U-S-X-X-WHTE

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20				
RC	80					70					50					30					10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10		
RCR																									
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100							
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94							
2	108	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88							
3	103	97	93	89	101	96	92	88	93	90	87	91	88	85	89	86	84	82							
4	98	91	86	82	97	90	85	82	88	84	81	86	83	80	84	81	79	77							
5	94	86	80	76	92	85	80	76	83	79	75	82	78	75	80	77	74	73							
6	89	81	75	71	88	80	75	71	79	74	70	77	73	70	76	72	70	68							
7	85	76	71	67	84	76	70	66	74	70	66	73	69	66	72	68	65	64							
8	81	72	67	63	80	72	66	62	71	66	62	70	65	62	69	65	62	60							
9	78	68	63	59	77	68	63	59	67	62	59	66	62	58	65	61	58	57							
10	74	65	59	56	73	64	59	56	64	59	55	63	58	55	62	58	55	54							

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	527282
5°	553465
10°	585716
15°	604181
20°	587164
25°	517457
30°	346939
35°	146990
40°	48777
45°	12466
50°	7880
55°	6346
60°	4868
65°	3632
70°	2885
75°	3050
80°	3915
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12466 cd/sqm

TEST NUMBER: P981044

CATALOG NUMBER: PRLX-CYL3-10-940-23L-WD-U-S-X-X-WHTE

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	242.5	10.2
10°-20°	743.2	31.2
20°-30°	944.9	39.6
30°-40°	378.0	15.9
40°-50°	47.2	2.0
50°-60°	15.2	0.6
60°-70°	7.2	0.3
70°-80°	3.9	0.2
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1930.6	81.0
0°-40°	2308.6	96.8
0°-60°	2371.0	99.5
0°-90°	2383.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2383.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2405	
5°	2514	242
15°	2661	743
25°	2139	945
35°	549	378
45°	40	47
55°	17	15
65°	7	7
75°	4	4
85°	2	2
90°	0	

TEST NUMBER: P981044

CATALOG NUMBER: PRLX-CYL3-10-940-23L-WD-U-S-X-X-WHTE

CANDELA DISTRIBUTION (FULL):

0°	
0°	2404.6
1°	2422.3
2°	2465.5
3°	2497.3
4°	2508.7
5°	2514.4
6°	2518.9
7°	2526.9
8°	2549.0
9°	2587.0
10°	2630.5
11°	2661.6
12°	2668.4
13°	2661.6
14°	2660.0
15°	2661.4
16°	2650.3
17°	2619.7
18°	2578.7
19°	2553.0
20°	2516.2
21°	2461.9
22°	2393.7
23°	2310.2
24°	2224.6
25°	2138.7
26°	2036.5
27°	1909.8
28°	1759.9
29°	1572.2
30°	1370.2
31°	1171.5
32°	993.3
33°	837.3
34°	692.0
35°	549.1
36°	427.1
37°	336.3
38°	271.2
39°	218.3
40°	170.4
41°	134.1
42°	106.3
43°	81.1
44°	56.9

TEST NUMBER: P981044

CATALOG NUMBER: PRLX-CYL3-10-940-23L-WD-U-S-X-X-WHTE

CANDELA DISTRIBUTION (continued):

	0°
45°	40.2
46°	32.4
47°	29.3
48°	26.9
49°	24.9
50°	23.1
51°	21.3
52°	19.5
53°	18.1
54°	17.0
55°	16.6
56°	16.5
57°	16.0
58°	15.1
59°	13.7
60°	11.1
61°	9.0
62°	8.2
63°	8.1
64°	7.7
65°	7.0
66°	6.8
67°	6.6
68°	6.3
69°	5.4
70°	4.5
71°	4.0
72°	3.9
73°	3.7
74°	3.7
75°	3.6
76°	3.6
77°	3.6
78°	3.5
79°	3.3
80°	3.1
81°	3.0
82°	2.8
83°	2.6
84°	2.2
85°	1.7
86°	1.0
87°	0.3
88°	0.1
89°	0.1

TEST NUMBER: P981044

CATALOG NUMBER: PRLX-CYL3-10-940-23L-WD-U-S-X-X-WHTE

CANDELA DISTRIBUTION (continued):

90° | $\overset{0^\circ}{\text{---}} \underset{0.0}{\text{---}}$

TEST NUMBER: P981044

CATALOG NUMBER: PRLX-CYL3-10-940-23L-WD-U-S-X-X-WHTE

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.23	9.16	8.60	9.47	9.78	8.23	9.16	8.60	9.47	9.78
	3H	8.86	9.67	9.24	10.00	10.37	8.86	9.67	9.24	10.00	10.37
	4H	9.08	9.83	9.49	10.19	10.58	9.08	9.83	9.49	10.19	10.58
	6H	9.47	10.15	9.89	10.53	10.93	9.47	10.15	9.89	10.53	10.93
	8H	9.69	10.33	10.13	10.72	11.13	9.69	10.33	10.13	10.72	11.13
	12H	9.80	10.41	10.24	10.80	11.23	9.80	10.41	10.24	10.80	11.23
4H	2H	8.25	9.00	8.66	9.35	9.75	8.25	9.00	8.66	9.35	9.75
	3H	8.99	9.60	9.40	10.01	10.41	8.99	9.60	9.40	10.01	10.41
	4H	9.35	9.89	9.79	10.32	10.77	9.35	9.89	9.79	10.32	10.77
	6H	9.96	10.42	10.43	10.87	11.35	9.96	10.42	10.43	10.87	11.35
	8H	10.29	10.72	10.77	11.17	11.65	10.29	10.72	10.77	11.17	11.65
	12H	10.51	10.88	11.01	11.37	11.85	10.51	10.88	11.01	11.37	11.85
8H	4H	9.45	9.88	9.93	10.33	10.81	9.45	9.88	9.93	10.33	10.81
	6H	10.27	10.60	10.78	11.11	11.59	10.27	10.60	10.78	11.11	11.59
	8H	10.75	11.04	11.28	11.57	12.07	10.75	11.04	11.28	11.57	12.07
	12H	11.12	11.38	11.65	11.88	12.46	11.12	11.38	11.65	11.88	12.46
12H	4H	9.46	9.83	9.95	10.32	10.80	9.46	9.83	9.95	10.32	10.80
	6H	10.34	10.64	10.88	11.16	11.66	10.34	10.64	10.88	11.16	11.66
	8H	10.90	11.16	11.43	11.66	12.24	10.90	11.16	11.43	11.66	12.24

END OF REPORT