

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979419

Luminaire Tested: PRLX-CYL6-930-74L-WD-U-S-X-X-WHTE

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2019
Report Number: P979419
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-CYL6-930-74L-WD-U-S-X-X-WHTE
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, WHITE TRIM WITH WIDE FLOOD OPTIC
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6978.9 lumens
Efficiency: N/A
Efficacy: 113.5 lumens/watt
Spacing Criteria (0/90/45): 1.05 / 1.05 / 0.91
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 61.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P979419

CATALOG NUMBER: PRLX-CYL6-930-74L-WD-U-S-X-X-WHTE

Luminous Intensity Polar Plot



TEST NUMBER: P979419

CATALOG NUMBER: PRLX-CYL6-930-74L-WD-U-S-X-X-WHTE

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	98		98
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88
4	98	91	86	82	96	90	85	81	88	83	80		86	82	79		84
5	93	85	80	76	92	84	79	75	83	78	75		81	77	74		79
6	89	80	75	70	87	80	74	70	78	73	70		77	72	69		75
7	85	76	70	66	83	75	70	66	74	69	65		73	68	65		71
8	81	71	66	62	79	71	65	62	70	65	61		69	64	61		68
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	73	64	58	55	72	64	58	54	63	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	75829
5°	75171
10°	73399
15°	73739
20°	72687
25°	70286
30°	53173
35°	24835
40°	4686
45°	1985
50°	1039
55°	683
60°	461
65°	272
70°	336
75°	354
80°	400
85°	531

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1985 cd/sqm

TEST NUMBER: P979419

CATALOG NUMBER: PRLX-CYL6-930-74L-WD-U-S-X-X-WHTE

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	700.5	10.0
10°-20°	1987.1	28.5
20°-30°	2775.0	39.8
30°-40°	1330.8	19.1
40°-50°	122.7	1.8
50°-60°	35.3	0.5
60°-70°	13.8	0.2
70°-80°	9.6	0.1
80°-90°	4.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5462.6	78.3
0°-40°	6793.4	97.3
0°-60°	6951.4	99.6
0°-90°	6978.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6978.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7531	
5°	7437	700
15°	7074	1987
25°	6326	2775
35°	2020	1331
45°	139	123
55°	39	35
65°	11	14
75°	9	10
85°	5	4
90°	0	

TEST NUMBER: P979419

CATALOG NUMBER: PRLX-CYL6-930-74L-WD-U-S-X-X-WHTE

CANDELA DISTRIBUTION (FULL):

	0°
0°	7530.9
2.5°	7512.6
5°	7437.2
7.5°	7290.9
10°	7178.9
12.5°	7169.8
15°	7073.8
17.5°	6906.9
20°	6783.5
22.5°	6712.7
25°	6326.4
27.5°	5528.8
30°	4573.4
32.5°	3348.3
35°	2020.4
37.5°	985.1
40°	356.5
42.5°	201.1
45°	139.4
47.5°	96.0
50°	66.3
52.5°	48.0
55°	38.9
57.5°	27.4
60°	22.9
62.5°	16.0
65°	11.4
67.5°	11.4
70°	11.4
72.5°	9.1
75°	9.1
77.5°	9.1
80°	6.9
82.5°	4.6
85°	4.6
87.5°	2.3
90°	0.0

TEST NUMBER: P979419

CATALOG NUMBER: PRLX-CYL6-930-74L-WD-U-S-X-X-WHTE

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.05	0.00	0.00	0.00	0.00	0.05
	4H	0.00	0.00	0.00	0.13	0.52	0.00	0.00	0.00	0.13	0.52
	6H	0.00	0.40	0.14	0.78	1.17	0.00	0.40	0.14	0.78	1.17
	8H	0.00	0.55	0.35	0.94	1.35	0.00	0.55	0.35	0.94	1.35
	12H	0.14	0.75	0.58	1.13	1.56	0.14	0.75	0.58	1.13	1.56
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.25	0.00	0.00	0.00	0.00	0.25
	4H	0.00	0.09	0.00	0.51	0.96	0.00	0.09	0.00	0.51	0.96
	6H	0.48	0.94	0.95	1.39	1.86	0.48	0.94	0.95	1.39	1.86
	8H	0.74	1.16	1.21	1.61	2.09	0.74	1.16	1.21	1.61	2.09
	12H	1.07	1.43	1.56	1.92	2.40	1.07	1.43	1.56	1.92	2.40
8H	4H	0.00	0.26	0.31	0.71	1.19	0.00	0.26	0.31	0.71	1.19
	6H	0.93	1.26	1.44	1.77	2.25	0.93	1.26	1.44	1.77	2.25
	8H	1.28	1.58	1.82	2.10	2.60	1.28	1.58	1.82	2.10	2.60
	12H	1.78	2.04	2.31	2.54	3.12	1.78	2.04	2.31	2.54	3.12
12H	4H	0.00	0.22	0.35	0.71	1.19	0.00	0.22	0.35	0.71	1.19
	6H	0.99	1.29	1.53	1.81	2.31	0.99	1.29	1.53	1.81	2.31
	8H	1.42	1.67	1.95	2.17	2.76	1.42	1.67	1.95	2.17	2.76

END OF REPORT