

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979469

Luminaire Tested: PRLX-CYL6-935-43L-WD-U-S-X-X-WHTE

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2019
Report Number: P979469
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-CYL6-935-43L-WD-U-S-X-X-WHTE
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, WHITE TRIM WITH WIDE FLOOD OPTIC
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4190.6 lumens
Efficiency: N/A
Efficacy: 142.1 lumens/watt
Spacing Criteria (0/90/45): 1.05 / 1.05 / 0.91
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 29.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P979469

CATALOG NUMBER: PRLX-CYL6-935-43L-WD-U-S-X-X-WHTE

Luminous Intensity Polar Plot



TEST NUMBER: P979469

CATALOG NUMBER: PRLX-CYL6-935-43L-WD-U-S-X-X-WHTE

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	98		98
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88
4	98	91	86	82	96	90	85	81	88	83	80		86	82	79		84
5	93	85	80	76	92	84	79	75	83	78	75		81	77	74		79
6	89	80	75	70	87	80	74	70	78	73	70		77	72	69		75
7	85	76	70	66	83	75	70	66	74	69	65		73	68	65		71
8	81	71	66	62	79	71	65	62	70	65	61		69	64	61		68
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	73	64	58	55	72	64	58	54	63	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	45533
5°	45138
10°	44074
15°	44278
20°	43646
25°	42204
30°	31929
35°	14913
40°	2814
45°	1192
50°	623
55°	409
60°	276
65°	164
70°	203
75°	214
80°	238
85°	312

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1192 cd/sqm

TEST NUMBER: P979469

CATALOG NUMBER: PRLX-CYL6-935-43L-WD-U-S-X-X-WHTE

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	420.6	10.0
10°-20°	1193.2	28.5
20°-30°	1666.3	39.8
30°-40°	799.1	19.1
40°-50°	73.7	1.8
50°-60°	21.2	0.5
60°-70°	8.3	0.2
70°-80°	5.8	0.1
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3280.1	78.3
0°-40°	4079.2	97.3
0°-60°	4174.1	99.6
0°-90°	4190.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4190.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4522	
5°	4466	421
15°	4248	1193
25°	3799	1666
35°	1213	799
45°	84	74
55°	23	21
65°	7	8
75°	6	6
85°	3	2
90°	0	

TEST NUMBER: P979469

CATALOG NUMBER: PRLX-CYL6-935-43L-WD-U-S-X-X-WHTE

CANDELA DISTRIBUTION (FULL):

0°	
0°	4522.1
2.5°	4511.1
5°	4465.8
7.5°	4378.0
10°	4310.7
12.5°	4305.2
15°	4247.6
17.5°	4147.4
20°	4073.3
22.5°	4030.7
25°	3798.8
27.5°	3319.8
30°	2746.2
32.5°	2010.6
35°	1213.2
37.5°	591.5
40°	214.1
42.5°	120.8
45°	83.7
47.5°	57.6
50°	39.8
52.5°	28.8
55°	23.3
57.5°	16.5
60°	13.7
62.5°	9.6
65°	6.9
67.5°	6.9
70°	6.9
72.5°	5.5
75°	5.5
77.5°	5.5
80°	4.1
82.5°	2.7
85°	2.7
87.5°	1.4
90°	0.0

TEST NUMBER: P979469

CATALOG NUMBER: PRLX-CYL6-935-43L-WD-U-S-X-X-WHTE

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.12	0.00	0.00	0.00	0.00	0.12
	8H	0.00	0.00	0.00	0.00	0.33	0.00	0.00	0.00	0.00	0.33
	12H	0.00	0.00	0.00	0.14	0.62	0.00	0.00	0.00	0.14	0.62
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.01	0.50	0.00	0.00	0.00	0.01	0.50
	8H	0.00	0.00	0.05	0.33	0.83	0.00	0.00	0.05	0.33	0.83
	12H	0.00	0.24	0.51	0.74	1.32	0.00	0.24	0.51	0.74	1.32
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.05	0.55	0.00	0.00	0.00	0.05	0.55
	8H	0.00	0.00	0.17	0.40	0.98	0.00	0.00	0.17	0.40	0.98

END OF REPORT