

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245407

Luminaire Tested: PRLX-UNA-M-930-06L-U-NL

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245407
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UNA-M-930-06L-U-NL
Description: 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, NATURAL LINES SHADE TEXT LIGHT LEVEL 4
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 480.1 lumens
Efficiency: N/A
Efficacy: 22.5 lumens/watt
Spacing Criteria (0/90/45): 0.21 / 0.21 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.46' x L: 0.46' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1245407

CATALOG NUMBER: PRLX-UNA-M-930-06L-U-NL

Luminous Intensity Polar Plot



TEST NUMBER: P1245407

CATALOG NUMBER: PRLX-UNA-M-930-06L-U-NL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20						20
RC	80					70					50					30						10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10	
RCR																						
0	108	108	108	108		101	101	101	101		86	86	86		73	73	73		61	61	61	
1	95	90	84	79		88	83	78	74		70	67	64		59	56	54		48	46	45	
2	86	77	70	63		79	71	65	59		61	56	51		51	47	43		42	39	36	
3	78	68	59	53		72	63	55	49		53	48	43		45	40	36		37	33	30	
4	72	60	51	45		66	56	48	42		48	42	37		40	35	32		33	30	27	
5	67	54	45	39		61	50	43	37		43	37	32		37	32	28		31	27	24	
6	62	49	41	34		57	46	38	33		40	33	29		34	29	25		28	25	22	
7	58	45	37	31		53	42	35	29		37	31	26		31	27	23		27	23	20	
8	54	41	34	28		50	39	32	27		34	28	24		29	25	21		25	21	19	
9	51	38	31	26		47	36	29	25		32	26	22		28	23	20		24	20	17	
10	48	36	29	24		45	34	27	23		30	24	21		26	22	19		23	19	17	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	45887
5°	23223
10°	4460
15°	1496
20°	895
25°	682
30°	563
35°	506
40°	463
45°	445
50°	433
55°	424
60°	428
65°	426
70°	435
75°	447
80°	456
85°	467

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 90°
Luminance: 484 cd/sqm

TEST NUMBER: P1245407

CATALOG NUMBER: PRLX-UNA-M-930-06L-U-NL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.7	8.3
10°-20°	19.1	4.0
20°-30°	16.5	3.4
30°-40°	19.9	4.1
40°-50°	24.5	5.1
50°-60°	29.8	6.2
60°-70°	34.8	7.3
70°-80°	39.5	8.2
80°-90°	42.3	8.8
90°-100°	43.5	9.1
100°-110°	42.3	8.8
110°-120°	38.5	8.0
120°-130°	32.4	6.7
130°-140°	25.0	5.2
140°-150°	17.3	3.6
150°-160°	10.0	2.1
160°-170°	4.3	0.9
170°-180°	0.6	0.1
0°-30°	75.4	15.7
0°-40°	95.2	19.8
0°-60°	149.6	31.2
0°-90°	266.2	55.5
90°-120°	124.3	25.9
90°-150°	199.0	41.4
90°-180°	214.0	44.6
0°-180°	480.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	895	
5°	617	40
15°	60	19
25°	36	17
35°	32	20
45°	32	25
55°	33	30
65°	35	35
75°	38	39
85°	39	32
90°	40	22
95°	40	33
105°	40	42
115°	39	38
125°	36	32
135°	32	25
145°	27	17
155°	22	10
165°	15	4
175°	4	1
180°	1	

TEST NUMBER: P1245407

CATALOG NUMBER: PRLX-UNA-M-930-06L-U-NL

CANDELA DISTRIBUTION (FULL):

0°	
0°	895.4
2.5°	964.7
5°	616.6
7.5°	215.1
10°	148.9
12.5°	85.3
15°	59.8
17.5°	48.4
20°	41.4
22.5°	37.5
25°	35.6
27.5°	33.7
30°	32.5
32.5°	31.8
35°	31.8
37.5°	31.2
40°	31.2
42.5°	31.2
45°	31.8
47.5°	31.8
50°	32.5
52.5°	32.5
55°	33.1
57.5°	33.7
60°	34.4
62.5°	34.4
65°	35.0
67.5°	35.6
70°	36.3
72.5°	36.9
75°	37.5
77.5°	37.5
80°	38.2
82.5°	38.8
85°	38.8
87.5°	38.8
90°	39.5
92.5°	39.5
95°	40.1
97.5°	40.1
100°	40.1
102.5°	40.1
105°	40.1
107.5°	40.1
110°	39.5

TEST NUMBER: P1245407

CATALOG NUMBER: PRLX-UNA-M-930-06L-U-NL

CANDELA DISTRIBUTION (continued):

	0°
112.5°	39.5
115°	38.8
117.5°	38.2
120°	37.5
122.5°	36.9
125°	36.3
127.5°	35.0
130°	34.4
132.5°	33.1
135°	32.5
137.5°	31.2
140°	29.9
142.5°	28.6
145°	27.4
147.5°	26.1
150°	24.8
152.5°	22.9
155°	21.6
157.5°	19.7
160°	18.5
162.5°	16.5
165°	14.6
167.5°	12.7
170°	10.8
172.5°	7.6
175°	4.5
177.5°	1.9
180°	0.6

TEST NUMBER: P1245407

CATALOG NUMBER: PRLX-UNA-M-930-06L-U-NL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.2	5.2	5.1	6.1	7.3	4.2	5.2	5.1	6.1	7.3
	3H	7.2	8.1	8.1	9.0	10.2	7.2	8.1	8.1	9.0	10.2
	4H	8.7	9.5	9.6	10.5	11.7	8.7	9.5	9.6	10.5	11.7
	6H	10.1	11.0	11.1	11.9	13.1	10.1	11.0	11.1	11.9	13.1
	8H	10.9	11.6	11.8	12.6	13.8	10.9	11.6	11.8	12.6	13.8
	12H	11.6	12.3	12.5	13.3	14.5	11.6	12.3	12.5	13.3	14.5
4H	2H	4.9	5.8	5.9	6.7	8.0	4.9	5.8	5.9	6.7	8.0
	3H	8.1	8.9	9.1	9.9	11.1	8.1	8.9	9.1	9.9	11.1
	4H	9.8	10.5	10.7	11.4	12.7	9.8	10.5	10.7	11.4	12.7
	6H	11.4	12.0	12.4	13.0	14.3	11.4	12.0	12.4	13.0	14.3
	8H	12.2	12.8	13.2	13.8	15.1	12.2	12.8	13.2	13.8	15.1
	12H	13.0	13.6	14.0	14.6	15.8	13.0	13.6	14.0	14.6	15.8
8H	4H	10.3	10.9	11.2	11.9	13.1	10.3	10.9	11.2	11.9	13.1
	6H	12.1	12.7	13.1	13.7	14.9	12.1	12.7	13.1	13.7	14.9
	8H	13.1	13.6	14.1	14.6	15.9	13.1	13.6	14.1	14.6	15.9
	12H	14.1	14.5	15.1	15.5	16.8	14.1	14.5	15.1	15.5	16.8
12H	4H	10.4	11.0	11.4	12.0	13.2	10.4	11.0	11.4	12.0	13.2
	6H	12.3	12.8	13.3	13.8	15.1	12.3	12.8	13.3	13.8	15.1
	8H	13.4	13.8	14.4	14.8	16.1	13.4	13.8	14.4	14.8	16.1

(END OF REPORT)