

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245409

Luminaire Tested: PRLX-UNA-M-930-06L-U-PS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245409
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UNA-M-930-06L-U-PS
Description: 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, PINSTRIPE SHADE TEXTURE LIGHT LEVEL 4
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 541.0 lumens
Efficiency: N/A
Efficacy: 25.4 lumens/watt
Spacing Criteria (0/90/45): 0.21 / 0.21 / 0.18
Luminous Opening: Rectangular w/ Sides (W: 0.46' x L: 0.46' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1245409

CATALOG NUMBER: PRLX-UNA-M-930-06L-U-PS

Luminous Intensity Polar Plot





TEST NUMBER: P1245409

CATALOG NUMBER: PRLX-UNA-M-930-06L-U-PS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	95	90	84	79	88	83	78	74	70	67	64	59	56	54	48	46	45	39
2	86	77	70	63	79	71	65	59	61	56	51	51	47	43	42	39	36	31
3	78	68	59	53	72	63	55	49	53	48	43	45	40	36	37	33	30	26
4	72	60	51	45	66	56	48	42	48	42	37	40	35	32	33	30	27	23
5	67	54	45	39	61	50	43	37	43	37	32	37	32	28	31	27	24	21
6	62	49	41	34	57	46	38	33	40	33	29	34	29	25	28	25	22	19
7	58	45	37	31	53	42	35	29	37	31	26	31	27	23	27	23	20	17
8	54	41	34	28	50	39	32	27	34	28	24	29	25	21	25	21	19	16
9	51	38	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	15
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51714
5°	26175
10°	5026
15°	1686
20°	1008
25°	770
30°	634
35°	572
40°	521
45°	502
50°	488
55°	478
60°	481
65°	479
70°	491
75°	504
80°	513
85°	528

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 90°
 Luminance: 545 cd/sqm

TEST NUMBER: P1245409

CATALOG NUMBER: PRLX-UNA-M-930-06L-U-PS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.8	8.3
10°-20°	21.5	4.0
20°-30°	18.6	3.4
30°-40°	22.4	4.1
40°-50°	27.7	5.1
50°-60°	33.6	6.2
60°-70°	39.2	7.3
70°-80°	44.5	8.2
80°-90°	47.8	8.8
90°-100°	49.0	9.1
100°-110°	47.7	8.8
110°-120°	43.4	8.0
120°-130°	36.5	6.7
130°-140°	28.2	5.2
140°-150°	19.4	3.6
150°-160°	11.3	2.1
160°-170°	4.8	0.9
170°-180°	0.7	0.1
0°-30°	84.9	15.7
0°-40°	107.3	19.8
0°-60°	168.5	31.2
0°-90°	300.1	55.5
90°-120°	140.1	25.9
90°-150°	224.2	41.4
90°-180°	241.0	44.5
0°-180°	541.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1009	
5°	695	45
15°	67	22
25°	40	19
35°	36	22
45°	36	28
55°	37	34
65°	39	39
75°	42	44
85°	44	36
90°	44	24
95°	45	37
105°	45	48
115°	44	43
125°	41	36
135°	37	28
145°	31	19
155°	24	11
165°	16	5
175°	5	1
180°	1	

TEST NUMBER: P1245409

CATALOG NUMBER: PRLX-UNA-M-930-06L-U-PS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1009.1
2.5°	1087.3
5°	695.0
7.5°	242.4
10°	167.8
12.5°	96.1
15°	67.4
17.5°	54.5
20°	46.6
22.5°	42.3
25°	40.2
27.5°	38.0
30°	36.6
32.5°	35.9
35°	35.9
37.5°	35.1
40°	35.1
42.5°	35.1
45°	35.9
47.5°	35.9
50°	36.6
52.5°	36.6
55°	37.3
57.5°	38.0
60°	38.7
62.5°	38.7
65°	39.4
67.5°	40.2
70°	40.9
72.5°	41.6
75°	42.3
77.5°	42.3
80°	43.0
82.5°	43.8
85°	43.8
87.5°	43.8
90°	44.5
92.5°	44.5
95°	45.2
97.5°	45.2
100°	45.2
102.5°	45.2
105°	45.2
107.5°	45.2
110°	44.5

TEST NUMBER: P1245409

CATALOG NUMBER: PRLX-UNA-M-930-06L-U-PS

CANDELA DISTRIBUTION (continued):

	0°
112.5°	44.5
115°	43.8
117.5°	43.0
120°	42.3
122.5°	41.6
125°	40.9
127.5°	39.4
130°	38.7
132.5°	37.3
135°	36.6
137.5°	35.1
140°	33.7
142.5°	32.3
145°	30.8
147.5°	29.4
150°	28.0
152.5°	25.8
155°	24.4
157.5°	22.2
160°	20.8
162.5°	18.6
165°	16.5
167.5°	14.3
170°	12.2
172.5°	8.6
175°	5.0
177.5°	2.2
180°	0.7



TEST NUMBER: P1245409

CATALOG NUMBER: PRLX-UNA-M-930-06L-U-PS

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.6	5.6	5.5	6.5	7.7	4.6	5.6	5.5	6.5	7.7
	3H	7.6	8.5	8.5	9.5	10.7	7.6	8.5	8.5	9.5	10.7
	4H	9.1	10.0	10.0	10.9	12.1	9.1	10.0	10.0	10.9	12.1
	6H	10.6	11.4	11.5	12.3	13.6	10.6	11.4	11.5	12.3	13.6
	8H	11.3	12.1	12.2	13.0	14.2	11.3	12.1	12.2	13.0	14.2
	12H	12.0	12.7	12.9	13.7	14.9	12.0	12.7	12.9	13.7	14.9
4H	2H	5.3	6.2	6.3	7.2	8.4	5.3	6.2	6.3	7.2	8.4
	3H	8.6	9.3	9.5	10.3	11.5	8.6	9.3	9.5	10.3	11.5
	4H	10.2	10.9	11.1	11.9	13.1	10.2	10.9	11.1	11.9	13.1
	6H	11.8	12.5	12.8	13.4	14.7	11.8	12.5	12.8	13.4	14.7
	8H	12.6	13.2	13.6	14.2	15.5	12.6	13.2	13.6	14.2	15.5
	12H	13.4	14.0	14.4	15.0	16.3	13.4	14.0	14.4	15.0	16.3
8H	4H	10.7	11.3	11.7	12.3	13.6	10.7	11.3	11.7	12.3	13.6
	6H	12.6	13.1	13.5	14.1	15.3	12.6	13.1	13.5	14.1	15.3
	8H	13.5	14.0	14.5	15.0	16.3	13.5	14.0	14.5	15.0	16.3
	12H	14.5	14.9	15.5	15.9	17.2	14.5	14.9	15.5	15.9	17.2
12H	4H	10.8	11.4	11.8	12.4	13.6	10.8	11.4	11.8	12.4	13.6
	6H	12.8	13.2	13.7	14.2	15.5	12.8	13.2	13.7	14.2	15.5
	8H	13.8	14.2	14.8	15.2	16.5	13.8	14.2	14.8	15.2	16.5

(END OF REPORT)