

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245465

Luminaire Tested: PRLX-UNA-S-930-07L-U-OW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245465
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2412-299-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UNA-S-930-07L-U-OW
Description: 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, OPEN WEAVE SHADE TEXTURE LIGHT LEVEL 3
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 735.9 lumens
Efficiency: N/A
Efficacy: 45.4 lumens/watt
Spacing Criteria (0/90/45): 0.33 / 0.33 / 0.34
Luminous Opening: Rectangular w/ Sides (W: 0.47' x L: 0.47' x H: 1.12')
CIE Type: Semi-Direct

Input Watts (W): 16.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1245465

CATALOG NUMBER: PRLX-UNA-S-930-07L-U-OW

Luminous Intensity Polar Plot





TEST NUMBER: P1245465

CATALOG NUMBER: PRLX-UNA-S-930-07L-U-OW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71	66
1	99	94	89	84	93	88	84	80	78	74	71	68	65	63	59	57	55	51
2	90	81	74	68	84	77	70	65	68	63	58	59	55	52	52	49	46	42
3	82	72	64	57	77	68	60	55	60	54	49	53	48	44	46	43	40	36
4	76	64	56	49	71	61	53	47	54	48	43	48	43	39	42	38	35	32
5	70	58	49	43	66	55	47	41	49	43	38	44	38	34	38	34	31	28
6	65	53	44	38	61	50	42	37	45	39	34	40	35	31	36	32	28	26
7	61	48	40	35	57	46	39	33	42	35	31	37	32	28	33	29	26	24
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	31	27	24	22
9	54	42	34	29	51	40	33	28	36	30	26	33	28	24	30	26	23	21
10	51	39	32	27	48	37	31	26	34	28	24	31	26	23	28	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	34468
5°	31981
10°	8567
15°	5587
20°	3929
25°	2745
30°	2139
35°	1789
40°	1570
45°	1420
50°	1301
55°	1211
60°	1146
65°	1092
70°	1045
75°	1006
80°	948
85°	923

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1420 cd/sqm

TEST NUMBER: P1245465

CATALOG NUMBER: PRLX-UNA-S-930-07L-U-OW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.9	8.4
10°-20°	50.9	6.9
20°-30°	50.6	6.9
30°-40°	50.8	6.9
40°-50°	53.9	7.3
50°-60°	56.5	7.7
60°-70°	57.4	7.8
70°-80°	55.9	7.6
80°-90°	51.2	7.0
90°-100°	50.6	6.9
100°-110°	48.4	6.6
110°-120°	43.9	6.0
120°-130°	36.7	5.0
130°-140°	28.5	3.9
140°-150°	20.0	2.7
150°-160°	12.2	1.7
160°-170°	5.6	0.8
170°-180°	0.9	0.1
0°-30°	163.4	22.2
0°-40°	214.2	29.1
0°-60°	324.6	44.1
0°-90°	489.1	66.5
90°-120°	142.9	19.4
90°-150°	228.1	31.0
90°-180°	247.0	33.6
0°-180°	735.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	704	
5°	787	62
15°	181	51
25°	108	51
35°	80	51
45°	70	54
55°	63	57
65°	58	57
75°	53	56
85°	47	39
90°	46	25
95°	47	38
105°	46	48
115°	44	44
125°	41	37
135°	37	28
145°	32	20
155°	26	12
165°	20	6
175°	8	1
180°	2	

TEST NUMBER: P1245465

CATALOG NUMBER: PRLX-UNA-S-930-07L-U-OW

CANDELA DISTRIBUTION (FULL):

0°	
0°	703.6
2.5°	763.9
5°	786.9
7.5°	747.1
10°	245.1
12.5°	200.3
15°	181.0
17.5°	163.0
20°	141.2
22.5°	121.3
25°	107.6
27.5°	98.3
30°	90.2
32.5°	85.2
35°	80.2
37.5°	77.1
40°	74.0
42.5°	71.5
45°	69.7
47.5°	67.8
50°	65.9
52.5°	64.7
55°	62.8
57.5°	61.6
60°	60.3
62.5°	59.1
65°	57.9
67.5°	56.6
70°	55.4
72.5°	54.7
75°	52.9
77.5°	51.6
80°	49.1
82.5°	47.3
85°	46.7
87.5°	46.0
90°	46.0
92.5°	46.0
95°	46.7
97.5°	46.7
100°	46.0
102.5°	46.0
105°	46.0
107.5°	45.4
110°	45.4



TEST NUMBER: P1245465

CATALOG NUMBER: PRLX-UNA-S-930-07L-U-OW

CANDELA DISTRIBUTION (continued):

	0°
112.5°	44.8
115°	44.2
117.5°	43.5
120°	42.9
122.5°	41.7
125°	41.1
127.5°	39.8
130°	39.2
132.5°	37.9
135°	36.7
137.5°	35.5
140°	34.2
142.5°	33.0
145°	31.7
147.5°	30.5
150°	29.2
152.5°	28.0
155°	26.1
157.5°	24.9
160°	23.0
162.5°	21.8
165°	19.9
167.5°	17.4
170°	14.3
172.5°	11.2
175°	7.5
177.5°	3.7
180°	1.9



TEST NUMBER: P1245465

CATALOG NUMBER: PRLX-UNA-S-930-07L-U-OW

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.7	9.8	9.5	10.6	11.6	8.7	9.8	9.5	10.6	11.6
	3H	11.1	12.1	11.9	13.0	14.0	11.1	12.1	11.9	13.0	14.0
	4H	12.3	13.2	13.1	14.1	15.1	12.3	13.2	13.1	14.1	15.1
	6H	13.4	14.3	14.3	15.1	16.2	13.4	14.3	14.3	15.1	16.2
	8H	13.9	14.8	14.8	15.6	16.7	13.9	14.8	14.8	15.6	16.7
	12H	14.4	15.2	15.3	16.1	17.2	14.4	15.2	15.3	16.1	17.2
4H	2H	9.3	10.3	10.1	11.1	12.2	9.3	10.3	10.1	11.1	12.2
	3H	12.0	12.8	12.8	13.7	14.7	12.0	12.8	12.8	13.7	14.7
	4H	13.3	14.1	14.2	14.9	16.0	13.3	14.1	14.2	14.9	16.0
	6H	14.6	15.2	15.4	16.1	17.2	14.6	15.2	15.4	16.1	17.2
	8H	15.2	15.8	16.0	16.7	17.8	15.2	15.8	16.0	16.7	17.8
	12H	15.8	16.3	16.7	17.3	18.4	15.8	16.3	16.7	17.3	18.4
8H	4H	13.7	14.4	14.6	15.2	16.4	13.7	14.4	14.6	15.2	16.4
	6H	15.2	15.7	16.1	16.7	17.8	15.2	15.7	16.1	16.7	17.8
	8H	15.9	16.4	16.8	17.3	18.4	15.9	16.4	16.8	17.3	18.4
	12H	16.7	17.1	17.6	18.0	19.2	16.7	17.1	17.6	18.0	19.2
12H	4H	13.8	14.4	14.7	15.3	16.4	13.8	14.4	14.7	15.3	16.4
	6H	15.3	15.8	16.2	16.7	17.9	15.3	15.8	16.2	16.7	17.9
	8H	16.1	16.6	17.0	17.5	18.7	16.1	16.6	17.0	17.5	18.7

(END OF REPORT)