

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1245342

Luminaire Tested: PRLX-UNA-L-935-09L-U-OW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245342
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2412-299-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-UNA-L-935-09L-U-OW
Description: 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, OPEN WEAVE SHADE TEXTURE LIGHT LEVEL 3
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 910.0 lumens
Efficiency: N/A
Efficacy: 40.3 lumens/watt
Spacing Criteria (0/90/45): 0.2 / 0.2 / 0.2
Luminous Opening: Rectangular w/ Sides (W: 0.58' x L: 0.58' x H: 1.92')
CIE Type: General Diffuse

Input Watts (W): 22.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1245342

CATALOG NUMBER: PRLX-UNA-L-935-09L-U-OW

Luminous Intensity Polar Plot





TEST NUMBER: P1245342

CATALOG NUMBER: PRLX-UNA-L-935-09L-U-OW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	109	109	109	109	101	101	101	101	87	87	87		74	74	74		62	62	62	56
1	96	90	85	80	88	83	79	75	71	68	64		60	57	55		49	47	46	40
2	86	77	70	63	80	72	65	59	61	56	51		51	47	44		42	39	37	32
3	79	68	59	52	72	63	55	49	54	48	43		45	40	37		37	34	31	27
4	72	60	51	44	66	56	48	42	48	41	37		40	35	31		33	30	27	23
5	66	54	45	38	61	50	42	36	43	37	32		36	31	28		30	27	23	20
6	61	48	40	34	57	45	37	32	39	33	28		33	28	25		28	24	21	18
7	57	44	36	30	53	41	34	28	36	30	25		31	26	22		26	22	19	17
8	53	41	33	27	49	38	31	26	33	27	23		29	24	20		24	21	18	15
9	50	37	30	25	46	35	28	23	31	25	21		27	22	19		23	19	16	14
10	47	35	27	22	44	33	26	21	29	23	19		25	21	17		22	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	38720
5°	18147
10°	5101
15°	2397
20°	1579
25°	1173
30°	965
35°	844
40°	761
45°	714
50°	681
55°	663
60°	651
65°	647
70°	646
75°	649
80°	642
85°	651

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 714 cd/sqm



TEST NUMBER: P1245342

CATALOG NUMBER: PRLX-UNA-L-935-09L-U-OW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.5	6.0
10°-20°	40.9	4.5
20°-30°	39.9	4.4
30°-40°	45.4	5.0
40°-50°	53.0	5.8
50°-60°	61.5	6.8
60°-70°	69.0	7.6
70°-80°	74.2	8.1
80°-90°	75.7	8.3
90°-100°	77.7	8.5
100°-110°	76.1	8.4
110°-120°	69.5	7.6
120°-130°	59.2	6.5
130°-140°	46.7	5.1
140°-150°	33.4	3.7
150°-160°	21.0	2.3
160°-170°	10.2	1.1
170°-180°	2.1	0.2
0°-30°	135.3	14.9
0°-40°	180.7	19.9
0°-60°	295.1	32.4
0°-90°	514.1	56.5
90°-120°	223.2	24.5
90°-150°	362.6	39.8
90°-180°	396.0	43.5
0°-180°	910.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1224	
5°	736	55
15°	138	41
25°	85	40
35°	72	45
45°	68	53
55°	68	61
65°	70	69
75°	70	74
85°	69	57
90°	70	38
95°	71	58
105°	72	76
115°	70	69
125°	66	59
135°	60	47
145°	53	33
155°	45	21
165°	36	10
175°	19	2
180°	12	

TEST NUMBER: P1245342

CATALOG NUMBER: PRLX-UNA-L-935-09L-U-OW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1223.9
2.5°	1328.1
5°	735.7
7.5°	341.2
10°	250.8
12.5°	172.6
15°	137.6
17.5°	117.3
20°	103.0
22.5°	92.4
25°	85.1
27.5°	80.2
30°	76.5
32.5°	74.1
35°	72.1
37.5°	70.4
40°	69.2
42.5°	68.8
45°	68.4
47.5°	68.0
50°	68.0
52.5°	68.4
55°	68.4
57.5°	68.8
60°	68.8
62.5°	69.2
65°	69.6
67.5°	70.0
70°	70.0
72.5°	70.4
75°	70.4
77.5°	70.0
80°	69.2
82.5°	69.2
85°	69.2
87.5°	69.6
90°	70.0
92.5°	70.8
95°	71.3
97.5°	71.7
100°	72.1
102.5°	72.1
105°	72.1
107.5°	71.7
110°	71.3



TEST NUMBER: P1245342

CATALOG NUMBER: PRLX-UNA-L-935-09L-U-OW

CANDELA DISTRIBUTION (continued):

	0°
112.5°	70.8
115°	70.0
117.5°	69.2
120°	68.4
122.5°	67.2
125°	66.0
127.5°	64.7
130°	63.5
132.5°	61.9
135°	60.3
137.5°	58.6
140°	56.6
142.5°	55.0
145°	52.9
147.5°	51.3
150°	49.3
152.5°	47.2
155°	45.2
157.5°	43.2
160°	40.7
162.5°	38.7
165°	35.8
167.5°	32.6
170°	28.5
172.5°	24.0
175°	18.7
177.5°	13.8
180°	12.2



TEST NUMBER: P1245342

CATALOG NUMBER: PRLX-UNA-L-935-09L-U-OW

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.0	7.0	6.9	7.9	9.1	6.0	7.0	6.9	7.9	9.1
	3H	8.8	9.8	9.7	10.7	11.9	8.8	9.8	9.7	10.7	11.9
	4H	10.2	11.1	11.1	12.0	13.2	10.2	11.1	11.1	12.0	13.2
	6H	11.5	12.4	12.5	13.3	14.5	11.5	12.4	12.5	13.3	14.5
	8H	12.2	13.0	13.1	13.9	15.1	12.2	13.0	13.1	13.9	15.1
	12H	12.8	13.6	13.7	14.5	15.8	12.8	13.6	13.7	14.5	15.8
4H	2H	6.7	7.6	7.6	8.5	9.7	6.7	7.6	7.6	8.5	9.7
	3H	9.7	10.5	10.7	11.5	12.7	9.7	10.5	10.7	11.5	12.7
	4H	11.3	12.0	12.2	12.9	14.2	11.3	12.0	12.2	12.9	14.2
	6H	12.8	13.4	13.7	14.4	15.6	12.8	13.4	13.7	14.4	15.6
	8H	13.5	14.1	14.5	15.1	16.3	13.5	14.1	14.5	15.1	16.3
	12H	14.2	14.8	15.2	15.8	17.0	14.2	14.8	15.2	15.8	17.0
8H	4H	11.8	12.4	12.7	13.3	14.6	11.8	12.4	12.7	13.3	14.6
	6H	13.5	14.0	14.4	15.0	16.2	13.5	14.0	14.4	15.0	16.2
	8H	14.4	14.8	15.3	15.8	17.1	14.4	14.8	15.3	15.8	17.1
	12H	15.3	15.7	16.2	16.7	18.0	15.3	15.7	16.2	16.7	18.0
12H	4H	11.9	12.4	12.8	13.4	14.7	11.9	12.4	12.8	13.4	14.7
	6H	13.6	14.1	14.6	15.1	16.4	13.6	14.1	14.6	15.1	16.4
	8H	14.6	15.0	15.6	16.0	17.3	14.6	15.0	15.6	16.0	17.3

(END OF REPORT)