

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503609

Luminaire Tested: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (2700K-650LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503609
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (2700K-650LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, RING, WHITE REFLECTOR
LIGHT LEVEL 1 - 650 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 2700K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 180.0 lumens
Efficiency: N/A
Efficacy: 27.3 lumens/watt
Spacing Criteria (0/90/45): 1.54 / 1.54 / 1.45
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 6.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503609

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (2700K-650LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503609

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (2700K-650LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	109	105	101	97	107	102	99	95	98	95	92	94	92	90	91	89	87	85		
2	100	92	86	80	98	90	84	79	87	82	78	84	79	76	81	77	74	72		
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	62		
4	84	73	65	58	82	72	64	58	69	62	57	67	61	56	65	60	56	53		
5	78	66	57	51	76	64	56	50	62	55	50	60	54	49	59	53	49	47		
6	72	59	51	44	70	58	50	44	57	49	44	55	48	44	53	48	43	41		
7	67	54	45	39	65	53	45	39	52	44	39	50	44	39	49	43	38	37		
8	62	49	41	35	61	49	41	35	47	40	35	46	39	35	45	39	35	33		
9	58	45	37	32	57	45	37	32	43	36	31	42	36	31	41	35	31	29		
10	55	42	34	29	53	41	34	29	40	33	29	39	33	28	38	32	28	27		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1850
5°	1857
10°	1879
15°	1976
20°	2100
25°	2246
30°	2371
35°	2405
40°	2270
45°	1997
50°	1660
55°	1296
60°	1135
65°	1087
70°	1082
75°	1144
80°	1332
85°	1380

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1997 cd/sqm

TEST NUMBER: P1503609

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (2700K-650LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	5.7	3.2
10°-20°	17.6	9.8
20°-30°	30.5	16.9
30°-40°	39.5	21.9
40°-50°	35.2	19.6
50°-60°	22.4	12.4
60°-70°	14.8	8.2
70°-80°	10.2	5.7
80°-90°	4.1	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	53.8	29.9
0°-40°	93.3	51.8
0°-60°	150.9	83.8
0°-90°	180.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	180.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	60	
5°	60	6
15°	62	18
25°	66	30
35°	64	39
45°	46	35
55°	24	22
65°	15	15
75°	10	10
85°	4	4
90°	0	

TEST NUMBER: P1503609

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (2700K-650LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	60.0
2.5°	59.9
5°	60.0
7.5°	60.0
10°	60.0
12.5°	60.9
15°	61.9
17.5°	62.9
20°	64.0
22.5°	65.1
25°	66.0
27.5°	66.5
30°	66.6
32.5°	66.1
35°	63.9
37.5°	60.7
40°	56.4
42.5°	51.3
45°	45.8
47.5°	40.4
50°	34.6
52.5°	29.1
55°	24.1
57.5°	20.8
60°	18.4
62.5°	16.5
65°	14.9
67.5°	13.4
70°	12.0
72.5°	10.8
75°	9.6
77.5°	8.6
80°	7.5
82.5°	6.2
85°	3.9
87.5°	1.1
90°	0.0

(END OF REPORT)