

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503656

Luminaire Tested: PRLX-SM4-02-LS-FS-D2W-XXXX-WHTE-XX (3000K-1000LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503656
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-02-LS-FS-D2W-XXXX-WHITE-XX (3000K-1000LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, RING, WHITE REFLECTOR
LIGHT LEVEL 3 - 1000 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 320.9 lumens
Efficiency: N/A
Efficacy: 27.9 lumens/watt
Spacing Criteria (0/90/45): 1.54 / 1.54 / 1.45
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 11.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503656

CATALOG NUMBER: PRLX-SM4-02-LS-FS-D2W-XXXX-WHTE-XX (3000K-1000LM)

Luminous Intensity Polar Plot



TEST NUMBER: P1503656

CATALOG NUMBER: PRLX-SM4-02-LS-FS-D2W-XXXX-WHTE-XX (3000K-1000LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20				
RC	80					70					50					30					10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10		
RCR																									
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100							
1	109	105	101	97	107	102	99	95	98	95	92	94	92	90	91	89	87	85							
2	100	92	86	80	97	90	84	79	87	82	78	84	79	76	81	77	74	72							
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	62							
4	84	73	65	58	82	72	64	58	69	62	57	67	61	56	65	60	56	53							
5	78	66	57	51	76	64	56	50	62	55	50	60	54	49	59	53	49	47							
6	72	59	51	44	70	58	50	44	57	49	44	55	48	43	53	48	43	41							
7	67	54	45	39	65	53	45	39	52	44	39	50	44	39	49	43	38	37							
8	62	49	41	35	61	49	41	35	47	40	35	46	39	35	45	39	34	33							
9	58	45	37	32	57	45	37	32	43	36	31	42	36	31	41	35	31	29							
10	55	42	34	29	53	41	34	29	40	33	29	39	33	28	38	32	28	27							

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3296
5°	3309
10°	3347
15°	3521
20°	3744
25°	4001
30°	4227
35°	4288
40°	4046
45°	3559
50°	2960
55°	2312
60°	2023
65°	1941
70°	1929
75°	2037
80°	2380
85°	2477

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3559 cd/sqm

TEST NUMBER: P1503656

CATALOG NUMBER: PRLX-SM4-02-LS-FS-D2W-XXXX-WHTE-XX (3000K-1000LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	10.2	3.2
10°-20°	31.4	9.8
20°-30°	54.3	16.9
30°-40°	70.4	21.9
40°-50°	62.7	19.5
50°-60°	40.0	12.5
60°-70°	26.5	8.3
70°-80°	18.2	5.7
80°-90°	7.3	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	95.9	29.9
0°-40°	166.2	51.8
0°-60°	268.9	83.8
0°-90°	320.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	320.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	107	
5°	107	10
15°	110	31
25°	118	54
35°	114	70
45°	82	63
55°	43	40
65°	27	26
75°	17	18
85°	7	7
90°	0	

TEST NUMBER: P1503656

CATALOG NUMBER: PRLX-SM4-02-LS-FS-D2W-XXXX-WHTE-XX (3000K-1000LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	106.9
2.5°	106.8
5°	106.9
7.5°	106.9
10°	106.9
12.5°	108.5
15°	110.3
17.5°	112.1
20°	114.1
22.5°	116.0
25°	117.6
27.5°	118.5
30°	118.7
32.5°	117.8
35°	113.9
37.5°	108.2
40°	100.5
42.5°	91.4
45°	81.6
47.5°	72.0
50°	61.7
52.5°	51.9
55°	43.0
57.5°	37.1
60°	32.8
62.5°	29.4
65°	26.6
67.5°	23.9
70°	21.4
72.5°	19.2
75°	17.1
77.5°	15.3
80°	13.4
82.5°	11.1
85°	7.0
87.5°	2.0
90°	0.0

(END OF REPORT)