

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503599

Luminaire Tested: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (3500K-1000LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503599
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-6)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (3500K-1000LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, RING, BRASS REFLECTOR
LIGHT LEVEL 3 - 1000 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3500K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 119.3 lumens
Efficiency: N/A
Efficacy: 11.0 lumens/watt
Spacing Criteria (0/90/45): 1.7 / 1.7 / 1.49
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 10.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503599

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (3500K-1000LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503599

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (3500K-1000LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	86	79	73	92	84	78	72	81	76	71	79	74	70	76	72	69	67			
4	88	77	69	64	85	76	69	63	73	67	62	71	66	61	69	65	61	59			
5	81	70	62	56	79	69	61	55	67	60	55	65	59	54	63	58	54	52			
6	75	63	55	49	73	62	55	49	60	54	49	59	53	48	57	52	48	46			
7	70	57	49	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41			
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37			
9	61	48	40	35	59	48	40	35	47	40	35	45	39	35	44	39	35	33			
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	31	30			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1264
5°	1257
10°	1252
15°	1354
20°	1503
25°	1698
30°	1909
35°	2029
40°	1888
45°	1526
50°	1051
55°	575
60°	407
65°	372
70°	343
75°	381
80°	391
85°	460

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1526 cd/sqm

TEST NUMBER: P1503599

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (3500K-1000LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	3.9	3.2
10°-20°	12.2	10.2
20°-30°	23.1	19.4
30°-40°	32.9	27.6
40°-50°	26.7	22.4
50°-60°	10.8	9.0
60°-70°	5.1	4.3
70°-80°	3.3	2.8
80°-90°	1.3	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	39.2	32.8
0°-40°	72.1	60.4
0°-60°	109.6	91.8
0°-90°	119.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	119.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	41	
5°	41	4
15°	42	12
25°	50	23
35°	54	33
45°	35	27
55°	11	11
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1503599

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (3500K-1000LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	41.0
2.5°	40.8
5°	40.6
7.5°	40.3
10°	40.0
12.5°	41.0
15°	42.4
17.5°	44.0
20°	45.8
22.5°	47.7
25°	49.9
27.5°	51.8
30°	53.6
32.5°	55.0
35°	53.9
37.5°	51.2
40°	46.9
42.5°	41.4
45°	35.0
47.5°	28.5
50°	21.9
52.5°	15.7
55°	10.7
57.5°	8.0
60°	6.6
62.5°	5.8
65°	5.1
67.5°	4.5
70°	3.8
72.5°	3.5
75°	3.2
77.5°	2.9
80°	2.2
82.5°	2.1
85°	1.3
87.5°	0.3
90°	0.0

(END OF REPORT)