

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503588

Luminaire Tested: PRLX-SM4-02-LS-FS-010-XXXX-BRNZ-XX (4000K-650LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503588
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-5)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-02-LS-FS-010-XXXX-BRNZ-XX (4000K-650LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, RING, BRONZE REFLECTOR
LIGHT LEVEL 1 - 650 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 4000K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 45.2 lumens
Efficiency: N/A
Efficacy: 6.9 lumens/watt
Spacing Criteria (0/90/45): 2.04 / 2.04 / 1.66
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 6.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503588

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-BRNZ-XX (4000K-650LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503588

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-BRNZ-XX (4000K-650LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	108	104	101	109	106	103	100	101	99	97	98	96	94	94	93	91	89			
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78			
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69			
4	89	78	71	65	86	77	70	65	75	69	64	73	67	63	70	66	62	60			
5	82	71	63	57	80	70	62	57	68	61	56	66	60	56	64	59	55	53			
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	47	43	41			
8	65	53	45	39	64	52	44	39	51	44	39	50	43	39	48	43	39	37			
9	61	48	40	35	59	47	40	35	46	40	35	45	39	35	44	39	35	33			
10	57	44	36	31	55	44	36	31	43	36	31	42	35	31	41	35	31	29			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	318
5°	319
10°	319
15°	393
20°	505
25°	646
30°	819
35°	922
40°	869
45°	685
50°	422
55°	161
60°	68
65°	58
70°	54
75°	60
80°	53
85°	71

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 685 cd/sqm

TEST NUMBER: P1503588

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-BRNZ-XX (4000K-650LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1.0	2.2
10°-20°	3.6	8.0
20°-30°	8.9	19.8
30°-40°	14.9	32.9
40°-50°	11.9	26.3
50°-60°	3.4	7.4
60°-70°	0.8	1.8
70°-80°	0.5	1.1
80°-90°	0.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	13.5	30.0
0°-40°	28.4	62.9
0°-60°	43.6	96.6
0°-90°	45.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	45.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10	
5°	10	1
15°	12	4
25°	19	9
35°	24	15
45°	16	12
55°	3	3
65°	1	1
75°	0	1
85°	0	0
90°	0	

TEST NUMBER: P1503588

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-BRNZ-XX (4000K-650LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	10.3
2.5°	10.3
5°	10.3
7.5°	10.3
10°	10.2
12.5°	11.1
15°	12.3
17.5°	13.7
20°	15.4
22.5°	17.2
25°	19.0
27.5°	21.0
30°	23.0
32.5°	24.4
35°	24.5
37.5°	23.5
40°	21.6
42.5°	18.9
45°	15.7
47.5°	12.3
50°	8.8
52.5°	5.6
55°	3.0
57.5°	1.7
60°	1.1
62.5°	0.9
65°	0.8
67.5°	0.7
70°	0.6
72.5°	0.5
75°	0.5
77.5°	0.5
80°	0.3
82.5°	0.3
85°	0.2
87.5°	0.1
90°	0.0

(END OF REPORT)