

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503669

Luminaire Tested: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-ND (2700K-650LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503669
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-8)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-ND (2700K-650LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, NO DIFFUSER, BRONZE REFLECTOR
LIGHT LEVEL 1 - 650 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 2700K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 424.6 lumens
Efficiency: N/A
Efficacy: 64.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.22 / 1.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 6.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503669

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-ND (2700K-650LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503669

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-ND (2700K-650LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90		
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80		
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	72	71		
4	90	80	73	67	88	79	72	67	76	71	66	74	69	65	72	68	64	63		
5	83	73	65	60	82	72	65	59	70	63	59	68	62	58	66	61	58	56		
6	78	66	59	53	76	65	58	53	64	57	52	62	56	52	61	56	52	50		
7	72	61	53	48	71	60	53	48	58	52	47	57	51	47	56	51	47	45		
8	68	56	48	43	66	55	48	43	54	47	43	53	47	42	52	46	42	41		
9	64	51	44	39	62	51	44	39	50	43	39	49	43	39	48	42	39	37		
10	60	48	41	36	59	47	40	36	46	40	36	45	40	35	45	39	35	34		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6784
5°	6779
10°	6763
15°	6736
20°	6629
25°	6567
30°	6409
35°	6211
40°	5756
45°	5102
50°	4222
55°	3118
60°	1912
65°	584
70°	90
75°	119
80°	178
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5102 cd/sqm

TEST NUMBER: P1503669

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-ND (2700K-650LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.8	4.9
10°-20°	59.4	14.0
20°-30°	88.7	20.9
30°-40°	102.3	24.1
40°-50°	89.3	21.0
50°-60°	52.1	12.3
60°-70°	10.7	2.5
70°-80°	1.1	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	168.9	39.8
0°-40°	271.2	63.9
0°-60°	412.7	97.2
0°-90°	424.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	424.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	220	
5°	219	21
15°	211	59
25°	193	89
35°	165	102
45°	117	89
55°	58	52
65°	8	11
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1503669

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-ND (2700K-650LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	220
2.5°	220
5°	219
7.5°	218
10°	216
12.5°	214
15°	211
17.5°	207
20°	202
22.5°	198
25°	193
27.5°	187
30°	180
32.5°	174
35°	165
37.5°	154
40°	143
42.5°	130
45°	117
47.5°	102
50°	88
52.5°	73
55°	58
57.5°	44
60°	31
62.5°	18
65°	8
67.5°	2
70°	1
72.5°	1
75°	1
77.5°	1
80°	1
82.5°	0
85°	0
87.5°	0
90°	0

(END OF REPORT)