

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1057318

Luminaire Tested: PRLX-CYL2W-DI-X-935-15L-FL-MD-U-S-X-X-BLAK

Issue Date: 8/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1057318
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2504-407-4, G2-2504-407-2)
Test Lab: INNOVATION CENTER
Issue Date: 8/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-CYL2W-DI-X-935-15L-FL-MD-U-S-X-X-BLAK
Description: PrentaLux 2-INCH CYLINDER
DOWNLIGHT 750 LUMENS, FLOOD OPTIC (38-DEGREES)
UPLIGHT 750 LUMENS, MEDIUM OPTIC (23-DEGREES)
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1780.5 lumens
Efficiency: N/A
Efficacy: 139.1 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.6
Luminous Opening: Circular (Dia: 0.15' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 12.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1057318

CATALOG NUMBER: PRLX-CYL2W-DI-X-935-15L-FL-MD-U-S-X-X-BLAK

Luminous Intensity Polar Plot



TEST NUMBER: P1057318

CATALOG NUMBER: PRLX-CYL2W-DI-X-935-15L-FL-MD-U-S-X-X-BLAK

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55
1	100	97	94	91	92	90	87	85	76	75	73	64	63	62	52	52	51
2	94	88	84	80	87	82	78	75	71	68	66	60	58	57	50	49	48
3	88	81	76	71	82	76	71	67	66	63	60	56	54	53	48	47	46
4	83	75	69	64	77	70	65	61	61	58	55	53	51	49	46	44	43
5	78	69	63	59	73	65	60	56	58	54	51	51	48	46	44	42	41
6	74	64	58	54	69	61	56	52	54	50	47	48	45	43	42	40	39
7	70	60	54	50	65	57	52	48	51	47	44	46	43	41	40	38	37
8	66	57	51	46	62	54	48	45	48	44	42	43	41	38	39	37	35
9	63	53	47	43	59	51	46	42	46	42	39	42	39	37	37	35	34
10	60	50	45	41	56	48	43	40	44	40	37	40	37	35	36	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1291610	1291610	1291610
5°	1257084	1257084	1257084
10°	1120069	1120069	1120069
15°	878840	878840	878840
20°	592717	592717	592717
25°	357012	357012	357012
30°	193171	193171	193171
35°	81423	81423	81423
40°	27088	27088	27088
45°	11574	11574	11574
50°	6817	6817	6817
55°	4719	4719	4719
60°	3222	3222	3222
65°	2592	2592	2592
70°	1507	1507	1507
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11574 cd/sqm

TEST NUMBER: P1057318

CATALOG NUMBER: PRLX-CYL2W-DI-X-935-15L-FL-MD-U-S-X-X-BLAK

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.8	10.0
10°-20°	357.2	20.1
20°-30°	234.6	13.2
30°-40°	72.2	4.1
40°-50°	11.4	0.6
50°-60°	3.9	0.2
60°-70°	1.5	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.6	0.0
110°-120°	1.9	0.1
120°-130°	3.9	0.2
130°-140°	14.8	0.8
140°-150°	87.2	4.9
150°-160°	199.2	11.2
160°-170°	345.1	19.4
170°-180°	269.0	15.1
0°-30°	769.7	43.2
0°-40°	841.9	47.3
0°-60°	857.2	48.1
0°-90°	859.0	48.2
90°-120°	2.4	0.1
90°-150°	108.2	6.1
90°-180°	922.0	51.8
0°-180°	1780.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2004	2004	2004	2004	2004	
5°	1943	1943	1943	1943	1943	178
15°	1317	1317	1317	1317	1317	357
25°	502	502	502	502	502	235
35°	104	104	104	104	104	72
45°	13	13	13	13	13	11
55°	4	4	4	4	4	4
65°	2	2	2	2	2	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0
95°	0	0	0	0	0	0
105°	1	1	1	1	1	1
115°	2	2	2	2	2	2
125°	4	4	4	4	4	4
135°	14	14	14	14	14	15
145°	133	133	133	133	133	87
155°	424	424	424	424	424	199
165°	1226	1226	1226	1226	1226	345
175°	3180	3180	3180	3180	3180	269
180°	3654	3654	3654	3654	3654	

TEST NUMBER: P1057318

CATALOG NUMBER: PRLX-CYL2W-DI-X-935-15L-FL-MD-U-S-X-X-BLAK

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2004.3	2004.3	2004.3	2004.3	2004.3
1°	1995.2	1995.2	1995.2	1995.2	1995.2
2°	1986.0	1986.0	1986.0	1986.0	1986.0
3°	1973.8	1973.8	1973.8	1973.8	1973.8
4°	1958.5	1958.5	1958.5	1958.5	1958.5
5°	1943.3	1943.3	1943.3	1943.3	1943.3
6°	1907.6	1907.6	1907.6	1907.6	1907.6
7°	1872.0	1872.0	1872.0	1872.0	1872.0
8°	1825.7	1825.7	1825.7	1825.7	1825.7
9°	1768.7	1768.7	1768.7	1768.7	1768.7
10°	1711.7	1711.7	1711.7	1711.7	1711.7
11°	1639.1	1639.1	1639.1	1639.1	1639.1
12°	1566.5	1566.5	1566.5	1566.5	1566.5
13°	1487.6	1487.6	1487.6	1487.6	1487.6
14°	1402.4	1402.4	1402.4	1402.4	1402.4
15°	1317.3	1317.3	1317.3	1317.3	1317.3
16°	1226.7	1226.7	1226.7	1226.7	1226.7
17°	1136.1	1136.1	1136.1	1136.1	1136.1
18°	1045.5	1045.5	1045.5	1045.5	1045.5
19°	954.9	954.9	954.9	954.9	954.9
20°	864.3	864.3	864.3	864.3	864.3
21°	785.3	785.3	785.3	785.3	785.3
22°	706.2	706.2	706.2	706.2	706.2
23°	633.8	633.8	633.8	633.8	633.8
24°	568.0	568.0	568.0	568.0	568.0
25°	502.1	502.1	502.1	502.1	502.1
26°	449.2	449.2	449.2	449.2	449.2
27°	396.3	396.3	396.3	396.3	396.3
28°	347.8	347.8	347.8	347.8	347.8
29°	303.7	303.7	303.7	303.7	303.7
30°	259.6	259.6	259.6	259.6	259.6
31°	223.6	223.6	223.6	223.6	223.6
32°	187.6	187.6	187.6	187.6	187.6
33°	156.4	156.4	156.4	156.4	156.4
34°	129.9	129.9	129.9	129.9	129.9
35°	103.5	103.5	103.5	103.5	103.5
36°	85.5	85.5	85.5	85.5	85.5
37°	67.5	67.5	67.5	67.5	67.5
38°	53.3	53.3	53.3	53.3	53.3
39°	42.8	42.8	42.8	42.8	42.8
40°	32.2	32.2	32.2	32.2	32.2
41°	26.8	26.8	26.8	26.8	26.8
42°	21.4	21.4	21.4	21.4	21.4
43°	17.5	17.5	17.5	17.5	17.5
44°	15.1	15.1	15.1	15.1	15.1

TEST NUMBER: P1057318

CATALOG NUMBER: PRLX-CYL2W-DI-X-935-15L-FL-MD-U-S-X-X-BLAK

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
45°	12.7	12.7	12.7	12.7	12.7
46°	11.4	11.4	11.4	11.4	11.4
47°	10.0	10.0	10.0	10.0	10.0
48°	8.8	8.8	8.8	8.8	8.8
49°	7.8	7.8	7.8	7.8	7.8
50°	6.8	6.8	6.8	6.8	6.8
51°	6.1	6.1	6.1	6.1	6.1
52°	5.4	5.4	5.4	5.4	5.4
53°	4.9	4.9	4.9	4.9	4.9
54°	4.6	4.6	4.6	4.6	4.6
55°	4.2	4.2	4.2	4.2	4.2
56°	3.9	3.9	3.9	3.9	3.9
57°	3.6	3.6	3.6	3.6	3.6
58°	3.2	3.2	3.2	3.2	3.2
59°	2.9	2.9	2.9	2.9	2.9
60°	2.5	2.5	2.5	2.5	2.5
61°	2.2	2.2	2.2	2.2	2.2
62°	1.9	1.9	1.9	1.9	1.9
63°	1.7	1.7	1.7	1.7	1.7
64°	1.7	1.7	1.7	1.7	1.7
65°	1.7	1.7	1.7	1.7	1.7
66°	1.4	1.4	1.4	1.4	1.4
67°	1.0	1.0	1.0	1.0	1.0
68°	0.8	0.8	0.8	0.8	0.8
69°	0.8	0.8	0.8	0.8	0.8
70°	0.8	0.8	0.8	0.8	0.8
71°	0.8	0.8	0.8	0.8	0.8
72°	0.8	0.8	0.8	0.8	0.8
73°	0.7	0.7	0.7	0.7	0.7
74°	0.3	0.3	0.3	0.3	0.3
75°	0.0	0.0	0.0	0.0	0.0
76°	0.0	0.0	0.0	0.0	0.0
77°	0.0	0.0	0.0	0.0	0.0
78°	0.0	0.0	0.0	0.0	0.0
79°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
81°	0.0	0.0	0.0	0.0	0.0
82°	0.0	0.0	0.0	0.0	0.0
83°	0.0	0.0	0.0	0.0	0.0
84°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
86°	0.0	0.0	0.0	0.0	0.0
87°	0.0	0.0	0.0	0.0	0.0
88°	0.0	0.0	0.0	0.0	0.0
89°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1057318

CATALOG NUMBER: PRLX-CYL2W-DI-X-935-15L-FL-MD-U-S-X-X-BLAK

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0
91°	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0
103°	0.2	0.2	0.2	0.2	0.2
104°	0.5	0.5	0.5	0.5	0.5
105°	0.8	0.8	0.8	0.8	0.8
106°	0.8	0.8	0.8	0.8	0.8
107°	0.8	0.8	0.8	0.8	0.8
108°	0.8	0.8	0.8	0.8	0.8
109°	0.8	0.8	0.8	0.8	0.8
110°	0.8	0.8	0.8	0.8	0.8
111°	1.2	1.2	1.2	1.2	1.2
112°	1.5	1.5	1.5	1.5	1.5
113°	1.7	1.7	1.7	1.7	1.7
114°	1.7	1.7	1.7	1.7	1.7
115°	1.7	1.7	1.7	1.7	1.7
116°	2.0	2.0	2.0	2.0	2.0
117°	2.4	2.4	2.4	2.4	2.4
118°	2.5	2.5	2.5	2.5	2.5
119°	2.5	2.5	2.5	2.5	2.5
120°	2.5	2.5	2.5	2.5	2.5
121°	2.9	2.9	2.9	2.9	2.9
122°	3.2	3.2	3.2	3.2	3.2
123°	3.6	3.6	3.6	3.6	3.6
124°	3.9	3.9	3.9	3.9	3.9
125°	4.2	4.2	4.2	4.2	4.2
126°	4.6	4.6	4.6	4.6	4.6
127°	4.9	4.9	4.9	4.9	4.9
128°	5.4	5.4	5.4	5.4	5.4
129°	6.1	6.1	6.1	6.1	6.1
130°	6.8	6.8	6.8	6.8	6.8
131°	7.8	7.8	7.8	7.8	7.8
132°	8.8	8.8	8.8	8.8	8.8
133°	10.3	10.3	10.3	10.3	10.3
134°	12.4	12.4	12.4	12.4	12.4

TEST NUMBER: P1057318

CATALOG NUMBER: PRLX-CYL2W-DI-X-935-15L-FL-MD-U-S-X-X-BLAK

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
135°	14.4	14.4	14.4	14.4	14.4
136°	19.5	19.5	19.5	19.5	19.5
137°	24.6	24.6	24.6	24.6	24.6
138°	31.4	31.4	31.4	31.4	31.4
139°	39.9	39.9	39.9	39.9	39.9
140°	48.3	48.3	48.3	48.3	48.3
141°	62.6	62.6	62.6	62.6	62.6
142°	76.8	76.8	76.8	76.8	76.8
143°	93.8	93.8	93.8	93.8	93.8
144°	113.5	113.5	113.5	113.5	113.5
145°	133.2	133.2	133.2	133.2	133.2
146°	159.0	159.0	159.0	159.0	159.0
147°	184.7	184.7	184.7	184.7	184.7
148°	211.7	211.7	211.7	211.7	211.7
149°	239.9	239.9	239.9	239.9	239.9
150°	268.0	268.0	268.0	268.0	268.0
151°	297.9	297.9	297.9	297.9	297.9
152°	327.7	327.7	327.7	327.7	327.7
153°	359.0	359.0	359.0	359.0	359.0
154°	391.5	391.5	391.5	391.5	391.5
155°	424.1	424.1	424.1	424.1	424.1
156°	466.2	466.2	466.2	466.2	466.2
157°	508.2	508.2	508.2	508.2	508.2
158°	559.3	559.3	559.3	559.3	559.3
159°	619.4	619.4	619.4	619.4	619.4
160°	679.4	679.4	679.4	679.4	679.4
161°	770.3	770.3	770.3	770.3	770.3
162°	861.3	861.3	861.3	861.3	861.3
163°	970.5	970.5	970.5	970.5	970.5
164°	1098.1	1098.1	1098.1	1098.1	1098.1
165°	1225.7	1225.7	1225.7	1225.7	1225.7
166°	1390.2	1390.2	1390.2	1390.2	1390.2
167°	1554.8	1554.8	1554.8	1554.8	1554.8
168°	1738.5	1738.5	1738.5	1738.5	1738.5
169°	1941.4	1941.4	1941.4	1941.4	1941.4
170°	2144.3	2144.3	2144.3	2144.3	2144.3
171°	2367.5	2367.5	2367.5	2367.5	2367.5
172°	2590.8	2590.8	2590.8	2590.8	2590.8
173°	2797.9	2797.9	2797.9	2797.9	2797.9
174°	2988.9	2988.9	2988.9	2988.9	2988.9
175°	3179.9	3179.9	3179.9	3179.9	3179.9
176°	3314.9	3314.9	3314.9	3314.9	3314.9
177°	3450.0	3450.0	3450.0	3450.0	3450.0
178°	3544.8	3544.8	3544.8	3544.8	3544.8
179°	3599.4	3599.4	3599.4	3599.4	3599.4



TEST NUMBER: P1057318
CATALOG NUMBER: PRLX-CYL2W-DI-X-935-15L-FL-MD-U-S-X-X-BLAK

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
180°	3654.1	3654.1	3654.1	3654.1	3654.1

TEST NUMBER: P1057318

CATALOG NUMBER: PRLX-CYL2W-DI-X-935-15L-FL-MD-U-S-X-X-BLAK

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.28	0.92	1.31	1.91	3.23	0.28	0.92	1.31	1.91	3.23
	3H	0.44	1.00	1.47	2.01	3.35	0.44	1.00	1.47	2.01	3.35
	4H	0.37	0.90	1.41	1.90	3.25	0.37	0.90	1.41	1.90	3.25
	6H	0.25	0.74	1.30	1.75	3.10	0.25	0.74	1.30	1.75	3.10
	8H	0.19	0.65	1.24	1.67	3.02	0.19	0.65	1.24	1.67	3.02
	12H	0.12	0.56	1.18	1.58	2.95	0.12	0.56	1.18	1.58	2.95
4H	2H	0.37	0.90	1.42	1.91	3.25	0.37	0.90	1.42	1.91	3.25
	3H	0.67	1.11	1.72	2.14	3.50	0.67	1.11	1.72	2.14	3.50
	4H	0.58	0.98	1.63	2.01	3.39	0.58	0.98	1.63	2.01	3.39
	6H	0.46	0.80	1.53	1.85	3.23	0.46	0.80	1.53	1.85	3.23
	8H	0.40	0.71	1.46	1.76	3.14	0.40	0.71	1.46	1.76	3.14
	12H	0.32	0.61	1.40	1.66	3.05	0.32	0.61	1.40	1.66	3.05
8H	4H	0.44	0.75	1.50	1.80	3.18	0.44	0.75	1.50	1.80	3.18
	6H	0.31	0.57	1.40	1.66	3.04	0.31	0.57	1.40	1.66	3.04
	8H	0.25	0.48	1.35	1.55	2.95	0.25	0.48	1.35	1.55	2.95
	12H	0.19	0.38	1.28	1.44	2.89	0.19	0.38	1.28	1.44	2.89
12H	4H	0.36	0.65	1.44	1.70	3.09	0.36	0.65	1.44	1.70	3.09
	6H	0.25	0.48	1.35	1.55	2.95	0.25	0.48	1.35	1.55	2.95
	8H	0.19	0.38	1.28	1.44	2.89	0.19	0.38	1.28	1.44	2.89

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

PrentaLux 3D Printing

Report Number: SP1-2504-407-2

Test Date: 07/17/2025

Luminaire Tested: PRLX-CYL2-X-935-10L-FL-U-S-X-X-BLAK


Data in this report applies to families of products including PRLX-CYL2-X-935-10L-FL-U-S-X-X-BLAK

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2504-407-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 07/17/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: PrentaLux 3D Printing
 Catalog Number: **PRLX-CYL2-X-935-10L-FL-U-S-X-X-BLAK**
 Description: PrentaLux 2-INCH CYLINDER, BLACK TRIM, FLOOD OPTIC, 1000 LUMENS, 3500K

Spectral Parameters

CCT (K):	3471	CRI (Ra):	92.0		
CIE u':	0.2363	R1:	93.5	R9:	60.0
CIE v':	0.5123	R2:	93.8	R10:	83.3
Duv:	0.0004	R3:	92.5	R11:	93.8
CIE x:	0.4073	R4:	93.5	R12:	74.7
CIE y:	0.3925	R5:	92.3	R13:	93.1
CIE z:	0.2001	R6:	92.2	R14:	94.7
Peak Wavelength (nm):	630	R7:	93.3	R15:	90.1
Dominant Wavelength (nm):	580	R8:	85.0		
Purity:	40.06645				
Rf:	90				
Rg:	100.7				



Test Conditions


Stabilization Time: 64M
 Operation Time: 2H 4M
 Sphere Temperature (°C): 24.0

REPORT NUMBER: SP1-2504-407-2

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2504-407-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2504-407-2

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	96	NR	620	248	NR	750	4	NR	880	0	NR
365	0	NR	495	117	NR	625	252	NR	755	3	NR	885	0	NR
370	0	NR	500	140	NR	630	1000	NR	760	3	NR	890	0	NR
375	0	NR	505	161	NR	635	638	NR	765	2	NR	895	0	NR
380	0	NR	510	179	NR	640	139	NR	770	2	NR	900	0	NR
385	0	NR	515	192	NR	645	136	NR	775	2	NR	905	0	NR
390	0	NR	520	201	NR	650	116	NR	780	1	NR	910	0	NR
395	1	NR	525	208	NR	655	91	NR	785	1	NR	915	0	NR
400	2	NR	530	214	NR	660	74	NR	790	1	NR	920	0	NR
405	3	NR	535	220	NR	665	59	NR	795	1	NR	925	0	NR
410	5	NR	540	225	NR	670	57	NR	800	1	NR	930	0	NR
415	8	NR	545	231	NR	675	43	NR	805	1	NR	935	0	NR
420	15	NR	550	237	NR	680	37	NR	810	1	NR	940	0	NR
425	26	NR	555	243	NR	685	31	NR	815	1	NR	945	0	NR
430	44	NR	560	250	NR	690	26	NR	820	0	NR	950	0	NR
435	72	NR	565	255	NR	695	22	NR	825	0	NR	955	0	NR
440	120	NR	570	259	NR	700	19	NR	830	0	NR	960	0	NR
445	206	NR	575	262	NR	705	16	NR	835	0	NR	965	0	NR
450	267	NR	580	263	NR	710	14	NR	840	0	NR	970	0	NR
455	197	NR	585	263	NR	715	12	NR	845	0	NR	975	0	NR
460	138	NR	590	260	NR	720	10	NR	850	0	NR	980	0	NR
465	117	NR	595	253	NR	725	8	NR	855	0	NR	985	0	NR
470	88	NR	600	250	NR	730	7	NR	860	0	NR	990	0	NR
475	71	NR	605	247	NR	735	6	NR	865	0	NR	995	0	NR
480	73	NR	610	284	NR	740	5	NR	870	0	NR	1000	0	NR
485	81	NR	615	315	NR	745	4	NR	875	0	NR			

REPORT NUMBER: SP1-2504-407-2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.57

λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)
360	0	NR	490	96	NR	620	248	NR	750	4	NR	880	0	NR
365	0	NR	495	117	NR	625	252	NR	755	3	NR	885	0	NR
370	0	NR	500	140	NR	630	1000	NR	760	3	NR	890	0	NR
375	0	NR	505	161	NR	635	638	NR	765	2	NR	895	0	NR
380	0	NR	510	179	NR	640	139	NR	770	2	NR	900	0	NR
385	0	NR	515	192	NR	645	136	NR	775	2	NR	905	0	NR
390	0	NR	520	201	NR	650	116	NR	780	1	NR	910	0	NR
395	1	NR	525	208	NR	655	91	NR	785	1	NR	915	0	NR
400	2	NR	530	214	NR	660	74	NR	790	1	NR	920	0	NR
405	3	NR	535	220	NR	665	59	NR	795	1	NR	925	0	NR
410	5	NR	540	225	NR	670	57	NR	800	1	NR	930	0	NR
415	8	NR	545	231	NR	675	43	NR	805	1	NR	935	0	NR
420	15	NR	550	237	NR	680	37	NR	810	1	NR	940	0	NR
425	26	NR	555	243	NR	685	31	NR	815	1	NR	945	0	NR
430	44	NR	560	250	NR	690	26	NR	820	0	NR	950	0	NR
435	72	NR	565	255	NR	695	22	NR	825	0	NR	955	0	NR
440	120	NR	570	259	NR	700	19	NR	830	0	NR	960	0	NR
445	206	NR	575	262	NR	705	16	NR	835	0	NR	965	0	NR
450	267	NR	580	263	NR	710	14	NR	840	0	NR	970	0	NR
455	197	NR	585	263	NR	715	12	NR	845	0	NR	975	0	NR
460	138	NR	590	260	NR	720	10	NR	850	0	NR	980	0	NR
465	117	NR	595	253	NR	725	8	NR	855	0	NR	985	0	NR
470	88	NR	600	250	NR	730	7	NR	860	0	NR	990	0	NR
475	71	NR	605	247	NR	735	6	NR	865	0	NR	995	0	NR
480	73	NR	610	284	NR	740	5	NR	870	0	NR	1000	0	NR
485	81	NR	615	315	NR	745	4	NR	875	0	NR			

REPORT NUMBER: SP1-2504-407-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.11

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	96	NR	620	248	NR	750	4	NR	880	0	NR
365	0	NR	495	117	NR	625	252	NR	755	3	NR	885	0	NR
370	0	NR	500	140	NR	630	1000	NR	760	3	NR	890	0	NR
375	0	NR	505	161	NR	635	638	NR	765	2	NR	895	0	NR
380	0	NR	510	179	NR	640	139	NR	770	2	NR	900	0	NR
385	0	NR	515	192	NR	645	136	NR	775	2	NR	905	0	NR
390	0	NR	520	201	NR	650	116	NR	780	1	NR	910	0	NR
395	1	NR	525	208	NR	655	91	NR	785	1	NR	915	0	NR
400	2	NR	530	214	NR	660	74	NR	790	1	NR	920	0	NR
405	3	NR	535	220	NR	665	59	NR	795	1	NR	925	0	NR
410	5	NR	540	225	NR	670	57	NR	800	1	NR	930	0	NR
415	8	NR	545	231	NR	675	43	NR	805	1	NR	935	0	NR
420	15	NR	550	237	NR	680	37	NR	810	1	NR	940	0	NR
425	26	NR	555	243	NR	685	31	NR	815	1	NR	945	0	NR
430	44	NR	560	250	NR	690	26	NR	820	0	NR	950	0	NR
435	72	NR	565	255	NR	695	22	NR	825	0	NR	955	0	NR
440	120	NR	570	259	NR	700	19	NR	830	0	NR	960	0	NR
445	206	NR	575	262	NR	705	16	NR	835	0	NR	965	0	NR
450	267	NR	580	263	NR	710	14	NR	840	0	NR	970	0	NR
455	197	NR	585	263	NR	715	12	NR	845	0	NR	975	0	NR
460	138	NR	590	260	NR	720	10	NR	850	0	NR	980	0	NR
465	117	NR	595	253	NR	725	8	NR	855	0	NR	985	0	NR
470	88	NR	600	250	NR	730	7	NR	860	0	NR	990	0	NR
475	71	NR	605	247	NR	735	6	NR	865	0	NR	995	0	NR
480	73	NR	610	284	NR	740	5	NR	870	0	NR	1000	0	NR
485	81	NR	615	315	NR	745	4	NR	875	0	NR			

REPORT NUMBER: SP1-2504-407-2



TM-30-18

Summary

$R_f = 90$
 $R_g = 100.7$
 $CIE R_a = 92.0$
 $R_9 = 60.0$




Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 88	CES51 = 98	CES76 = 82
CES02 = 62	CES27 = 95	CES52 = 96	CES77 = 87
CES03 = 31	CES28 = 93	CES53 = 93	CES78 = 80
CES04 = 70	CES29 = 89	CES54 = 97	CES79 = 93
CES05 = 49	CES30 = 97	CES55 = 96	CES80 = 91
CES06 = 51	CES31 = 90	CES56 = 93	CES81 = 77
CES07 = 43	CES32 = 82	CES57 = 93	CES82 = 96
CES08 = 41	CES33 = 92	CES58 = 94	CES83 = 94
CES09 = 29	CES34 = 89	CES59 = 97	CES84 = 94
CES10 = 75	CES35 = 93	CES60 = 95	CES85 = 81
CES11 = 58	CES36 = 87	CES61 = 94	CES86 = 81
CES12 = 64	CES37 = 90	CES62 = 93	CES87 = 90
CES13 = 43	CES38 = 97	CES63 = 91	CES88 = 96
CES14 = 74	CES39 = 98	CES64 = 91	CES89 = 82
CES15 = 71	CES40 = 95	CES65 = 88	CES90 = 97
CES16 = 47	CES41 = 96	CES66 = 88	CES91 = 78
CES17 = 49	CES42 = 88	CES67 = 86	CES92 = 77
CES18 = 56	CES43 = 89	CES68 = 88	CES93 = 86
CES19 = 71	CES44 = 99	CES69 = 89	CES94 = 72
CES20 = 66	CES45 = 93	CES70 = 84	CES95 = 83
CES21 = 86	CES46 = 93	CES71 = 81	CES96 = 91
CES22 = 78	CES47 = 90	CES72 = 94	CES97 = 92
CES23 = 91	CES48 = 95	CES73 = 78	CES98 = 92
CES24 = 90	CES49 = 91	CES74 = 92	CES99 = 93
CES25 = 71	CES50 = 98	CES75 = 82	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)