

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503804

Luminaire Tested: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (2700K-650LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503804
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-8)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (2700K-650LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, NO DIFFUSER, BRONZE REFLECTOR
LIGHT LEVEL 1 - 650 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 2700K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 465.5 lumens
Efficiency: N/A
Efficacy: 67.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.22 / 1.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 6.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503804

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (2700K-650LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503804

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (2700K-650LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90		
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80		
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	72	71		
4	90	80	73	67	88	79	72	67	76	71	66	74	69	65	72	68	64	63		
5	83	73	65	60	82	72	65	59	70	63	59	68	62	58	66	61	58	56		
6	78	66	59	53	76	65	58	53	64	57	52	62	56	52	61	56	52	50		
7	72	61	53	48	71	60	53	48	58	52	47	57	51	47	56	51	47	45		
8	68	56	48	43	66	55	48	43	54	47	43	53	47	42	52	46	42	41		
9	64	51	44	39	62	51	44	39	50	43	39	49	43	39	48	42	39	37		
10	60	48	41	36	59	47	40	36	46	40	36	45	40	35	45	39	35	34		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	7438
5°	7432
10°	7415
15°	7387
20°	7269
25°	7200
30°	7029
35°	6810
40°	6312
45°	5595
50°	4629
55°	3419
60°	2097
65°	642
70°	99
75°	131
80°	195
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5595 cd/sqm

TEST NUMBER: P1503804

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (2700K-650LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.8	4.9
10°-20°	65.1	14.0
20°-30°	97.2	20.9
30°-40°	112.2	24.1
40°-50°	98.0	21.0
50°-60°	57.1	12.3
60°-70°	11.8	2.5
70°-80°	1.2	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	185.2	39.8
0°-40°	297.4	63.9
0°-60°	452.5	97.2
0°-90°	465.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	465.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	241	
5°	240	23
15°	231	65
25°	212	97
35°	181	112
45°	128	98
55°	64	57
65°	9	12
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1503804

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (2700K-650LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	241.2
2.5°	241.2
5°	240.1
7.5°	239.0
10°	236.8
12.5°	234.6
15°	231.4
17.5°	227.0
20°	221.5
22.5°	217.1
25°	211.6
27.5°	205.0
30°	197.4
32.5°	190.8
35°	180.9
37.5°	168.9
40°	156.8
42.5°	142.5
45°	128.3
47.5°	111.8
50°	96.5
52.5°	80.0
55°	63.6
57.5°	48.2
60°	34.0
62.5°	19.7
65°	8.8
67.5°	2.2
70°	1.1
72.5°	1.1
75°	1.1
77.5°	1.1
80°	1.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)