

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503819

Luminaire Tested: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (2700K-650LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503819
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-14)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (2700K-650LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN CYLINDER, BRONZE REFLECTOR
LIGHT LEVEL 1 - 650 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 2700K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 474.8 lumens
Efficiency: N/A
Efficacy: 68.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 6.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503819

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (2700K-650LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503819

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (2700K-650LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87			
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			
3	94	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	88	77	69	64	85	76	69	63	73	67	62	71	66	61	69	65	61	59			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			
10	59	46	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	8082
5°	8079
10°	8035
15°	7735
20°	7341
25°	6938
30°	6441
35°	5903
40°	5342
45°	4688
50°	3943
55°	3183
60°	2504
65°	2240
70°	2173
75°	2085
80°	1953
85°	1557

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4688 cd/sqm

TEST NUMBER: P1503819

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (2700K-650LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.8	5.2
10°-20°	68.0	14.3
20°-30°	93.5	19.7
30°-40°	97.9	20.6
40°-50°	82.5	17.4
50°-60°	53.7	11.3
60°-70°	30.8	6.5
70°-80°	18.2	3.8
80°-90°	5.4	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	186.3	39.2
0°-40°	284.2	59.9
0°-60°	420.4	88.5
0°-90°	474.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	474.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	262	
5°	261	25
15°	242	68
25°	204	94
35°	157	98
45°	108	82
55°	59	54
65°	31	31
75°	18	18
85°	4	5
90°	0	

TEST NUMBER: P1503819

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-OC (2700K-650LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	262.1
2.5°	262.1
5°	261.0
7.5°	261.0
10°	256.6
12.5°	250.0
15°	242.3
17.5°	233.5
20°	223.7
22.5°	213.8
25°	203.9
27.5°	193.0
30°	180.9
32.5°	168.9
35°	156.8
37.5°	144.7
40°	132.7
42.5°	119.5
45°	107.5
47.5°	94.3
50°	82.2
52.5°	71.3
55°	59.2
57.5°	49.3
60°	40.6
62.5°	34.0
65°	30.7
67.5°	27.4
70°	24.1
72.5°	20.8
75°	17.5
77.5°	13.2
80°	11.0
82.5°	7.7
85°	4.4
87.5°	2.2
90°	0.0

(END OF REPORT)