

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503863

Luminaire Tested: PRLX-SM4-03-LS-FS-D2W-XXXX-BRSS-XX-OC (2700K-1000LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503863
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-15)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-D2W-XXXX-BRSS-XX-OC (2700K-1000LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN CYLINDER, BRASS REFLECTOR
LIGHT LEVEL 3 - 1000 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 2700K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 793.8 lumens
Efficiency: N/A
Efficacy: 69.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 11.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503863

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRSS-XX-OC (2700K-1000LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503863

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRSS-XX-OC (2700K-1000LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87			
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			
3	94	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	68	66			
4	88	77	69	63	85	76	69	63	73	67	62	71	66	61	69	64	61	59			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47			
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35			
10	59	46	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	13475
5°	13471
10°	13402
15°	12913
20°	12266
25°	11551
30°	10739
35°	9859
40°	8868
45°	7797
50°	6582
55°	5339
60°	4231
65°	3823
70°	3579
75°	3443
80°	3214
85°	2547

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7797 cd/sqm

TEST NUMBER: P1503863

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRSS-XX-OC (2700K-1000LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.4	5.2
10°-20°	113.5	14.3
20°-30°	156.0	19.6
30°-40°	163.4	20.6
40°-50°	137.9	17.4
50°-60°	90.1	11.4
60°-70°	52.3	6.6
70°-80°	30.5	3.8
80°-90°	8.8	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	310.8	39.2
0°-40°	474.2	59.7
0°-60°	702.2	88.5
0°-90°	793.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	793.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	437	
5°	435	41
15°	404	114
25°	340	156
35°	262	163
45°	179	138
55°	99	90
65°	52	52
75°	29	30
85°	7	9
90°	0	

TEST NUMBER: P1503863

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRSS-XX-OC (2700K-1000LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	437.0
2.5°	437.0
5°	435.2
7.5°	433.4
10°	428.0
12.5°	417.2
15°	404.5
17.5°	390.1
20°	373.8
22.5°	357.6
25°	339.5
27.5°	321.4
30°	301.6
32.5°	281.7
35°	261.9
37.5°	242.0
40°	220.3
42.5°	200.5
45°	178.8
47.5°	158.9
50°	137.2
52.5°	119.2
55°	99.3
57.5°	83.1
60°	68.6
62.5°	57.8
65°	52.4
67.5°	47.0
70°	39.7
72.5°	34.3
75°	28.9
77.5°	23.5
80°	18.1
82.5°	12.6
85°	7.2
87.5°	3.6
90°	0.0

(END OF REPORT)