

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P981042

Luminaire Tested: PRLX-CYL3-10-940-23L-MD-U-S-X-X-WHTE

Issue Date: 4/11/2025

Test Information

Test Method: LM-79-2019
Report Number: P981042
TEST IS SCALED FROM (FO44193.PSO)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/11/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-CYL3-10-940-23L-MD-U-S-X-X-WHTE
Description: PrentaLux 3-INCH CYLINDER, MEDIUM OPTIC
2300 LUMENS
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2492.9 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 0.32 / 0.32 / 0.37
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 22.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P981042

CATALOG NUMBER: PRLX-CYL3-10-940-23L-MD-U-S-X-X-WHTE

Luminous Intensity Polar Plot



TEST NUMBER: P981042

CATALOG NUMBER: PRLX-CYL3-10-940-23L-MD-U-S-X-X-WHTE

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	115	112	110	109	112	110	108	107	106	105	104		103	102	101		96
2	111	107	103	101	108	105	102	100	102	99	97		99	97	95		92
3	107	102	98	95	105	100	97	94	98	95	92		95	93	91		88
4	103	97	93	89	101	96	92	89	94	91	88		92	89	87		85
5	99	93	88	85	98	92	88	85	90	87	84		89	86	83		82
6	96	89	85	81	95	89	84	81	87	83	81		86	83	80		78
7	93	86	81	78	92	85	81	78	84	80	78		83	80	77		76
8	90	83	78	75	89	82	78	75	81	77	75		80	77	74		73
9	87	80	75	72	86	79	75	72	79	75	72		78	74	72		71
10	85	77	73	70	84	77	73	70	76	72	70		75	72	69		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2532144
5°	2060615
10°	1204320
15°	713148
20°	464747
25°	343254
30°	210286
35°	53271
40°	16603
45°	3876
50°	1774
55°	1376
60°	1447
65°	1660
70°	1923
75°	2203
80°	3031
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3876 cd/sqm

TEST NUMBER: P981042

CATALOG NUMBER: PRLX-CYL3-10-940-23L-MD-U-S-X-X-WHTE

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	758.4	30.4
10°-20°	891.5	35.8
20°-30°	643.0	25.8
30°-40°	174.2	7.0
40°-50°	15.1	0.6
50°-60°	3.4	0.1
60°-70°	3.2	0.1
70°-80°	2.8	0.1
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2292.9	92.0
0°-40°	2467.2	99.0
0°-60°	2485.7	99.7
0°-90°	2492.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2492.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11548	
5°	9361	758
15°	3141	892
25°	1419	643
35°	199	174
45°	12	15
55°	4	3
65°	3	3
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P981042

CATALOG NUMBER: PRLX-CYL3-10-940-23L-MD-U-S-X-X-WHTE

CANDELA DISTRIBUTION (FULL):

0°	
0°	11547.5
1°	11466.9
2°	11195.5
3°	10727.6
4°	10103.3
5°	9361.4
6°	8552.3
7°	7713.9
8°	6879.8
9°	6104.7
10°	5408.7
11°	4810.9
12°	4306.7
13°	3865.6
14°	3477.7
15°	3141.4
16°	2847.3
17°	2584.2
18°	2348.1
19°	2155.5
20°	1991.6
21°	1855.9
22°	1729.6
23°	1616.2
24°	1512.3
25°	1418.7
26°	1329.9
27°	1234.1
28°	1126.7
29°	987.7
30°	830.5
31°	675.0
32°	531.7
33°	401.5
34°	288.1
35°	199.0
36°	138.2
37°	100.5
38°	82.6
39°	69.7
40°	58.0
41°	47.5
42°	37.2
43°	25.9
44°	16.6

TEST NUMBER: P981042

CATALOG NUMBER: PRLX-CYL3-10-940-23L-MD-U-S-X-X-WHTE

CANDELA DISTRIBUTION (continued):

	0°
45°	12.5
46°	9.9
47°	8.2
48°	6.8
49°	5.8
50°	5.2
51°	4.6
52°	4.3
53°	4.0
54°	3.8
55°	3.6
56°	3.6
57°	3.5
58°	3.3
59°	3.3
60°	3.3
61°	3.2
62°	3.2
63°	3.2
64°	3.2
65°	3.2
66°	3.2
67°	3.2
68°	3.1
69°	3.1
70°	3.0
71°	3.0
72°	2.9
73°	2.8
74°	2.7
75°	2.6
76°	2.6
77°	2.5
78°	2.5
79°	2.4
80°	2.4
81°	2.3
82°	2.2
83°	2.1
84°	1.7
85°	1.4
86°	0.8
87°	0.2
88°	0.1
89°	0.0

TEST NUMBER: P981042

CATALOG NUMBER: PRLX-CYL3-10-940-23L-MD-U-S-X-X-WHTE

CANDELA DISTRIBUTION (continued):

90° | $\frac{0^\circ}{0.0}$

TEST NUMBER: P981042

CATALOG NUMBER: PRLX-CYL3-10-940-23L-MD-U-S-X-X-WHTE

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.70	1.48	1.08	1.82	2.19	0.70	1.48	1.08	1.82	2.19
	4H	2.10	2.82	2.50	3.17	3.56	2.10	2.82	2.50	3.17	3.56
	6H	3.60	4.26	4.02	4.64	5.04	3.60	4.26	4.02	4.64	5.04
	8H	4.37	4.99	4.81	5.38	5.79	4.37	4.99	4.81	5.38	5.79
	12H	4.78	5.37	5.22	5.76	6.19	4.78	5.37	5.22	5.76	6.19
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	1.80	2.39	2.22	2.80	3.21	1.80	2.39	2.22	2.80	3.21
	4H	3.33	3.85	3.76	4.28	4.73	3.33	3.85	3.76	4.28	4.73
	6H	5.01	5.46	5.48	5.91	6.39	5.01	5.46	5.48	5.91	6.39
	8H	5.86	6.27	6.34	6.73	7.20	5.86	6.27	6.34	6.73	7.20
	12H	6.40	6.76	6.90	7.25	7.73	6.40	6.76	6.90	7.25	7.73
8H	4H	3.89	4.31	4.37	4.76	5.24	3.89	4.31	4.37	4.76	5.24
	6H	5.84	6.16	6.35	6.67	7.16	5.84	6.16	6.35	6.67	7.16
	8H	6.85	7.14	7.39	7.67	8.16	6.85	7.14	7.39	7.67	8.16
	12H	7.57	7.81	8.09	8.31	8.89	7.57	7.81	8.09	8.31	8.89
12H	4H	4.03	4.38	4.52	4.87	5.35	4.03	4.38	4.52	4.87	5.35
	6H	6.06	6.35	6.60	6.88	7.37	6.06	6.35	6.60	6.88	7.37
	8H	7.18	7.42	7.70	7.92	8.50	7.18	7.42	7.70	7.92	8.50

END OF REPORT