

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503894

Luminaire Tested: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-ND (2700K-650LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503894
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-7)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-ND (2700K-650LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, NO DIFFUSER, WHITE REFLECTOR
LIGHT LEVEL 1 - 650 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 2700K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 615.0 lumens
Efficiency: N/A
Efficacy: 89.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.3
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 6.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503894

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-ND (2700K-650LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503894

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-ND (2700K-650LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88		
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76		
3	94	85	78	72	92	83	77	72	81	75	70	78	73	69	76	71	68	66		
4	87	76	69	63	85	75	68	62	73	66	61	70	65	61	68	64	60	58		
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51		
6	75	63	54	49	73	62	54	48	60	53	48	58	52	48	57	51	47	45		
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	41		
8	65	52	44	39	63	52	44	39	50	44	39	49	43	38	48	42	38	36		
9	61	48	41	35	59	48	40	35	47	40	35	46	39	35	45	39	35	33		
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	41	36	32	30		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	8622
5°	8621
10°	8583
15°	8540
20°	8493
25°	8394
30°	8279
35°	8090
40°	7636
45°	6982
50°	6102
55°	5070
60°	3787
65°	2481
70°	1974
75°	1954
80°	1953
85°	1557

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6982 cd/sqm

TEST NUMBER: P1503894

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-ND (2700K-650LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.4	4.3
10°-20°	75.5	12.3
20°-30°	113.6	18.5
30°-40°	133.5	21.7
40°-50°	122.8	20.0
50°-60°	84.0	13.7
60°-70°	36.5	5.9
70°-80°	17.4	2.8
80°-90°	5.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	215.5	35.0
0°-40°	349.1	56.8
0°-60°	555.9	90.4
0°-90°	615.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	615.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	280	
5°	278	26
15°	268	76
25°	247	114
35°	215	134
45°	160	123
55°	94	84
65°	34	36
75°	16	17
85°	4	5
90°	0	

TEST NUMBER: P1503894

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-ND (2700K-650LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	279.6
2.5°	278.5
5°	278.5
7.5°	276.3
10°	274.1
12.5°	271.9
15°	267.5
17.5°	263.2
20°	258.8
22.5°	252.2
25°	246.7
27.5°	240.1
30°	232.5
32.5°	224.8
35°	214.9
37.5°	202.8
40°	189.7
42.5°	175.4
45°	160.1
47.5°	143.6
50°	127.2
52.5°	110.7
55°	94.3
57.5°	77.8
60°	61.4
62.5°	47.1
65°	34.0
67.5°	25.2
70°	21.9
72.5°	18.6
75°	16.4
77.5°	14.3
80°	11.0
82.5°	7.7
85°	4.4
87.5°	2.2
90°	0.0

(END OF REPORT)