

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503910

Luminaire Tested: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OC (2700K-800LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503910
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-13)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-D2W-XXXX-WHITE-XX-OC (2700K-800LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN CYLINDER, WHITE REFLECTOR
LIGHT LEVEL 2 - 800 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 2700K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 675.5 lumens
Efficiency: N/A
Efficacy: 76.8 lumens/watt
Spacing Criteria (0/90/45): 1.07 / 1.07 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 8.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503910

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OC (2700K-800LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503910

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OC (2700K-800LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76			
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66			
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	52			
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	11200
5°	11156
10°	11069
15°	10707
20°	10183
25°	9612
30°	8969
35°	8278
40°	7507
45°	6677
50°	5742
55°	4790
60°	3861
65°	3451
70°	3264
75°	2990
80°	2717
85°	2477

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6677 cd/sqm

TEST NUMBER: P1503910

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OC (2700K-800LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.2	5.1
10°-20°	94.0	13.9
20°-30°	129.8	19.2
30°-40°	137.2	20.3
40°-50°	117.9	17.4
50°-60°	80.2	11.9
60°-70°	47.3	7.0
70°-80°	27.0	4.0
80°-90°	7.8	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	258.1	38.2
0°-40°	395.3	58.5
0°-60°	593.4	87.8
0°-90°	675.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	675.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	363	
5°	360	34
15°	335	94
25°	282	130
35°	220	137
45°	153	118
55°	89	80
65°	47	47
75°	25	27
85°	7	8
90°	0	

TEST NUMBER: P1503910

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OC (2700K-800LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	363.2
2.5°	361.8
5°	360.4
7.5°	359.1
10°	353.5
12.5°	345.1
15°	335.4
17.5°	322.9
20°	310.3
22.5°	296.4
25°	282.5
27.5°	268.6
30°	251.9
32.5°	236.6
35°	219.9
37.5°	203.2
40°	186.5
42.5°	169.8
45°	153.1
47.5°	136.4
50°	119.7
52.5°	104.4
55°	89.1
57.5°	75.2
60°	62.6
62.5°	52.9
65°	47.3
67.5°	41.8
70°	36.2
72.5°	30.6
75°	25.1
77.5°	20.9
80°	15.3
82.5°	11.1
85°	7.0
87.5°	2.8
90°	0.0

(END OF REPORT)