

Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503671

Luminaire Tested: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-ND (3000K-1000LM)

Issue Date: 7/28/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1503671  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/28/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PrentaLux  
Catalog Number: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-ND (3000K-1000LM)  
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, NO DIFFUSER, BRONZE REFLECTOR  
LIGHT LEVEL 3 - 1000 NOMINAL LUMENS  
Light Source: SELECTABLE CCT - 3000K CCT, 90 CRI  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 676.0 lumens  
Efficiency: N/A  
Efficacy: 62.0 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.22 / 1.27  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1503671

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-ND (3000K-1000LM)

### Luminous Intensity Polar Plot





TEST NUMBER: P1503671

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-ND (3000K-1000LM)

### COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |  |  |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|--|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |  |  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |  |  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |  |  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |  |  |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |  |  |
| 1   | 112 | 108 | 105 | 102 | 109 | 106 | 103 | 101 | 102 | 100 | 98  | 98  | 96  | 95  | 95  | 93  | 92  | 90  |  |  |
| 2   | 104 | 98  | 93  | 88  | 102 | 96  | 91  | 87  | 93  | 89  | 85  | 90  | 86  | 84  | 87  | 84  | 82  | 80  |  |  |
| 3   | 97  | 88  | 82  | 77  | 95  | 87  | 81  | 76  | 84  | 79  | 75  | 82  | 77  | 74  | 79  | 76  | 72  | 71  |  |  |
| 4   | 90  | 80  | 73  | 67  | 88  | 79  | 72  | 67  | 76  | 71  | 66  | 74  | 69  | 65  | 72  | 68  | 64  | 63  |  |  |
| 5   | 83  | 73  | 65  | 60  | 82  | 72  | 65  | 59  | 70  | 63  | 59  | 68  | 62  | 58  | 66  | 61  | 58  | 56  |  |  |
| 6   | 78  | 66  | 59  | 53  | 76  | 65  | 58  | 53  | 64  | 57  | 52  | 62  | 56  | 52  | 61  | 56  | 52  | 50  |  |  |
| 7   | 72  | 61  | 53  | 48  | 71  | 60  | 53  | 48  | 58  | 52  | 47  | 57  | 51  | 47  | 56  | 51  | 47  | 45  |  |  |
| 8   | 68  | 56  | 48  | 43  | 66  | 55  | 48  | 43  | 54  | 47  | 43  | 53  | 47  | 42  | 52  | 46  | 42  | 41  |  |  |
| 9   | 64  | 51  | 44  | 39  | 62  | 51  | 44  | 39  | 50  | 43  | 39  | 49  | 43  | 39  | 48  | 42  | 39  | 37  |  |  |
| 10  | 60  | 48  | 41  | 36  | 59  | 47  | 40  | 36  | 46  | 40  | 36  | 45  | 40  | 35  | 45  | 39  | 35  | 34  |  |  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°    |
|-----|-------|
| 0°  | 10802 |
| 5°  | 10794 |
| 10° | 10768 |
| 15° | 10723 |
| 20° | 10553 |
| 25° | 10456 |
| 30° | 10205 |
| 35° | 9889  |
| 40° | 9166  |
| 45° | 8124  |
| 50° | 6721  |
| 55° | 4962  |
| 60° | 3047  |
| 65° | 927   |
| 70° | 144   |
| 75° | 191   |
| 80° | 284   |
| 85° | 0     |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle:  $0^\circ$ 

Vertical Angle:  $45^\circ$

Luminance: 8124 cd/sqm

TEST NUMBER: P1503671

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-ND (3000K-1000LM)

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 33.2   | 4.9       |
| 10°-20°   | 94.6   | 14.0      |
| 20°-30°   | 141.2  | 20.9      |
| 30°-40°   | 162.9  | 24.1      |
| 40°-50°   | 142.3  | 21.0      |
| 50°-60°   | 83.0   | 12.3      |
| 60°-70°   | 17.1   | 2.5       |
| 70°-80°   | 1.7    | 0.3       |
| 80°-90°   | 0.2    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 268.9  | 39.8      |
| 0°-40°    | 431.8  | 63.9      |
| 0°-60°    | 657.0  | 97.2      |
| 0°-90°    | 676.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 676.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 350 |      |
| 5°  | 349 | 33   |
| 15° | 336 | 95   |
| 25° | 307 | 141  |
| 35° | 263 | 163  |
| 45° | 186 | 142  |
| 55° | 92  | 83   |
| 65° | 13  | 17   |
| 75° | 2   | 2    |
| 85° | 0   | 0    |
| 90° | 0   |      |

TEST NUMBER: P1503671

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-ND (3000K-1000LM)

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 350.3 |
| 2.5°  | 350.3 |
| 5°    | 348.7 |
| 7.5°  | 347.1 |
| 10°   | 343.9 |
| 12.5° | 340.7 |
| 15°   | 335.9 |
| 17.5° | 329.6 |
| 20°   | 321.6 |
| 22.5° | 315.2 |
| 25°   | 307.3 |
| 27.5° | 297.7 |
| 30°   | 286.6 |
| 32.5° | 277.0 |
| 35°   | 262.7 |
| 37.5° | 245.2 |
| 40°   | 227.7 |
| 42.5° | 207.0 |
| 45°   | 186.3 |
| 47.5° | 162.4 |
| 50°   | 140.1 |
| 52.5° | 116.2 |
| 55°   | 92.3  |
| 57.5° | 70.1  |
| 60°   | 49.4  |
| 62.5° | 28.7  |
| 65°   | 12.7  |
| 67.5° | 3.2   |
| 70°   | 1.6   |
| 72.5° | 1.6   |
| 75°   | 1.6   |
| 77.5° | 1.6   |
| 80°   | 1.6   |
| 82.5° | 0.0   |
| 85°   | 0.0   |
| 87.5° | 0.0   |
| 90°   | 0.0   |

(END OF REPORT)