

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P981014

Luminaire Tested: PRLX-CYL3S-10-930-15L-MD-U-S-X-X-WHTE

Issue Date: 4/11/2025

Test Information

Test Method: LM-79-2024
Report Number: P981014
TEST IS SCALED FROM (FO44193.PSO)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/11/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PentaLux
Catalog Number: PRLX-CYL3S-10-930-15L-MD-U-S-X-X-WHTE
Description: PentaLux 3-INCH CYLINDER, MEDIUM OPTIC
1500 LUMENS
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1500.4 lumens
Efficiency: N/A
Efficacy: 111.1 lumens/watt
Spacing Criteria (0/90/45): 0.32 / 0.32 / 0.37
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P981014

CATALOG NUMBER: PRLX-CYL3S-10-930-15L-MD-U-S-X-X-WHTE

Luminous Intensity Polar Plot





TEST NUMBER: P981014

CATALOG NUMBER: PRLX-CYL3S-10-930-15L-MD-U-S-X-X-WHTE

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	112	110	109	112	110	108	107	106	105	104	103	102	101	99	98	98	96
2	111	107	103	101	108	105	102	100	102	99	97	99	97	95	96	95	93	92
3	107	102	98	95	105	100	97	94	98	95	92	95	93	91	93	91	90	88
4	103	97	93	89	101	96	92	89	94	91	88	92	89	87	90	88	86	85
5	99	93	88	85	98	92	88	85	90	87	84	89	86	83	87	85	83	82
6	96	89	85	81	95	89	84	81	87	83	81	86	83	80	85	82	80	78
7	93	86	81	78	92	85	81	78	84	80	78	83	80	77	82	79	77	76
8	90	83	78	75	89	82	78	75	81	77	75	80	77	74	80	76	74	73
9	87	80	75	72	86	79	75	72	79	75	72	78	74	72	77	74	72	71
10	85	77	73	70	84	77	73	70	76	72	70	75	72	69	75	72	69	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1523979
5°	1240190
10°	724836
15°	429197
20°	279721
25°	206576
30°	126551
35°	32070
40°	9990
45°	2326
50°	1058
55°	803
60°	877
65°	986
70°	1154
75°	1356
80°	1768
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2326 cd/sqm

TEST NUMBER: P981014

CATALOG NUMBER: PRLX-CYL3S-10-930-15L-MD-U-S-X-X-WHTE

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	456.4	30.4
10°-20°	536.6	35.8
20°-30°	387.0	25.8
30°-40°	104.9	7.0
40°-50°	9.1	0.6
50°-60°	2.0	0.1
60°-70°	1.9	0.1
70°-80°	1.7	0.1
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1380.0	92.0
0°-40°	1484.9	99.0
0°-60°	1496.0	99.7
0°-90°	1500.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1500.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6950	
5°	5634	456
15°	1891	537
25°	854	387
35°	120	105
45°	8	9
55°	2	2
65°	2	2
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P981014

CATALOG NUMBER: PRLX-CYL3S-10-930-15L-MD-U-S-X-X-WHTE

CANDELA DISTRIBUTION (FULL):

0°	
0°	6949.9
1°	6901.3
2°	6738.0
3°	6456.4
4°	6080.7
5°	5634.2
6°	5147.2
7°	4642.6
8°	4140.6
9°	3674.1
10°	3255.3
11°	2895.5
12°	2592.0
13°	2326.5
14°	2093.1
15°	1890.6
16°	1713.7
17°	1555.3
18°	1413.2
19°	1297.3
20°	1198.7
21°	1117.0
22°	1041.0
23°	972.7
24°	910.2
25°	853.8
26°	800.4
27°	742.8
28°	678.1
29°	594.4
30°	499.8
31°	406.2
32°	320.0
33°	241.7
34°	173.4
35°	119.8
36°	83.2
37°	60.5
38°	49.7
39°	41.9
40°	34.9
41°	28.6
42°	22.4
43°	15.6
44°	10.0

TEST NUMBER: P981014

CATALOG NUMBER: PRLX-CYL3S-10-930-15L-MD-U-S-X-X-WHTE

CANDELA DISTRIBUTION (continued):

	0°
45°	7.5
46°	6.0
47°	4.9
48°	4.1
49°	3.5
50°	3.1
51°	2.8
52°	2.6
53°	2.4
54°	2.3
55°	2.1
56°	2.1
57°	2.1
58°	2.0
59°	2.0
60°	2.0
61°	1.9
62°	1.9
63°	1.9
64°	1.9
65°	1.9
66°	1.9
67°	1.9
68°	1.9
69°	1.9
70°	1.8
71°	1.8
72°	1.8
73°	1.7
74°	1.6
75°	1.6
76°	1.6
77°	1.5
78°	1.5
79°	1.4
80°	1.4
81°	1.4
82°	1.3
83°	1.2
84°	1.0
85°	0.8
86°	0.5
87°	0.1
88°	0.1
89°	0.0



TEST NUMBER: P981014

CATALOG NUMBER: PRLX-CYL3S-10-930-15L-MD-U-S-X-X-WHTE

CANDELA DISTRIBUTION (continued):

90° | $\frac{0^\circ}{0.0}$



TEST NUMBER: P981014
 CATALOG NUMBER: PRLX-CYL3S-10-930-15L-MD-U-S-X-X-WHTE

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.14	0.51	0.00	0.00	0.00	0.14	0.51
	4H	0.37	1.09	0.78	1.45	1.84	0.37	1.09	0.78	1.45	1.84
	6H	1.82	2.48	2.24	2.86	3.26	1.82	2.48	2.24	2.86	3.26
	8H	2.58	3.19	3.01	3.58	4.00	2.58	3.19	3.01	3.58	4.00
	12H	2.95	3.54	3.39	3.93	4.36	2.95	3.54	3.39	3.93	4.36
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.09	0.68	0.50	1.09	1.49	0.09	0.68	0.50	1.09	1.49
	4H	1.60	2.13	2.04	2.55	3.00	1.60	2.13	2.04	2.55	3.00
	6H	3.23	3.67	3.70	4.13	4.60	3.23	3.67	3.70	4.13	4.60
	8H	4.05	4.47	4.53	4.92	5.40	4.05	4.47	4.53	4.92	5.40
	12H	4.56	4.92	5.06	5.41	5.89	4.56	4.92	5.06	5.41	5.89
8H	4H	2.16	2.57	2.64	3.03	3.50	2.16	2.57	2.64	3.03	3.50
	6H	4.04	4.36	4.55	4.87	5.36	4.04	4.36	4.55	4.87	5.36
	8H	5.03	5.31	5.56	5.84	6.34	5.03	5.31	5.56	5.84	6.34
	12H	5.70	5.94	6.22	6.44	7.03	5.70	5.94	6.22	6.44	7.03
12H	4H	2.29	2.64	2.78	3.13	3.61	2.29	2.64	2.78	3.13	3.61
	6H	4.26	4.55	4.80	5.07	5.57	4.26	4.55	4.80	5.07	5.57
	8H	5.34	5.58	5.86	6.08	6.66	5.34	5.58	5.86	6.08	6.66