

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P981021

Luminaire Tested: PRLX-CYL3S-10-935-10L-FL-U-S-X-X-WHTE

Issue Date: 4/11/2025

Test Information

Test Method: LM-79-2024
Report Number: P981021
TEST IS SCALED FROM (FO44194.PSO)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/11/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PentaLux
Catalog Number: PRLX-CYL3S-10-935-10L-FL-U-S-X-X-WHTE
Description: PentaLux 3-INCH CYLINDER, FLOOD OPTIC
1000 LUMENS
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 969.8 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.62
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P981021

CATALOG NUMBER: PRLX-CYL3S-10-935-10L-FL-U-S-X-X-WHTE

Luminous Intensity Polar Plot





TEST NUMBER: P981021

CATALOG NUMBER: PRLX-CYL3S-10-935-10L-FL-U-S-X-X-WHTE

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	86
4	101	95	91	87	100	94	90	87	92	88	86	90	87	85	88	86	84	82
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79
6	94	87	82	78	93	86	81	78	84	80	77	83	80	77	82	79	76	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69
9	84	76	71	68	83	76	71	68	75	70	68	74	70	67	73	70	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	64	63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	516055
5°	485339
10°	407674
15°	308106
20°	232257
25°	161163
30°	93812
35°	25698
40°	5954
45°	1892
50°	1160
55°	803
60°	614
65°	571
70°	577
75°	678
80°	884
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1892 cd/sqm

TEST NUMBER: P981021

CATALOG NUMBER: PRLX-CYL3S-10-935-10L-FL-U-S-X-X-WHTE

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	198.5	20.5
10°-20°	377.9	39.0
20°-30°	303.4	31.3
30°-40°	79.3	8.2
40°-50°	6.3	0.6
50°-60°	2.0	0.2
60°-70°	1.1	0.1
70°-80°	0.8	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	879.9	90.7
0°-40°	959.2	98.9
0°-60°	967.5	99.8
0°-90°	969.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	969.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2353	
5°	2205	199
15°	1357	378
25°	666	303
35°	96	79
45°	6	6
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P981021

CATALOG NUMBER: PRLX-CYL3S-10-935-10L-FL-U-S-X-X-WHTE

CANDELA DISTRIBUTION (FULL):

0°	
0°	2353.4
1°	2346.8
2°	2327.5
3°	2297.3
4°	2255.6
5°	2204.9
6°	2146.3
7°	2079.1
8°	2004.3
9°	1921.8
10°	1830.9
11°	1734.4
12°	1634.7
13°	1536.3
14°	1444.4
15°	1357.2
16°	1276.6
17°	1199.6
18°	1127.9
19°	1060.1
20°	995.3
21°	930.6
22°	867.7
23°	797.7
24°	730.3
25°	666.1
26°	605.0
27°	545.5
28°	490.1
29°	433.0
30°	370.5
31°	306.0
32°	244.0
33°	187.2
34°	137.2
35°	96.0
36°	66.2
37°	45.0
38°	32.5
39°	25.9
40°	20.8
41°	16.5
42°	13.0
43°	10.0
44°	7.7

TEST NUMBER: P981021

CATALOG NUMBER: PRLX-CYL3S-10-935-10L-FL-U-S-X-X-WHTE

CANDELA DISTRIBUTION (continued):

	0°
45°	6.1
46°	5.3
47°	4.7
48°	4.2
49°	3.8
50°	3.4
51°	3.0
52°	2.8
53°	2.5
54°	2.3
55°	2.1
56°	2.0
57°	1.8
58°	1.7
59°	1.5
60°	1.4
61°	1.3
62°	1.3
63°	1.2
64°	1.1
65°	1.1
66°	1.0
67°	1.0
68°	1.0
69°	1.0
70°	0.9
71°	0.9
72°	0.9
73°	0.9
74°	0.8
75°	0.8
76°	0.8
77°	0.7
78°	0.7
79°	0.7
80°	0.7
81°	0.6
82°	0.6
83°	0.5
84°	0.4
85°	0.3
86°	0.2
87°	0.1
88°	0.0
89°	0.0



TEST NUMBER: P981021

CATALOG NUMBER: PRLX-CYL3S-10-935-10L-FL-U-S-X-X-WHTE

CANDELA DISTRIBUTION (continued):

90° | $\frac{0^\circ}{0.0}$

TEST NUMBER: P981021
 CATALOG NUMBER: PRLX-CYL3S-10-935-10L-FL-U-S-X-X-WHTE

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.09	0.00	0.47	0.87	0.00	0.09	0.00	0.47	0.87
	8H	0.00	0.50	0.32	0.89	1.30	0.00	0.50	0.32	0.89	1.30
	12H	0.06	0.65	0.49	1.03	1.46	0.06	0.65	0.49	1.03	1.46
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.28	0.73	0.00	0.00	0.00	0.28	0.73
	6H	0.51	0.95	0.98	1.40	1.88	0.51	0.95	0.98	1.40	1.88
	8H	1.05	1.46	1.53	1.92	2.39	1.05	1.46	1.53	1.92	2.39
	12H	1.33	1.68	1.82	2.17	2.65	1.33	1.68	1.82	2.17	2.65
8H	4H	0.00	0.09	0.16	0.55	1.02	0.00	0.09	0.16	0.55	1.02
	6H	1.11	1.44	1.62	1.94	2.43	1.11	1.44	1.62	1.94	2.43
	8H	1.81	2.09	2.34	2.62	3.12	1.81	2.09	2.34	2.62	3.12
	12H	2.21	2.46	2.74	2.96	3.54	2.21	2.46	2.74	2.96	3.54
12H	4H	0.00	0.10	0.24	0.59	1.07	0.00	0.10	0.24	0.59	1.07
	6H	1.26	1.55	1.80	2.07	2.57	1.26	1.55	1.80	2.07	2.57
	8H	2.03	2.28	2.56	2.78	3.36	2.03	2.28	2.56	2.78	3.36