

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503791

Luminaire Tested: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-OT (3000K-1000LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503791
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-10)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-OT (3000K-1000LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN TAPERED, WHITE REFLECTOR
LIGHT LEVEL 3 - 1000 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3000K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 621.2 lumens
Efficiency: N/A
Efficacy: 57.0 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 10.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503791

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-OT (3000K-1000LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503791

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-OT (3000K-1000LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	105	101	98	107	103	99	96	99	96	93	95	92	90	91	89	87	85								
2	101	93	87	81	98	91	85	80	87	83	78	84	80	77	81	78	75	73								
3	92	83	75	69	90	81	74	68	78	72	67	75	70	66	73	69	65	63								
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55								
5	79	67	59	52	77	66	58	52	64	57	52	62	56	51	60	55	50	48								
6	73	61	53	46	72	60	52	46	58	51	46	57	50	46	55	49	45	43								
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39								
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35								
9	60	47	40	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32								
10	57	44	36	31	55	43	36	31	42	36	31	42	35	31	41	35	31	29								

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	9195
5°	9196
10°	9168
15°	9082
20°	8768
25°	8326
30°	7762
35°	7134
40°	6449
45°	5743
50°	5018
55°	4425
60°	4231
65°	4261
70°	4274
75°	4230
80°	3978
85°	3432

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5743 cd/sqm

TEST NUMBER: P1503791

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-OT (3000K-1000LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.2	4.5
10°-20°	79.8	12.8
20°-30°	112.2	18.1
30°-40°	118.3	19.0
40°-50°	101.7	16.4
50°-60°	75.1	12.1
60°-70°	57.6	9.3
70°-80°	37.2	6.0
80°-90°	11.1	1.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	220.2	35.4
0°-40°	338.5	54.5
0°-60°	515.2	82.9
0°-90°	621.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	621.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	298	
5°	297	28
15°	284	80
25°	245	112
35°	190	118
45°	132	102
55°	82	75
65°	58	58
75°	36	37
85°	10	11
90°	0	

TEST NUMBER: P1503791

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-OT (3000K-1000LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	298.2
2.5°	297.9
5°	297.1
7.5°	295.2
10°	292.8
12.5°	289.6
15°	284.5
17.5°	276.7
20°	267.2
22.5°	256.5
25°	244.7
27.5°	231.8
30°	218.0
32.5°	203.6
35°	189.5
37.5°	175.3
40°	160.2
42.5°	146.0
45°	131.7
47.5°	118.0
50°	104.6
52.5°	93.0
55°	82.3
57.5°	74.4
60°	68.6
62.5°	63.4
65°	58.4
67.5°	53.0
70°	47.4
72.5°	41.7
75°	35.5
77.5°	29.0
80°	22.4
82.5°	16.1
85°	9.7
87.5°	3.8
90°	0.0

(END OF REPORT)