

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503808

Luminaire Tested: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (3000K-800LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503808
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-8)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (3000K-800LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, NO DIFFUSER, BRONZE REFLECTOR
LIGHT LEVEL 2 - 800 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 583.2 lumens
Efficiency: N/A
Efficacy: 66.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.22 / 1.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 8.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503808

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (3000K-800LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503808

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (3000K-800LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80			
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	72	71			
4	90	80	73	67	88	79	72	67	76	71	66	74	69	65	72	68	64	63			
5	83	73	65	60	82	72	65	59	70	63	59	68	62	58	66	61	58	56			
6	78	66	59	53	76	65	58	53	64	57	52	62	56	52	61	56	52	50			
7	72	61	53	48	71	60	53	48	58	52	47	57	51	47	56	51	47	45			
8	68	56	48	43	66	55	48	43	54	47	43	53	47	42	52	46	42	41			
9	64	51	44	39	62	51	44	39	50	43	39	49	43	39	48	42	39	37			
10	60	48	41	36	59	47	40	36	46	40	36	45	40	35	45	39	35	34			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	9319
5°	9311
10°	9290
15°	9252
20°	9106
25°	9020
30°	8802
35°	8530
40°	7906
45°	7008
50°	5800
55°	4285
60°	2627
65°	803
70°	126
75°	167
80°	249
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7008 cd/sqm

TEST NUMBER: P1503808

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (3000K-800LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.6	4.9
10°-20°	81.6	14.0
20°-30°	121.8	20.9
30°-40°	140.5	24.1
40°-50°	122.7	21.0
50°-60°	71.6	12.3
60°-70°	14.7	2.5
70°-80°	1.5	0.3
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	232.0	39.8
0°-40°	372.5	63.9
0°-60°	566.8	97.2
0°-90°	583.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	583.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	302	
5°	301	29
15°	290	82
25°	265	122
35°	227	141
45°	161	123
55°	80	72
65°	11	15
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1503808

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRNZ-XX-ND (3000K-800LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	302.2
2.5°	302.2
5°	300.8
7.5°	299.4
10°	296.7
12.5°	293.9
15°	289.8
17.5°	284.3
20°	277.5
22.5°	272.0
25°	265.1
27.5°	256.9
30°	247.2
32.5°	239.0
35°	226.6
37.5°	211.5
40°	196.4
42.5°	178.6
45°	160.7
47.5°	140.1
50°	120.9
52.5°	100.3
55°	79.7
57.5°	60.4
60°	42.6
62.5°	24.7
65°	11.0
67.5°	2.7
70°	1.4
72.5°	1.4
75°	1.4
77.5°	1.4
80°	1.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)