

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503866

Luminaire Tested: PRLX-SM4-03-LS-FS-D2W-XXXX-BRSS-XX-OC (3000K-1000LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503866
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-15)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-D2W-XXXX-BRSS-XX-OC (3000K-1000LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN CYLINDER, BRASS REFLECTOR
LIGHT LEVEL 3 - 1000 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 783.4 lumens
Efficiency: N/A
Efficacy: 68.1 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 11.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503866

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRSS-XX-OC (3000K-1000LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503866

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRSS-XX-OC (3000K-1000LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87		
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76		
3	94	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	68	66		
4	88	77	69	63	85	76	69	63	73	67	62	71	66	61	69	64	61	59		
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52		
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47		
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42		
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38		
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35		
10	59	46	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	13300
5°	13295
10°	13226
15°	12744
20°	12106
25°	11401
30°	10597
35°	9727
40°	8751
45°	7697
50°	6500
55°	5269
60°	4175
65°	3772
70°	3534
75°	3396
80°	3161
85°	2512

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7697 cd/sqm

TEST NUMBER: P1503866

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRSS-XX-OC (3000K-1000LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.8	5.2
10°-20°	112.0	14.3
20°-30°	153.9	19.6
30°-40°	161.2	20.6
40°-50°	136.1	17.4
50°-60°	88.9	11.4
60°-70°	51.6	6.6
70°-80°	30.1	3.8
80°-90°	8.7	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	306.8	39.2
0°-40°	468.0	59.7
0°-60°	693.0	88.5
0°-90°	783.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	783.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	431	
5°	430	41
15°	399	112
25°	335	154
35°	258	161
45°	176	136
55°	98	89
65°	52	52
75°	28	30
85°	7	9
90°	0	

TEST NUMBER: P1503866

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRSS-XX-OC (3000K-1000LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	431.3
2.5°	431.3
5°	429.5
7.5°	427.8
10°	422.4
12.5°	411.7
15°	399.2
17.5°	385.0
20°	368.9
22.5°	352.9
25°	335.1
27.5°	317.3
30°	297.6
32.5°	278.0
35°	258.4
37.5°	238.8
40°	217.4
42.5°	197.8
45°	176.5
47.5°	156.8
50°	135.5
52.5°	117.6
55°	98.0
57.5°	82.0
60°	67.7
62.5°	57.0
65°	51.7
67.5°	46.3
70°	39.2
72.5°	33.9
75°	28.5
77.5°	23.2
80°	17.8
82.5°	12.5
85°	7.1
87.5°	3.6
90°	0.0

(END OF REPORT)