

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503897

Luminaire Tested: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-ND (3000K-650LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503897
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-7)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-ND (3000K-650LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, NO DIFFUSER, WHITE REFLECTOR
LIGHT LEVEL 1 - 650 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 607.0 lumens
Efficiency: N/A
Efficacy: 88.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.3
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 6.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503897

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-ND (3000K-650LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503897

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-ND (3000K-650LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88		
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76		
3	94	85	78	72	92	83	77	72	81	75	70	78	73	69	76	71	68	66		
4	87	76	69	63	85	75	68	62	73	66	61	70	65	61	68	64	60	58		
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51		
6	75	63	54	49	73	62	54	48	60	53	48	58	52	48	57	51	47	45		
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	41		
8	65	52	44	39	63	52	44	39	50	44	39	49	43	38	48	42	38	36		
9	61	48	41	35	59	48	40	35	47	40	35	46	39	35	45	39	35	33		
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	41	36	32	30		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	8511
5°	8509
10°	8470
15°	8431
20°	8381
25°	8285
30°	8168
35°	7984
40°	7536
45°	6890
50°	6021
55°	5005
60°	3737
65°	2444
70°	1947
75°	1930
80°	1918
85°	1521

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6890 cd/sqm

TEST NUMBER: P1503897

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-ND (3000K-650LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.1	4.3
10°-20°	74.5	12.3
20°-30°	112.1	18.5
30°-40°	131.8	21.7
40°-50°	121.2	20.0
50°-60°	82.9	13.7
60°-70°	36.0	5.9
70°-80°	17.1	2.8
80°-90°	5.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	212.7	35.0
0°-40°	344.5	56.8
0°-60°	548.6	90.4
0°-90°	607.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	607.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	276	
5°	275	26
15°	264	75
25°	244	112
35°	212	132
45°	158	121
55°	93	83
65°	34	36
75°	16	17
85°	4	5
90°	0	

TEST NUMBER: P1503897

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-ND (3000K-650LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	276.0
2.5°	274.9
5°	274.9
7.5°	272.7
10°	270.5
12.5°	268.4
15°	264.1
17.5°	259.7
20°	255.4
22.5°	248.9
25°	243.5
27.5°	237.0
30°	229.4
32.5°	221.8
35°	212.1
37.5°	200.2
40°	187.2
42.5°	173.1
45°	158.0
47.5°	141.8
50°	125.5
52.5°	109.3
55°	93.1
57.5°	76.8
60°	60.6
62.5°	46.5
65°	33.5
67.5°	24.9
70°	21.6
72.5°	18.4
75°	16.2
77.5°	14.1
80°	10.8
82.5°	7.6
85°	4.3
87.5°	2.2
90°	0.0

(END OF REPORT)