

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503898

Luminaire Tested: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-ND (3000K-800LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503898
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-7)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-ND (3000K-800LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, NO DIFFUSER, WHITE REFLECTOR
LIGHT LEVEL 2 - 800 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 770.5 lumens
Efficiency: N/A
Efficacy: 87.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.3
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 8.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503898

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-ND (3000K-800LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503898

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-ND (3000K-800LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88		
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76		
3	94	85	78	72	92	83	77	72	81	75	70	78	73	69	76	71	68	66		
4	87	76	69	63	85	75	68	62	73	66	61	70	65	61	68	64	60	58		
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51		
6	75	63	54	49	73	62	54	48	60	53	48	58	52	48	57	51	47	45		
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	41		
8	65	52	44	39	63	52	44	39	50	44	39	49	43	38	48	42	38	36		
9	61	48	41	35	59	48	40	35	47	40	35	46	39	35	45	39	35	33		
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	41	36	32	30		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	10802
5°	10800
10°	10753
15°	10698
20°	10639
25°	10513
30°	10369
35°	10134
40°	9564
45°	8744
50°	7642
55°	6349
60°	4743
65°	3108
70°	2479
75°	2454
80°	2433
85°	1946

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8744 cd/sqm

TEST NUMBER: P1503898

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-ND (3000K-800LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.1	4.3
10°-20°	94.6	12.3
20°-30°	142.3	18.5
30°-40°	167.3	21.7
40°-50°	153.8	20.0
50°-60°	105.2	13.7
60°-70°	45.7	5.9
70°-80°	21.8	2.8
80°-90°	6.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	270.0	35.0
0°-40°	437.3	56.8
0°-60°	696.3	90.4
0°-90°	770.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	770.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	350	
5°	349	33
15°	335	95
25°	309	142
35°	269	167
45°	200	154
55°	118	105
65°	43	46
75°	21	22
85°	6	7
90°	0	

TEST NUMBER: P1503898

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-ND (3000K-800LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	350.3
2.5°	348.9
5°	348.9
7.5°	346.1
10°	343.4
12.5°	340.6
15°	335.1
17.5°	329.7
20°	324.2
22.5°	315.9
25°	309.0
27.5°	300.8
30°	291.2
32.5°	281.6
35°	269.2
37.5°	254.1
40°	237.6
42.5°	219.8
45°	200.5
47.5°	179.9
50°	159.3
52.5°	138.7
55°	118.1
57.5°	97.5
60°	76.9
62.5°	59.1
65°	42.6
67.5°	31.6
70°	27.5
72.5°	23.4
75°	20.6
77.5°	17.9
80°	13.7
82.5°	9.6
85°	5.5
87.5°	2.7
90°	0.0

(END OF REPORT)