

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503926

Luminaire Tested: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OT (3000K-1000LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503926
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-10)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OT (3000K-1000LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN TAPERED, WHITE REFLECTOR
LIGHT LEVEL 3 - 1000 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3000K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 695.4 lumens
Efficiency: N/A
Efficacy: 60.5 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 11.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503926

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OT (3000K-1000LM)

Luminous Intensity Polar Plot



TEST NUMBER: P1503926

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OT (3000K-1000LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20						20
RC	80					70					50					30					10	0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10	0
RCR																						
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102	100
1	110	105	101	98		107	103	99	96		99	96	93		95	92	90		91	89	87	85
2	101	93	87	81		98	91	85	80		87	83	78		84	80	77		81	78	75	73
3	92	83	75	69		90	81	74	68		78	72	67		75	70	66		73	69	65	63
4	85	74	66	60		83	73	65	59		70	64	58		68	62	58		66	61	57	55
5	79	67	59	52		77	66	58	52		64	57	52		62	56	51		60	55	50	48
6	73	61	53	46		72	60	52	46		58	51	46		57	50	46		55	49	45	43
7	68	56	47	42		67	55	47	42		53	46	41		52	46	41		51	45	41	39
8	64	51	43	38		63	51	43	38		49	42	37		48	42	37		47	41	37	35
9	60	47	40	34		59	47	39	34		46	39	34		45	38	34		44	38	34	32
10	57	44	36	31		55	43	36	31		42	36	31		42	35	31		41	35	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	10293
5°	10295
10°	10264
15°	10168
20°	9815
25°	9319
30°	8688
35°	7984
40°	7218
45°	6428
50°	5618
55°	4951
60°	4736
65°	4772
70°	4787
75°	4730
80°	4457
85°	3856

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6428 cd/sqm

TEST NUMBER: P1503926

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OT (3000K-1000LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.6	4.5
10°-20°	89.3	12.8
20°-30°	125.6	18.1
30°-40°	132.4	19.0
40°-50°	113.8	16.4
50°-60°	84.1	12.1
60°-70°	64.5	9.3
70°-80°	41.7	6.0
80°-90°	12.4	1.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	246.5	35.4
0°-40°	378.9	54.5
0°-60°	576.7	82.9
0°-90°	695.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	695.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	334	
5°	333	32
15°	318	89
25°	274	126
35°	212	132
45°	147	114
55°	92	84
65°	65	65
75°	40	42
85°	11	12
90°	0	

TEST NUMBER: P1503926

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OT (3000K-1000LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	333.8
2.5°	333.5
5°	332.6
7.5°	330.4
10°	327.8
12.5°	324.2
15°	318.5
17.5°	309.8
20°	299.1
22.5°	287.1
25°	273.9
27.5°	259.5
30°	244.0
32.5°	228.0
35°	212.1
37.5°	196.2
40°	179.3
42.5°	163.4
45°	147.4
47.5°	132.1
50°	117.1
52.5°	104.1
55°	92.1
57.5°	83.2
60°	76.8
62.5°	70.9
65°	65.4
67.5°	59.4
70°	53.1
72.5°	46.7
75°	39.7
77.5°	32.4
80°	25.1
82.5°	18.0
85°	10.9
87.5°	4.3
90°	0.0

(END OF REPORT)