

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503704

Luminaire Tested: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OT (3500K-1000LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503704
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-11)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OT (3500K-1000LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN TAPERED, BRONZE REFLECTOR
LIGHT LEVEL 3 - 1000 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3500K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 506.5 lumens
Efficiency: N/A
Efficacy: 46.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 10.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503704

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OT (3500K-1000LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503704

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OT (3500K-1000LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	105	102	98	107	103	100	96	99	96	93	95	93	91	92	90	88	86		
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74		
3	93	83	76	70	91	82	75	69	79	73	68	76	71	67	74	70	66	64		
4	86	75	67	61	84	74	66	60	71	65	60	69	63	59	67	62	58	56		
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50		
6	74	62	54	48	72	61	53	48	59	52	47	58	52	47	56	51	46	45		
7	69	57	49	43	68	56	48	43	55	48	43	53	47	42	52	46	42	40		
8	65	52	44	39	63	52	44	39	50	44	39	49	43	38	48	42	38	36		
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33		
10	57	45	38	33	56	45	37	33	44	37	32	43	37	32	42	36	32	31		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	8033
5°	8033
10°	8000
15°	7892
20°	7554
25°	7087
30°	6545
35°	5933
40°	5257
45°	4557
50°	3876
55°	3312
60°	3158
65°	3247
70°	3300
75°	3300
80°	3125
85°	2724

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4557 cd/sqm

TEST NUMBER: P1503704

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OT (3500K-1000LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.6	4.9
10°-20°	69.2	13.7
20°-30°	95.6	18.9
30°-40°	98.2	19.4
40°-50°	80.8	16.0
50°-60°	56.5	11.2
60°-70°	43.8	8.7
70°-80°	29.0	5.7
80°-90°	8.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	189.4	37.4
0°-40°	287.7	56.8
0°-60°	425.0	83.9
0°-90°	506.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	506.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	260	
5°	260	25
15°	247	69
25°	208	96
35°	158	98
45°	104	81
55°	62	56
65°	44	44
75°	28	29
85°	8	9
90°	0	

TEST NUMBER: P1503704

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OT (3500K-1000LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	260.5
2.5°	260.3
5°	259.5
7.5°	257.9
10°	255.5
12.5°	252.1
15°	247.2
17.5°	239.5
20°	230.2
22.5°	219.8
25°	208.3
27.5°	196.3
30°	183.8
32.5°	170.7
35°	157.6
37.5°	144.2
40°	130.6
42.5°	117.6
45°	104.5
47.5°	92.5
50°	80.8
52.5°	70.2
55°	61.6
57.5°	55.2
60°	51.2
62.5°	48.0
65°	44.5
67.5°	40.6
70°	36.6
72.5°	32.3
75°	27.7
77.5°	22.7
80°	17.6
82.5°	12.5
85°	7.7
87.5°	2.9
90°	0.0

(END OF REPORT)