

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P979569

Luminaire Tested: PRLX-CYL6-940-62L-WD-U-S-X-X-WHTE

Issue Date: 4/3/2025

Test Information

Test Method: LM-79-2019
Report Number: P979569
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-353-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 4/3/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-CYL6-940-62L-WD-U-S-X-X-WHTE
Description: 3D PRINTED LUMINAIRE, INTEGRAL LED LIGHT ENGINE, WHITE TRIM WITH WIDE FLOOD OPTIC
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6307.8 lumens
Efficiency: N/A
Efficacy: 131.4 lumens/watt
Spacing Criteria (0/90/45): 1.05 / 1.05 / 0.91
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P979569

CATALOG NUMBER: PRLX-CYL6-940-62L-WD-U-S-X-X-WHTE

Luminous Intensity Polar Plot



TEST NUMBER: P979569

CATALOG NUMBER: PRLX-CYL6-940-62L-WD-U-S-X-X-WHTE

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20				
RC	80					70					50					30					10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10		
RCR																									
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100							
1	114	111	109	106	111	109	107	105	105	103	102	101	100	98	98	97	96	94							
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88							
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82							
4	98	91	86	82	96	90	85	81	88	83	80	86	82	79	84	81	78	77							
5	93	85	80	76	92	84	79	75	83	78	75	81	77	74	79	76	73	72							
6	89	80	75	70	87	80	74	70	78	73	70	77	72	69	75	72	69	67							
7	85	76	70	66	83	75	70	66	74	69	65	73	68	65	71	68	65	63							
8	81	71	66	62	79	71	65	62	70	65	61	69	64	61	68	64	61	59							
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56							
10	73	64	58	55	72	64	58	54	63	58	54	62	57	54	61	57	54	53							

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	68536
5°	67941
10°	66341
15°	66647
20°	65696
25°	63527
30°	48060
35°	22446
40°	4236
45°	1794
50°	938
55°	616
60°	417
65°	245
70°	303
75°	323
80°	360
85°	474

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1794 cd/sqm

TEST NUMBER: P979569

CATALOG NUMBER: PRLX-CYL6-940-62L-WD-U-S-X-X-WHTE

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	633.1	10.0
10°-20°	1796.0	28.5
20°-30°	2508.1	39.8
30°-40°	1202.8	19.1
40°-50°	110.9	1.8
50°-60°	31.9	0.5
60°-70°	12.5	0.2
70°-80°	8.8	0.1
80°-90°	3.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4937.3	78.3
0°-40°	6140.1	97.3
0°-60°	6282.9	99.6
0°-90°	6307.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6307.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6807	
5°	6722	633
15°	6394	1796
25°	5718	2508
35°	1826	1203
45°	126	111
55°	35	32
65°	10	12
75°	8	9
85°	4	4
90°	0	

TEST NUMBER: P979569

CATALOG NUMBER: PRLX-CYL6-940-62L-WD-U-S-X-X-WHTE

CANDELA DISTRIBUTION (FULL):

0°	
0°	6806.6
2.5°	6790.1
5°	6721.9
7.5°	6589.7
10°	6488.5
12.5°	6480.2
15°	6393.5
17.5°	6242.7
20°	6131.1
22.5°	6067.1
25°	5718.0
27.5°	4997.0
30°	4133.6
32.5°	3026.3
35°	1826.1
37.5°	890.3
40°	322.3
42.5°	181.8
45°	126.0
47.5°	86.8
50°	59.9
52.5°	43.4
55°	35.1
57.5°	24.8
60°	20.7
62.5°	14.5
65°	10.3
67.5°	10.3
70°	10.3
72.5°	8.3
75°	8.3
77.5°	8.3
80°	6.2
82.5°	4.1
85°	4.1
87.5°	2.1
90°	0.0

TEST NUMBER: P979569

CATALOG NUMBER: PRLX-CYL6-940-62L-WD-U-S-X-X-WHTE

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.19	0.00	0.00	0.00	0.00	0.19
	6H	0.00	0.07	0.00	0.44	0.84	0.00	0.07	0.00	0.44	0.84
	8H	0.00	0.21	0.01	0.60	1.01	0.00	0.21	0.01	0.60	1.01
	12H	0.00	0.40	0.23	0.78	1.22	0.00	0.40	0.23	0.78	1.22
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.18	0.63	0.00	0.00	0.00	0.18	0.63
	6H	0.15	0.61	0.62	1.06	1.53	0.15	0.61	0.62	1.06	1.53
	8H	0.40	0.82	0.87	1.27	1.75	0.40	0.82	0.87	1.27	1.75
	12H	0.71	1.08	1.21	1.57	2.05	0.71	1.08	1.21	1.57	2.05
8H	4H	0.00	0.00	0.00	0.38	0.86	0.00	0.00	0.00	0.38	0.86
	6H	0.60	0.93	1.11	1.43	1.92	0.60	0.93	1.11	1.43	1.92
	8H	0.94	1.23	1.47	1.76	2.26	0.94	1.23	1.47	1.76	2.26
	12H	1.42	1.68	1.95	2.18	2.76	1.42	1.68	1.95	2.18	2.76
12H	4H	0.00	0.00	0.02	0.38	0.86	0.00	0.00	0.02	0.38	0.86
	6H	0.65	0.95	1.19	1.47	1.97	0.65	0.95	1.19	1.47	1.97
	8H	1.07	1.33	1.60	1.83	2.41	1.07	1.33	1.60	1.83	2.41

END OF REPORT