

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503854

Luminaire Tested: PRLX-SM4-03-LS-FS-D2W-XXXX-BRSS-XX-ND (3500K-1000LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503854
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-9)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-D2W-XXXX-BRSS-XX-ND (3500K-1000LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, NO DIFFUSER, BRASS REFLECTOR
LIGHT LEVEL 3 - 1000 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3500K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 806.2 lumens
Efficiency: N/A
Efficacy: 70.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.22 / 1.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 11.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503854

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRSS-XX-ND (3500K-1000LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503854

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRSS-XX-ND (3500K-1000LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	90		
2	104	97	92	87	101	95	91	86	92	88	84	89	86	83	86	83	81	79		
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	71	70		
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	61		
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55		
6	77	65	58	52	75	65	57	52	63	56	51	61	55	51	60	55	51	49		
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44		
8	67	55	47	42	66	54	47	42	53	46	42	52	46	42	51	45	41	40		
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36		
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	38	34	33		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	12584
5°	12580
10°	12556
15°	12406
20°	12286
25°	12075
30°	11878
35°	11489
40°	10643
45°	9520
50°	8002
55°	6107
60°	3941
65°	1685
70°	802
75°	846
80°	622
85°	637

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9520 cd/sqm

TEST NUMBER: P1503854

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRSS-XX-ND (3500K-1000LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.6	4.8
10°-20°	109.7	13.6
20°-30°	163.8	20.3
30°-40°	189.3	23.5
40°-50°	167.1	20.7
50°-60°	101.8	12.6
60°-70°	27.2	3.4
70°-80°	6.8	0.8
80°-90°	1.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	312.1	38.7
0°-40°	501.4	62.2
0°-60°	770.4	95.6
0°-90°	806.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	806.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	408	
5°	406	39
15°	389	110
25°	355	164
35°	305	189
45°	218	167
55°	114	102
65°	23	27
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1503854

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-BRSS-XX-ND (3500K-1000LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	408.1
2.5°	406.4
5°	406.4
7.5°	402.8
10°	401.0
12.5°	395.7
15°	388.6
17.5°	381.5
20°	374.4
22.5°	365.5
25°	354.9
27.5°	346.0
30°	333.6
32.5°	321.2
35°	305.2
37.5°	285.7
40°	264.4
42.5°	241.3
45°	218.3
47.5°	193.4
50°	166.8
52.5°	140.2
55°	113.6
57.5°	88.7
60°	63.9
62.5°	40.8
65°	23.1
67.5°	10.6
70°	8.9
72.5°	7.1
75°	7.1
77.5°	5.3
80°	3.5
82.5°	3.5
85°	1.8
87.5°	0.0
90°	0.0

(END OF REPORT)