

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503930

Luminaire Tested: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OT (3500K-650LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503930
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-10)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-D2W-XXXX-WHITE-XX-OT (3500K-650LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN TAPERED, WHITE REFLECTOR
LIGHT LEVEL 1 - 650 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3500K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 420.4 lumens
Efficiency: N/A
Efficacy: 60.9 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 6.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503930

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OT (3500K-650LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503930

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHITE-XX-OT (3500K-650LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	105	101	98	107	103	99	96	99	96	93	95	92	90	91	89	87	85			
2	101	93	87	81	98	91	85	80	87	83	78	84	80	77	81	78	75	73			
3	92	83	75	69	90	81	74	68	78	72	67	75	70	66	73	69	65	63			
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55			
5	79	67	59	52	77	66	58	52	64	57	52	62	56	51	60	55	50	48			
6	73	61	53	46	72	60	52	46	58	51	46	57	50	46	55	49	45	43			
7	68	56	47	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39			
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35			
9	60	47	40	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32			
10	57	44	36	31	55	43	36	31	42	36	31	42	35	31	41	35	31	29			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6223
5°	6222
10°	6203
15°	6145
20°	5933
25°	5634
30°	5252
35°	4826
40°	4364
45°	3886
50°	3396
55°	2995
60°	2862
65°	2882
70°	2894
75°	2859
80°	2699
85°	2335

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3886 cd/sqm

TEST NUMBER: P1503930

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OT (3500K-650LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.1	4.5
10°-20°	54.0	12.8
20°-30°	76.0	18.1
30°-40°	80.0	19.0
40°-50°	68.8	16.4
50°-60°	50.8	12.1
60°-70°	39.0	9.3
70°-80°	25.2	6.0
80°-90°	7.5	1.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	149.0	35.5
0°-40°	229.0	54.5
0°-60°	348.6	82.9
0°-90°	420.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	420.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	202	
5°	201	19
15°	192	54
25°	166	76
35°	128	80
45°	89	69
55°	56	51
65°	40	39
75°	24	25
85°	7	8
90°	0	

TEST NUMBER: P1503930

CATALOG NUMBER: PRLX-SM4-03-LS-FS-D2W-XXXX-WHTE-XX-OT (3500K-650LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	201.8
2.5°	201.6
5°	201.0
7.5°	199.8
10°	198.1
12.5°	196.0
15°	192.5
17.5°	187.3
20°	180.8
22.5°	173.6
25°	165.6
27.5°	156.9
30°	147.5
32.5°	137.8
35°	128.2
37.5°	118.6
40°	108.4
42.5°	98.8
45°	89.1
47.5°	79.8
50°	70.8
52.5°	62.9
55°	55.7
57.5°	50.3
60°	46.4
62.5°	42.9
65°	39.5
67.5°	35.9
70°	32.1
72.5°	28.2
75°	24.0
77.5°	19.6
80°	15.2
82.5°	10.9
85°	6.6
87.5°	2.6
90°	0.0

(END OF REPORT)