

Scaled data based on original data using  
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503708

Luminaire Tested: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OT (4000K-650LM)

Issue Date: 7/28/2026

**Test Information**

Test Method: LM-79-2024  
Report Number: P1503708  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/28/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PrentaLux  
Catalog Number: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OT (4000K-650LM)  
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN TAPERED, BRONZE REFLECTOR  
LIGHT LEVEL 1 - 650 NOMINAL LUMENS  
Light Source: SELECTABLE CCT - 4000K CCT, 90 CRI  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 310.6 lumens  
Efficiency: N/A  
Efficacy: 47.8 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.14  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 6.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1503708

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OT (4000K-650LM)

### Luminous Intensity Polar Plot





TEST NUMBER: P1503708

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OT (4000K-650LM)

### COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |  |  |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|--|----|
| RF  | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |  |  | 20 |
| RC  | 80  |     |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |  |  | 0  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |  |  |    |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |  |  |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |  |  |    |
| 1   | 110 | 105 | 102 | 98  | 107 | 103 | 100 | 96  | 99  | 96  | 93  | 95  | 93  | 91  | 92  | 90  | 88  | 86  |  |  |    |
| 2   | 101 | 93  | 87  | 82  | 98  | 92  | 86  | 81  | 88  | 83  | 79  | 85  | 81  | 77  | 82  | 79  | 76  | 74  |  |  |    |
| 3   | 93  | 83  | 76  | 70  | 91  | 82  | 75  | 69  | 79  | 73  | 68  | 76  | 71  | 67  | 74  | 70  | 66  | 64  |  |  |    |
| 4   | 86  | 75  | 67  | 61  | 84  | 74  | 66  | 60  | 71  | 65  | 60  | 69  | 63  | 59  | 67  | 62  | 58  | 56  |  |  |    |
| 5   | 80  | 68  | 60  | 54  | 78  | 67  | 59  | 53  | 65  | 58  | 53  | 63  | 57  | 52  | 61  | 56  | 52  | 50  |  |  |    |
| 6   | 74  | 62  | 54  | 48  | 72  | 61  | 53  | 48  | 59  | 52  | 47  | 58  | 52  | 47  | 56  | 51  | 46  | 44  |  |  |    |
| 7   | 69  | 57  | 49  | 43  | 68  | 56  | 48  | 43  | 55  | 48  | 43  | 53  | 47  | 42  | 52  | 46  | 42  | 40  |  |  |    |
| 8   | 65  | 52  | 44  | 39  | 63  | 52  | 44  | 39  | 50  | 44  | 39  | 49  | 43  | 38  | 48  | 42  | 38  | 36  |  |  |    |
| 9   | 61  | 48  | 41  | 36  | 60  | 48  | 41  | 35  | 47  | 40  | 35  | 46  | 40  | 35  | 45  | 39  | 35  | 33  |  |  |    |
| 10  | 57  | 45  | 38  | 33  | 56  | 45  | 37  | 33  | 44  | 37  | 32  | 43  | 37  | 32  | 42  | 36  | 32  | 31  |  |  |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   |
|-----|------|
| 0°  | 4925 |
| 5°  | 4925 |
| 10° | 4907 |
| 15° | 4840 |
| 20° | 4634 |
| 25° | 4345 |
| 30° | 4013 |
| 35° | 3636 |
| 40° | 3220 |
| 45° | 2795 |
| 50° | 2375 |
| 55° | 2032 |
| 60° | 1937 |
| 65° | 1992 |
| 70° | 2029 |
| 75° | 2025 |
| 80° | 1918 |
| 85° | 1663 |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle:  $0^\circ$ 

Vertical Angle:  $45^\circ$

Luminance: 2795 cd/sqm

TEST NUMBER: P1503708

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OT (4000K-650LM)

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 15.1   | 4.9       |
| 10°-20°   | 42.4   | 13.7      |
| 20°-30°   | 58.6   | 18.9      |
| 30°-40°   | 60.2   | 19.4      |
| 40°-50°   | 49.6   | 16.0      |
| 50°-60°   | 34.6   | 11.2      |
| 60°-70°   | 26.9   | 8.7       |
| 70°-80°   | 17.8   | 5.7       |
| 80°-90°   | 5.3    | 1.7       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 116.2  | 37.4      |
| 0°-40°    | 176.4  | 56.8      |
| 0°-60°    | 260.6  | 83.9      |
| 0°-90°    | 310.6  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 310.6  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 160 |      |
| 5°  | 159 | 15   |
| 15° | 152 | 42   |
| 25° | 128 | 59   |
| 35° | 97  | 60   |
| 45° | 64  | 50   |
| 55° | 38  | 35   |
| 65° | 27  | 27   |
| 75° | 17  | 18   |
| 85° | 5   | 5    |
| 90° | 0   |      |

TEST NUMBER: P1503708

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRNZ-XX-OT (4000K-650LM)

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 159.7 |
| 2.5°  | 159.6 |
| 5°    | 159.1 |
| 7.5°  | 158.1 |
| 10°   | 156.7 |
| 12.5° | 154.6 |
| 15°   | 151.6 |
| 17.5° | 146.8 |
| 20°   | 141.2 |
| 22.5° | 134.8 |
| 25°   | 127.7 |
| 27.5° | 120.4 |
| 30°   | 112.7 |
| 32.5° | 104.7 |
| 35°   | 96.6  |
| 37.5° | 88.4  |
| 40°   | 80.0  |
| 42.5° | 72.1  |
| 45°   | 64.1  |
| 47.5° | 56.7  |
| 50°   | 49.5  |
| 52.5° | 43.1  |
| 55°   | 37.8  |
| 57.5° | 33.8  |
| 60°   | 31.4  |
| 62.5° | 29.4  |
| 65°   | 27.3  |
| 67.5° | 24.9  |
| 70°   | 22.5  |
| 72.5° | 19.8  |
| 75°   | 17.0  |
| 77.5° | 13.9  |
| 80°   | 10.8  |
| 82.5° | 7.7   |
| 85°   | 4.7   |
| 87.5° | 1.8   |
| 90°   | 0.0   |

(END OF REPORT)