

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503564

Luminaire Tested: PRLX-SM4-01-LS-FS-D2W-XXXX-SMGY-VF (2700K-650LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503564
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-01-LS-FS-D2W-XXXX-SMGY-VF (2700K-650LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, ROUND, SMOKY GRAY LENS
LIGHT LEVEL 1 - 650 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 2700K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 166.6 lumens
Efficiency: N/A
Efficacy: 24.2 lumens/watt
Spacing Criteria (0/90/45): 4.81 / 4.81 / 4.13
Luminous Opening: Vertical Cylinder (Dia: 0.5' x H: 0.14')
CIE Type: Semi-Direct

Input Watts (W): 6.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503564

CATALOG NUMBER: PRLX-SM4-01-LS-FS-D2W-XXXX-SMGY-VF (2700K-650LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503564

CATALOG NUMBER: PRLX-SM4-01-LS-FS-D2W-XXXX-SMGY-VF (2700K-650LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	65		
1	96	89	84	78	90	84	78	74	73	69	65	63	60	57	54	52	49	45		
2	85	75	66	59	79	70	62	55	60	54	49	52	47	43	44	40	37	32		
3	76	63	54	46	70	59	50	43	51	44	38	43	38	33	37	32	28	24		
4	68	54	44	37	63	51	41	34	44	36	30	37	31	26	31	26	22	19		
5	62	47	37	30	57	44	35	28	38	30	24	32	26	21	27	22	18	14		
6	56	42	32	25	52	39	30	23	33	26	20	28	22	17	24	19	15	12		
7	52	37	27	21	48	34	26	19	30	22	17	25	19	15	21	16	12	9		
8	48	33	24	18	44	31	22	17	27	20	14	23	17	12	19	14	10	8		
9	44	30	21	15	41	28	20	14	24	17	12	21	15	11	17	12	9	6		
10	41	27	19	13	38	25	18	12	22	15	11	19	13	9	16	11	8	5		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	133
5°	146
10°	207
15°	304
20°	408
25°	531
30°	672
35°	816
40°	952
45°	1111
50°	1360
55°	1667
60°	1855
65°	1774
70°	1535
75°	1409
80°	1495
85°	1806

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 90°

Luminance: 2397 cd/sqm

TEST NUMBER: P1503564

CATALOG NUMBER: PRLX-SM4-01-LS-FS-D2W-XXXX-SMGY-VF (2700K-650LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.3	0.2
10°-20°	1.7	1.0
20°-30°	4.8	2.9
30°-40°	9.4	5.7
40°-50°	15.0	9.0
50°-60°	22.8	13.7
60°-70°	23.0	13.8
70°-80°	16.5	9.9
80°-90°	15.6	9.4
90°-100°	16.2	9.7
100°-110°	12.6	7.5
110°-120°	10.0	6.0
120°-130°	7.6	4.6
130°-140°	5.4	3.2
140°-150°	3.3	2.0
150°-160°	1.7	1.0
160°-170°	0.7	0.4
170°-180°	0.1	0.1
0°-30°	6.8	4.1
0°-40°	16.2	9.7
0°-60°	54.0	32.4
0°-90°	109.0	65.4
90°-120°	38.8	23.3
90°-150°	55.1	33.1
90°-180°	58.0	34.8
0°-180°	166.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2	
5°	3	0
15°	6	2
25°	10	5
35°	15	9
45°	19	15
55°	26	23
65°	24	23
75°	15	16
85°	14	12
90°	15	8
95°	15	12
105°	12	13
115°	10	10
125°	8	8
135°	7	5
145°	5	3
155°	4	2
165°	2	1
175°	1	0
180°	0	

TEST NUMBER: P1503564

CATALOG NUMBER: PRLX-SM4-01-LS-FS-D2W-XXXX-SMGY-VF (2700K-650LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	2.4
2.5°	2.4
5°	2.7
7.5°	3.2
10°	3.9
12.5°	4.8
15°	5.8
17.5°	6.8
20°	7.8
22.5°	9.0
25°	10.1
27.5°	11.3
30°	12.6
32.5°	13.8
35°	15.0
37.5°	16.1
40°	17.0
42.5°	17.9
45°	19.1
47.5°	20.5
50°	22.3
52.5°	24.2
55°	25.8
57.5°	26.8
60°	26.8
62.5°	25.5
65°	23.6
67.5°	21.1
70°	18.5
72.5°	16.7
75°	15.1
77.5°	14.4
80°	13.9
82.5°	13.9
85°	14.1
87.5°	14.7
90°	15.0
92.5°	15.4
95°	15.2
97.5°	14.6
100°	13.5
102.5°	12.5
105°	11.7
107.5°	11.2
110°	10.6

TEST NUMBER: P1503564

CATALOG NUMBER: PRLX-SM4-01-LS-FS-D2W-XXXX-SMGY-VF (2700K-650LM)

CANDELA DISTRIBUTION (continued):

	0°
112.5°	10.4
115°	10.0
117.5°	9.8
120°	9.4
122.5°	9.0
125°	8.4
127.5°	8.0
130°	7.7
132.5°	7.2
135°	6.9
137.5°	6.6
140°	6.1
142.5°	5.7
145°	5.3
147.5°	4.9
150°	4.5
152.5°	4.1
155°	3.6
157.5°	3.3
160°	3.0
162.5°	2.5
165°	2.4
167.5°	2.0
170°	1.9
172.5°	1.4
175°	0.8
177.5°	0.1
180°	0.0

(END OF REPORT)