

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503737

Luminaire Tested: PRLX-SM4-03-LS-FS-010-XXXX-BRSS-XX-OC (4000K-1000LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503737
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-15)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-010-XXXX-BRSS-XX-OC (4000K-1000LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN CYLINDER, BRASS REFLECTOR
LIGHT LEVEL 3 - 1000 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 4000K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 710.2 lumens
Efficiency: N/A
Efficacy: 65.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 10.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503737

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRSS-XX-OC (4000K-1000LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503737

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRSS-XX-OC (4000K-1000LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87		
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76		
3	94	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	68	66		
4	88	77	69	63	85	76	69	63	73	67	62	71	66	61	69	64	61	59		
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52		
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47		
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42		
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38		
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35		
10	59	46	39	34	57	46	39	34	45	39	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	12057
5°	12054
10°	11989
15°	11553
20°	10973
25°	10333
30°	9607
35°	8820
40°	7934
45°	6973
50°	5891
55°	4779
60°	3787
65°	3422
70°	3201
75°	3074
80°	2877
85°	2300

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6973 cd/sqm

TEST NUMBER: P1503737

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRSS-XX-OC (4000K-1000LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.0	5.2
10°-20°	101.5	14.3
20°-30°	139.5	19.6
30°-40°	146.2	20.6
40°-50°	123.4	17.4
50°-60°	80.6	11.4
60°-70°	46.8	6.6
70°-80°	27.3	3.8
80°-90°	7.9	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	278.1	39.2
0°-40°	424.2	59.7
0°-60°	628.2	88.5
0°-90°	710.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	710.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	391	
5°	389	37
15°	362	102
25°	304	140
35°	234	146
45°	160	123
55°	89	81
65°	47	47
75°	26	27
85°	6	8
90°	0	

TEST NUMBER: P1503737

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRSS-XX-OC (4000K-1000LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	391.0
2.5°	391.0
5°	389.4
7.5°	387.7
10°	382.9
12.5°	373.2
15°	361.9
17.5°	349.0
20°	334.4
22.5°	319.9
25°	303.7
27.5°	287.6
30°	269.8
32.5°	252.0
35°	234.3
37.5°	216.5
40°	197.1
42.5°	179.3
45°	159.9
47.5°	142.2
50°	122.8
52.5°	106.6
55°	88.9
57.5°	74.3
60°	61.4
62.5°	51.7
65°	46.9
67.5°	42.0
70°	35.5
72.5°	30.7
75°	25.8
77.5°	21.0
80°	16.2
82.5°	11.3
85°	6.5
87.5°	3.2
90°	0.0

(END OF REPORT)