

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503754

Luminaire Tested: PRLX-SM4-03-LS-FS-010-XXXX-BRSS-XX-OT (4000K-800LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503754
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-12)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-010-XXXX-BRSS-XX-OT (4000K-800LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN TAPERED, BRASS REFLECTOR
LIGHT LEVEL 2 - 800 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 4000K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 412.3 lumens
Efficiency: N/A
Efficacy: 50.3 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 8.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503754

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRSS-XX-OT (4000K-800LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503754

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRSS-XX-OT (4000K-800LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20				
RC	80					70					50					30					10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10		
RCR																									
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100							
1	110	105	101	98	107	103	100	96	99	96	93	95	93	90	91	90	88	86							
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74							
3	93	83	76	70	91	82	75	69	79	73	68	76	71	67	74	69	66	64							
4	86	75	67	61	84	74	66	60	71	65	60	69	63	59	67	62	58	56							
5	80	68	60	53	78	67	59	53	65	58	53	63	57	52	61	56	52	50							
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44							
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40							
8	65	52	44	39	63	51	44	39	50	43	38	49	43	38	48	42	38	36							
9	61	48	41	35	59	48	40	35	47	40	35	46	39	35	45	39	35	33							
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30							

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6473
5°	6476
10°	6444
15°	6362
20°	6100
25°	5733
30°	5295
35°	4815
40°	4291
45°	3724
50°	3185
55°	2731
60°	2609
65°	2671
70°	2705
75°	2681
80°	2539
85°	2158

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3724 cd/sqm

TEST NUMBER: P1503754

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRSS-XX-OT (4000K-800LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.9	4.8
10°-20°	55.8	13.5
20°-30°	77.3	18.7
30°-40°	79.7	19.3
40°-50°	66.1	16.0
50°-60°	46.7	11.3
60°-70°	36.1	8.8
70°-80°	23.7	5.7
80°-90°	7.0	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	153.0	37.1
0°-40°	232.7	56.4
0°-60°	345.5	83.8
0°-90°	412.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	412.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	210	
5°	209	20
15°	199	56
25°	168	77
35°	128	80
45°	85	66
55°	51	47
65°	37	36
75°	22	24
85°	6	7
90°	0	

TEST NUMBER: P1503754

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-BRSS-XX-OT (4000K-800LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	209.9
2.5°	209.8
5°	209.2
7.5°	207.8
10°	205.8
12.5°	203.2
15°	199.3
17.5°	193.2
20°	185.9
22.5°	177.5
25°	168.5
27.5°	159.0
30°	148.7
32.5°	138.3
35°	127.9
37.5°	117.2
40°	106.6
42.5°	96.0
45°	85.4
47.5°	75.7
50°	66.4
52.5°	58.1
55°	50.8
57.5°	45.7
60°	42.3
62.5°	39.5
65°	36.6
67.5°	33.5
70°	30.0
72.5°	26.5
75°	22.5
77.5°	18.6
80°	14.3
82.5°	10.2
85°	6.1
87.5°	2.4
90°	0.0

(END OF REPORT)