

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503784

Luminaire Tested: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-OC (4000K-800LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503784
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-13)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-OC (4000K-800LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, OPEN CYLINDER, WHITE REFLECTOR
LIGHT LEVEL 2 - 800 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 4000K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 604.3 lumens
Efficiency: N/A
Efficacy: 73.7 lumens/watt
Spacing Criteria (0/90/45): 1.07 / 1.07 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 8.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503784

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-OC (4000K-800LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503784

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-OC (4000K-800LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76			
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66			
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	52			
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34			
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	10022
5°	9983
10°	9901
15°	9580
20°	9110
25°	8598
30°	8026
35°	7405
40°	6714
45°	5974
50°	5138
55°	4285
60°	3454
65°	3086
70°	2921
75°	2669
80°	2433
85°	2194

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5974 cd/sqm

TEST NUMBER: P1503784

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-OC (4000K-800LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.6	5.1
10°-20°	84.1	13.9
20°-30°	116.1	19.2
30°-40°	122.8	20.3
40°-50°	105.4	17.4
50°-60°	71.7	11.9
60°-70°	42.3	7.0
70°-80°	24.1	4.0
80°-90°	7.0	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	230.9	38.2
0°-40°	353.6	58.5
0°-60°	530.8	87.8
0°-90°	604.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	604.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	325	
5°	322	31
15°	300	84
25°	253	116
35°	197	123
45°	137	105
55°	80	72
65°	42	42
75°	22	24
85°	6	7
90°	0	

TEST NUMBER: P1503784

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-OC (4000K-800LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	325.0
2.5°	323.7
5°	322.5
7.5°	321.2
10°	316.2
12.5°	308.8
15°	300.1
17.5°	288.8
20°	277.6
22.5°	265.2
25°	252.7
27.5°	240.3
30°	225.4
32.5°	211.7
35°	196.7
37.5°	181.8
40°	166.8
42.5°	151.9
45°	137.0
47.5°	122.0
50°	107.1
52.5°	93.4
55°	79.7
57.5°	67.2
60°	56.0
62.5°	47.3
65°	42.3
67.5°	37.4
70°	32.4
72.5°	27.4
75°	22.4
77.5°	18.7
80°	13.7
82.5°	10.0
85°	6.2
87.5°	2.5
90°	0.0

(END OF REPORT)