

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503772

Luminaire Tested: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-ND (5000K-800LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503772
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-7)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-ND (5000K-800LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, DISC, NO DIFFUSER, WHITE REFLECTOR
LIGHT LEVEL 2 - 800 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 5000K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 718.8 lumens
Efficiency: N/A
Efficacy: 87.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.3
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 8.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503772

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-ND (5000K-800LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503772

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-ND (5000K-800LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88		
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76		
3	94	85	78	72	92	83	77	72	81	75	70	78	73	69	76	71	68	66		
4	87	76	69	63	85	75	68	62	73	66	61	70	65	61	68	64	60	58		
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51		
6	75	63	54	49	73	62	54	48	60	53	48	58	52	48	57	51	47	45		
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	41		
8	65	52	44	39	63	52	44	39	50	44	39	49	43	38	48	42	38	36		
9	61	48	41	35	59	48	40	35	47	40	35	46	39	35	45	39	35	33		
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	41	36	32	30		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	10074
5°	10076
10°	10029
15°	9979
20°	9923
25°	9809
30°	9671
35°	9452
40°	8924
45°	8159
50°	7129
55°	5925
60°	4428
65°	2897
70°	2308
75°	2288
80°	2273
85°	1804

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8159 cd/sqm

TEST NUMBER: P1503772

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-ND (5000K-800LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.9	4.3
10°-20°	88.3	12.3
20°-30°	132.7	18.5
30°-40°	156.0	21.7
40°-50°	143.5	20.0
50°-60°	98.2	13.7
60°-70°	42.6	5.9
70°-80°	20.3	2.8
80°-90°	6.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	251.9	35.0
0°-40°	407.9	56.7
0°-60°	649.6	90.4
0°-90°	718.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	718.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	327	
5°	326	31
15°	313	88
25°	288	133
35°	251	156
45°	187	143
55°	110	98
65°	40	43
75°	19	20
85°	5	6
90°	0	

TEST NUMBER: P1503772

CATALOG NUMBER: PRLX-SM4-03-LS-FS-010-XXXX-WHTE-XX-ND (5000K-800LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	326.7
2.5°	325.5
5°	325.5
7.5°	322.9
10°	320.3
12.5°	317.8
15°	312.6
17.5°	307.5
20°	302.4
22.5°	294.7
25°	288.3
27.5°	280.6
30°	271.6
32.5°	262.7
35°	251.1
37.5°	237.0
40°	221.7
42.5°	205.0
45°	187.1
47.5°	167.9
50°	148.6
52.5°	129.4
55°	110.2
57.5°	91.0
60°	71.8
62.5°	55.1
65°	39.7
67.5°	29.5
70°	25.6
72.5°	21.8
75°	19.2
77.5°	16.7
80°	12.8
82.5°	9.0
85°	5.1
87.5°	2.6
90°	0.0

(END OF REPORT)