

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503594

Luminaire Tested: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (2700K-650LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503594
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-6)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (2700K-650LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, RING, BRASS REFLECTOR
LIGHT LEVEL 1 - 650 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 2700K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 74.6 lumens
Efficiency: N/A
Efficacy: 11.3 lumens/watt
Spacing Criteria (0/90/45): 1.7 / 1.7 / 1.49
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 6.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503594

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (2700K-650LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503594

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (2700K-650LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88		
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77		
3	95	86	79	73	92	84	78	72	81	76	71	79	74	70	76	72	69	67		
4	88	77	69	64	85	76	69	63	73	67	62	71	66	61	69	64	61	59		
5	81	70	62	56	79	69	61	55	67	60	55	65	59	54	63	58	54	52		
6	75	63	55	49	73	62	55	49	60	54	49	59	53	48	57	52	48	46		
7	70	57	49	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41		
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37		
9	61	48	40	35	59	48	40	35	47	40	35	45	39	35	44	39	35	33		
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	31	30		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	789
5°	786
10°	783
15°	846
20°	939
25°	1062
30°	1193
35°	1269
40°	1179
45°	955
50°	657
55°	360
60°	253
65°	233
70°	216
75°	238
80°	249
85°	283

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 955 cd/sqm

TEST NUMBER: P1503594

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (2700K-650LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2.4	3.2
10°-20°	7.6	10.2
20°-30°	14.5	19.4
30°-40°	20.6	27.6
40°-50°	16.7	22.4
50°-60°	6.7	9.0
60°-70°	3.2	4.3
70°-80°	2.1	2.8
80°-90°	0.8	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	24.5	32.8
0°-40°	45.1	60.4
0°-60°	68.5	91.8
0°-90°	74.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	74.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	26	
5°	25	2
15°	26	8
25°	31	14
35°	34	21
45°	22	17
55°	7	7
65°	3	3
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1503594

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (2700K-650LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	25.6
2.5°	25.5
5°	25.4
7.5°	25.2
10°	25.0
12.5°	25.6
15°	26.5
17.5°	27.5
20°	28.6
22.5°	29.8
25°	31.2
27.5°	32.4
30°	33.5
32.5°	34.4
35°	33.7
37.5°	32.0
40°	29.3
42.5°	25.9
45°	21.9
47.5°	17.8
50°	13.7
52.5°	9.8
55°	6.7
57.5°	5.0
60°	4.1
62.5°	3.6
65°	3.2
67.5°	2.8
70°	2.4
72.5°	2.2
75°	2.0
77.5°	1.8
80°	1.4
82.5°	1.3
85°	0.8
87.5°	0.2
90°	0.0

(END OF REPORT)