

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503638

Luminaire Tested: PRLX-SM4-02-LS-FS-D2W-XXXX-BRSS-XX (2700K-1000LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503638
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-6)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-02-LS-FS-D2W-XXXX-BRSS-XX (2700K-1000LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, RING, BRASS REFLECTOR
LIGHT LEVEL 3 - 1000 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 2700K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 134.7 lumens
Efficiency: N/A
Efficacy: 11.7 lumens/watt
Spacing Criteria (0/90/45): 1.7 / 1.7 / 1.49
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 11.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503638

CATALOG NUMBER: PRLX-SM4-02-LS-FS-D2W-XXXX-BRSS-XX (2700K-1000LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503638

CATALOG NUMBER: PRLX-SM4-02-LS-FS-D2W-XXXX-BRSS-XX (2700K-1000LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	86	79	73	92	84	78	72	81	76	71	79	74	70	76	72	69	67			
4	88	77	69	64	85	76	69	63	73	67	62	71	66	61	69	65	61	59			
5	81	70	62	56	79	69	61	55	67	60	55	65	59	54	63	58	54	52			
6	75	63	55	49	73	62	55	49	60	54	49	59	53	48	57	52	48	46			
7	70	57	49	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41			
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37			
9	61	48	40	35	59	48	40	35	47	40	35	45	39	35	44	39	35	33			
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	31	30			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1425
5°	1421
10°	1412
15°	1529
20°	1693
25°	1916
30°	2154
35°	2293
40°	2129
45°	1723
50°	1185
55°	651
60°	456
65°	423
70°	388
75°	429
80°	444
85°	495

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1723 cd/sqm

TEST NUMBER: P1503638

CATALOG NUMBER: PRLX-SM4-02-LS-FS-D2W-XXXX-BRSS-XX (2700K-1000LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	4.4	3.2
10°-20°	13.7	10.2
20°-30°	26.1	19.4
30°-40°	37.2	27.6
40°-50°	30.1	22.4
50°-60°	12.2	9.0
60°-70°	5.8	4.3
70°-80°	3.8	2.8
80°-90°	1.5	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	44.2	32.8
0°-40°	81.4	60.4
0°-60°	123.7	91.8
0°-90°	134.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	134.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	46	
5°	46	4
15°	48	14
25°	56	26
35°	61	37
45°	40	30
55°	12	12
65°	6	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1503638

CATALOG NUMBER: PRLX-SM4-02-LS-FS-D2W-XXXX-BRSS-XX (2700K-1000LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	46.2
2.5°	46.0
5°	45.9
7.5°	45.5
10°	45.1
12.5°	46.2
15°	47.9
17.5°	49.7
20°	51.6
22.5°	53.8
25°	56.3
27.5°	58.5
30°	60.5
32.5°	62.1
35°	60.9
37.5°	57.8
40°	52.9
42.5°	46.8
45°	39.5
47.5°	32.1
50°	24.7
52.5°	17.7
55°	12.1
57.5°	9.0
60°	7.4
62.5°	6.5
65°	5.8
67.5°	5.1
70°	4.3
72.5°	4.0
75°	3.6
77.5°	3.3
80°	2.5
82.5°	2.3
85°	1.4
87.5°	0.4
90°	0.0

(END OF REPORT)