

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503939

Luminaire Tested: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-ND (2700K-750LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503939
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-17)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-ND (2700K-750LM)
Description: PrentaLux Fluxyn SM6 SURFACE MOUNT, DISC, NO DIFFUSER, BRONZE REFLECTOR
LIGHT LEVEL 1 - 750 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 2700K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 670.6 lumens
Efficiency: N/A
Efficacy: 83.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.36
Luminous Opening: Circular (Dia: 1.17' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503939

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-ND (2700K-750LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503939

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-ND (2700K-750LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	79	78								
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	69	68								
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59								
5	81	70	62	56	79	69	61	55	67	60	55	65	59	54	63	58	54	52								
6	75	63	55	49	73	62	55	49	60	54	49	59	53	48	57	52	48	46								
7	70	57	49	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41								
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37								
9	61	48	41	35	60	48	40	35	47	40	35	46	39	35	45	39	35	33								
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	41	36	32	30								

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3011
5°	3012
10°	3006
15°	2992
20°	2968
25°	2944
30°	2895
35°	2864
40°	2826
45°	2748
50°	2491
55°	2089
60°	1551
65°	882
70°	177
75°	39
80°	58
85°	116

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2748 cd/sqm

TEST NUMBER: P1503939

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-ND (2700K-750LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.3	4.2
10°-20°	80.9	12.1
20°-30°	122.0	18.2
30°-40°	145.8	21.7
40°-50°	147.1	21.9
50°-60°	105.8	15.8
60°-70°	37.9	5.6
70°-80°	2.0	0.3
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	231.3	34.5
0°-40°	377.1	56.2
0°-60°	630.0	94.0
0°-90°	670.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	670.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	299	
5°	298	28
15°	287	81
25°	265	122
35°	233	146
45°	193	147
55°	119	106
65°	37	38
75°	1	2
85°	1	1
90°	0	

TEST NUMBER: P1503939

CATALOG NUMBER: PRLX-SM6-03-LS-FS-010-XXXX-BRNZ-XX-ND (2700K-750LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	299
2.5°	298
5°	298
7.5°	296
10°	294
12.5°	291
15°	287
17.5°	282
20°	277
22.5°	272
25°	265
27.5°	258
30°	249
32.5°	241
35°	233
37.5°	225
40°	215
42.5°	206
45°	193
47.5°	177
50°	159
52.5°	140
55°	119
57.5°	98
60°	77
62.5°	57
65°	37
67.5°	19
70°	6
72.5°	2
75°	1
77.5°	1
80°	1
82.5°	1
85°	1
87.5°	0
90°	0

(END OF REPORT)