

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503655

Luminaire Tested: PRLX-SM4-02-LS-FS-D2W-XXXX-WHTE-XX (2700K-800LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503655
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-02-LS-FS-D2W-XXXX-WHITE-XX (2700K-800LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, RING, WHITE REFLECTOR
LIGHT LEVEL 2 - 800 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 2700K CCT, 90 CRI - DIM TO WARM (1800K)
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 250.5 lumens
Efficiency: N/A
Efficacy: 28.5 lumens/watt
Spacing Criteria (0/90/45): 1.54 / 1.54 / 1.45
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 8.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503655

CATALOG NUMBER: PRLX-SM4-02-LS-FS-D2W-XXXX-WHTE-XX (2700K-800LM)

Luminous Intensity Polar Plot



TEST NUMBER: P1503655

CATALOG NUMBER: PRLX-SM4-02-LS-FS-D2W-XXXX-WHTE-XX (2700K-800LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20				
RC	80					70					50					30					10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10		
R	C																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100							
1	109	105	101	97	107	102	99	95	98	95	92	94	92	90	91	89	87	85							
2	100	92	86	80	98	90	84	79	87	82	78	84	79	76	81	77	74	72							
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	62							
4	84	73	65	58	82	72	64	58	69	62	57	67	61	56	65	60	56	53							
5	78	66	57	51	76	64	56	50	62	55	50	60	54	49	59	53	49	47							
6	72	59	51	44	70	58	50	44	57	49	44	55	48	44	53	48	43	41							
7	67	54	45	39	65	53	45	39	52	44	39	50	44	39	49	43	38	37							
8	62	49	41	35	61	49	41	35	47	40	35	46	39	35	45	39	35	33							
9	58	45	37	32	57	45	37	32	43	36	31	42	36	31	41	35	31	29							
10	55	42	34	29	53	41	34	29	40	33	29	39	33	28	38	32	28	27							

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2575
5°	2585
10°	2615
15°	2749
20°	2924
25°	3123
30°	3301
35°	3347
40°	3160
45°	2778
50°	2312
55°	1801
60°	1579
65°	1510
70°	1506
75°	1597
80°	1847
85°	1911

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2778 cd/sqm

TEST NUMBER: P1503655

CATALOG NUMBER: PRLX-SM4-02-LS-FS-D2W-XXXX-WHTE-XX (2700K-800LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	8.0	3.2
10°-20°	24.5	9.8
20°-30°	42.4	16.9
30°-40°	54.9	21.9
40°-50°	49.0	19.6
50°-60°	31.2	12.4
60°-70°	20.7	8.2
70°-80°	14.2	5.7
80°-90°	5.6	2.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	74.9	29.9
0°-40°	129.8	51.8
0°-60°	209.9	83.8
0°-90°	250.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	250.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	84	
5°	84	8
15°	86	25
25°	92	42
35°	89	55
45°	64	49
55°	34	31
65°	21	21
75°	13	14
85°	5	6
90°	0	

TEST NUMBER: P1503655

CATALOG NUMBER: PRLX-SM4-02-LS-FS-D2W-XXXX-WHTE-XX (2700K-800LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	83.5
2.5°	83.4
5°	83.5
7.5°	83.5
10°	83.5
12.5°	84.8
15°	86.1
17.5°	87.5
20°	89.1
22.5°	90.6
25°	91.8
27.5°	92.5
30°	92.7
32.5°	92.0
35°	88.9
37.5°	84.5
40°	78.5
42.5°	71.4
45°	63.7
47.5°	56.2
50°	48.2
52.5°	40.5
55°	33.5
57.5°	28.9
60°	25.6
62.5°	23.0
65°	20.7
67.5°	18.6
70°	16.7
72.5°	15.0
75°	13.4
77.5°	12.0
80°	10.4
82.5°	8.6
85°	5.4
87.5°	1.5
90°	0.0

(END OF REPORT)