

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503597

Luminaire Tested: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (3000K-650LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503597
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-6)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (3000K-650LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, RING, BRASS REFLECTOR
LIGHT LEVEL 1 - 650 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3000K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 72.1 lumens
Efficiency: N/A
Efficacy: 11.1 lumens/watt
Spacing Criteria (0/90/45): 1.7 / 1.7 / 1.49
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 6.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503597

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (3000K-650LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503597

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (3000K-650LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88					88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	78	77					77			
3	95	86	79	73	92	84	78	72	81	76	71	79	74	70	76	72	69	67					67			
4	88	77	69	64	85	76	69	63	73	67	62	71	66	61	69	64	61	59					59			
5	81	70	62	56	79	69	61	55	67	60	55	65	59	54	63	58	54	52					52			
6	75	63	55	49	73	62	55	49	60	54	49	59	53	48	57	52	48	46					46			
7	70	57	49	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41					41			
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37					37			
9	61	48	40	35	59	48	40	35	47	40	35	45	39	35	44	39	35	33					33			
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	31	30					30			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	762
5°	761
10°	758
15°	817
20°	906
25°	1028
30°	1154
35°	1227
40°	1139
45°	925
50°	633
55°	349
60°	247
65°	226
70°	207
75°	226
80°	249
85°	283

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 925 cd/sqm

TEST NUMBER: P1503597

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (3000K-650LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2.3	3.2
10°-20°	7.3	10.2
20°-30°	14.0	19.4
30°-40°	19.9	27.6
40°-50°	16.1	22.4
50°-60°	6.5	9.0
60°-70°	3.1	4.3
70°-80°	2.0	2.8
80°-90°	0.8	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	23.7	32.8
0°-40°	43.6	60.4
0°-60°	66.2	91.8
0°-90°	72.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	72.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	25	
5°	25	2
15°	26	7
25°	30	14
35°	33	20
45°	21	16
55°	6	7
65°	3	3
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1503597

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-BRSS-XX (3000K-650LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	24.7
2.5°	24.6
5°	24.6
7.5°	24.4
10°	24.2
12.5°	24.7
15°	25.6
17.5°	26.6
20°	27.6
22.5°	28.8
25°	30.2
27.5°	31.3
30°	32.4
32.5°	33.3
35°	32.6
37.5°	30.9
40°	28.3
42.5°	25.0
45°	21.2
47.5°	17.2
50°	13.2
52.5°	9.5
55°	6.5
57.5°	4.8
60°	4.0
62.5°	3.5
65°	3.1
67.5°	2.7
70°	2.3
72.5°	2.1
75°	1.9
77.5°	1.7
80°	1.4
82.5°	1.3
85°	0.8
87.5°	0.2
90°	0.0

(END OF REPORT)