

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503613

Luminaire Tested: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (3000K-800LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503613
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (3000K-800LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, RING, WHITE REFLECTOR
LIGHT LEVEL 2 - 800 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3000K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 220.9 lumens
Efficiency: N/A
Efficacy: 26.6 lumens/watt
Spacing Criteria (0/90/45): 1.54 / 1.54 / 1.45
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 8.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503613

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (3000K-800LM)

Luminous Intensity Polar Plot



TEST NUMBER: P1503613

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (3000K-800LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	109	105	101	97	107	102	99	95	98	95	92	94	92	90	91	89	87	85		
2	100	92	86	80	98	90	84	79	87	82	78	84	79	76	81	77	74	72		
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	62		
4	84	73	65	58	82	72	64	58	69	62	57	67	61	56	65	60	56	53		
5	78	66	57	51	76	64	56	50	62	55	50	60	54	49	59	53	49	47		
6	72	59	51	44	70	58	50	44	57	49	44	55	48	44	53	48	43	41		
7	67	54	45	39	65	53	45	39	52	44	39	50	44	39	49	43	38	37		
8	62	49	41	35	61	49	41	35	47	40	35	46	39	35	45	39	34	33		
9	58	45	37	32	57	45	37	32	43	36	31	42	36	31	41	35	31	29		
10	55	42	34	29	53	41	34	29	40	33	29	39	33	28	38	32	28	27		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2270
5°	2278
10°	2305
15°	2423
20°	2576
25°	2756
30°	2909
35°	2951
40°	2786
45°	2451
50°	2039
55°	1591
60°	1394
65°	1335
70°	1325
75°	1406
80°	1634
85°	1698

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2451 cd/sqm

TEST NUMBER: P1503613

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (3000K-800LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	7.0	3.2
10°-20°	21.6	9.8
20°-30°	37.4	16.9
30°-40°	48.4	21.9
40°-50°	43.2	19.6
50°-60°	27.5	12.4
60°-70°	18.2	8.2
70°-80°	12.6	5.7
80°-90°	5.0	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	66.0	29.9
0°-40°	114.4	51.8
0°-60°	185.1	83.8
0°-90°	220.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	220.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	74	
5°	74	7
15°	76	22
25°	81	37
35°	78	48
45°	56	43
55°	30	27
65°	18	18
75°	12	13
85°	5	5
90°	0	

TEST NUMBER: P1503613

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (3000K-800LM)

CANDELA DISTRIBUTION (FULL):

0°	
0°	73.6
2.5°	73.5
5°	73.6
7.5°	73.6
10°	73.6
12.5°	74.7
15°	75.9
17.5°	77.2
20°	78.5
22.5°	79.9
25°	81.0
27.5°	81.6
30°	81.7
32.5°	81.1
35°	78.4
37.5°	74.5
40°	69.2
42.5°	62.9
45°	56.2
47.5°	49.6
50°	42.5
52.5°	35.7
55°	29.6
57.5°	25.5
60°	22.6
62.5°	20.2
65°	18.3
67.5°	16.4
70°	14.7
72.5°	13.3
75°	11.8
77.5°	10.6
80°	9.2
82.5°	7.6
85°	4.8
87.5°	1.3
90°	0.0

(END OF REPORT)