

Scaled data based on original data using
LM-79-2024 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P1503615

Luminaire Tested: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (3500K-650LM)

Issue Date: 7/28/2026

Test Information

Test Method: LM-79-2024
Report Number: P1503615
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2606-836-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PrentaLux
Catalog Number: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (3500K-650LM)
Description: PrentaLux Fluxyn SM4 SURFACE MOUNT, RING, WHITE REFLECTOR
LIGHT LEVEL 1 - 650 NOMINAL LUMENS
Light Source: SELECTABLE CCT - 3500K CCT, 90 CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 174.9 lumens
Efficiency: N/A
Efficacy: 26.9 lumens/watt
Spacing Criteria (0/90/45): 1.54 / 1.54 / 1.45
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 6.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1503615

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (3500K-650LM)

Luminous Intensity Polar Plot





TEST NUMBER: P1503615

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (3500K-650LM)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	109	105	101	97	107	102	99	95	98	95	92	94	92	90	91	89	87	85		
2	100	92	86	80	97	90	84	79	87	82	78	84	79	76	81	77	74	72		
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	62		
4	84	73	65	58	82	72	64	58	69	62	57	67	61	56	65	60	56	53		
5	78	66	57	51	76	64	56	50	62	55	50	60	54	49	59	53	49	47		
6	72	59	51	44	70	58	50	44	57	49	44	55	48	43	53	48	43	41		
7	67	54	45	39	65	53	45	39	52	44	39	50	44	39	49	43	38	37		
8	62	49	41	35	61	49	41	35	47	40	35	46	39	35	45	39	34	33		
9	58	45	37	32	57	45	37	32	43	36	31	42	36	31	41	35	31	29		
10	55	42	34	29	53	41	34	29	40	33	29	39	33	28	38	32	28	27		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1798
5°	1805
10°	1825
15°	1919
20°	2041
25°	2181
30°	2304
35°	2338
40°	2206
45°	1941
50°	1612
55°	1258
60°	1104
65°	1058
70°	1055
75°	1108
80°	1296
85°	1344

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1941 cd/sqm

TEST NUMBER: P1503615

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (3500K-650LM)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	5.6	3.2
10°-20°	17.1	9.8
20°-30°	29.6	16.9
30°-40°	38.4	21.9
40°-50°	34.2	19.5
50°-60°	21.8	12.4
60°-70°	14.4	8.2
70°-80°	10.0	5.7
80°-90°	4.0	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	52.3	29.9
0°-40°	90.6	51.8
0°-60°	146.6	83.8
0°-90°	174.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	174.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	58	
5°	58	6
15°	60	17
25°	64	30
35°	62	38
45°	44	34
55°	23	22
65°	14	14
75°	9	10
85°	4	4
90°	0	

TEST NUMBER: P1503615

CATALOG NUMBER: PRLX-SM4-02-LS-FS-010-XXXX-WHTE-XX (3500K-650LM)

CANDELA DISTRIBUTION (FULL):

	0°
0°	58.3
2.5°	58.2
5°	58.3
7.5°	58.3
10°	58.3
12.5°	59.2
15°	60.1
17.5°	61.1
20°	62.2
22.5°	63.2
25°	64.1
27.5°	64.6
30°	64.7
32.5°	64.2
35°	62.1
37.5°	59.0
40°	54.8
42.5°	49.8
45°	44.5
47.5°	39.2
50°	33.6
52.5°	28.3
55°	23.4
57.5°	20.2
60°	17.9
62.5°	16.0
65°	14.5
67.5°	13.0
70°	11.7
72.5°	10.5
75°	9.3
77.5°	8.4
80°	7.3
82.5°	6.0
85°	3.8
87.5°	1.1
90°	0.0

(END OF REPORT)